




Wera Bit Drivers, Bits, & Adapters


Driver Bit, Bitholding Screwdriver, and L-key Set

This 52-piece set packs maximum screwdriving utility into a compact, lightweight set protected by an extremely robust folding textile box.

- BiTorsion bits for long service life
- Impaktor bits for extreme conditions
- Chrome-plated Hex-Plus L-keys with ball-end hex on long arm
- One Rapidaptor bit holder for quick, one-handed bit changes
- One Kraftform Kompact bitholding screwdriver for that ergonomic Kraftform feel



Take-it-Easy Tool Finder



BiTorsion Bits



Impaktor Impact Bits

Screwdriver Bit Sets

Part Number	Part Image	Number of Pieces	Type	Size (Tip Size x Length)	Quantity Included	Set Includes	Price
<u>05057460055</u>		52	 Phillips	#1 x 25mm	2	bitholding screwdriver with Rapidaptor quick-release chuck, Rapidaptor universal bit holder, (8) BiTorsion Phillips bits ((2) #1, (4) #2, (2) #3), (3) Impaktor Phillips bits ((2) #2, #3), (8) BiTorsion Pozidriv bits ((2) #1, (4) #2, (2) #3), (3) Impaktor Pozidriv bits ((2) #2, #3), (12) BiTorsion Torx bits ((2) T10, (2) T15, (3) T20, (2) T25, (2) T30, T40), (3) Impaktor Torx bits (T25, T30, T40), (2) BiTorsion 5.5mm flat/slotted bits, (3) Impaktor hex bits (4, 5, 6mm), (8) L-keys with Hex-Plus profile (1.5, 2, 2.5, 3, 4, 5, 6, 8mm), durable cloth pouch	
				#2 x 25mm	4		
				#3 x 25mm	2		
			 Impact-rated Phillips	#2 x 50mm	2		
				#3 x 50mm	1		
			 Slotted	0.8 x 5.5mm x 25mm	1		
				1 x 5.5mm x 25mm	1		
			 Pozidriv	#1 x 25mm	2		
				#2 x 25mm	4		
				#3 x 25mm	2		
			 Impact-rated Pozidriv	#2 x 50mm	2		
				#3 x 50mm	1		
			 Torx	T10 x 25mm	2		
				T15 x 25mm	2		
				T20 x 25mm	3		
				T25 x 25mm	2		
				T30 x 25mm	2		
				T40 x 25mm	1		
			 Impact-rated Torx	T25 x 50mm	1		
				T30 x 50mm	1		
				T40 x 50mm	1		
			 Impact-rated Hex Plus	4 x 50mm	1		
				5 x 50mm	1		
				6 x 50mm	1		
			 Hex Plus L-key	1.5 x 50mm	1		
				2 x 56mm	1		
				2.5 x 63mm	1		
				3 x 71mm	1		
4 x 80mm	1						
5 x 90mm	1						
6 x 100mm	1						
8 x 112mm	1						

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.




Wera Bit Drivers, Bits, & Adapters

Universal Bit Holder

The Rapidaptor universal bit holder is designed for bits with 1/4 in external hexagon drives. The Rapidaptor allows for mounting the bits without using the sleeve. The bit is removed by simply pushing it forward—for lightning-fast bit changes with just one hand.

Features

- Rapidaptor technology for rapid bit change
- Free-floating magnetic sleeve
- One-hand operation



Driver Bit Adapter				
Part Number	Drive Size	Overall Length	Description	Price
TW-DB-ADT-MAG	1/4in	2.25in [57mm]	Wera Rapidaptor magnetic driver bit adapter, 1/4in drive, 2.25in (57mm) overall length. Rapidaptor technology for rapid bit change.	

Note: Bit-holders are warranted against manufacturer defect only.



Wera Bit Drivers, Bits, & Adapters

Standard Driver Bits

Wera bits are designed for demanding applications in trade and industry. They are able to transfer high torque loads, are safe to use, and are extremely durable.



Standard Driver Bits								
Part Number	Part Image	Type	Tip Size	Bit Length	Drive Size	Description	Package Quantity	Price
<u>TW-DB-PH-1</u>		 Phillips	#1	2.75in	1/4in	Wera #1 Phillips general purpose driver bit, 2.75in bit length, 1/4in drive, hexagonal. Package of 10.	10	
<u>TW-DB-PH-2</u>			#2			Wera #2 Phillips general purpose driver bit, 2.75in bit length, 1/4in drive, hexagonal. Package of 10.		
<u>TW-DB-SL-1</u>		 Slotted	3.0mm	2in		Wera 3.0mm slotted general purpose driver bit, 2in bit length, 1/4in drive, hexagonal. Package of 10.		

Note: Screwdriver bits are warranted against manufacturer defect only.