


# WA-F1/F2 Panels for Single-Door Freestanding Enclosures



## Description

- Panels for single-door single-access and single-door dual-access, freestanding NEMA 12, and freestanding NEMA 4 enclosures
- Can be positioned anywhere along horizontal depth-wise mounting channels
- Half-height panels can be located in the upper or lower portion of the enclosure
- Mounting hardware is furnished with each panel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- May be used in two-door enclosures along with other freestanding accessories


Enclosure Shipping Schedule					
Same day	1 - 5 days	1 - 7 days	1 - 10 days	1 - 15 days	1 - 20 days

Color indicates shipping lead time in business days.

Painted Steel	Price	Galvanized	Price	Steel Gauge	Panel Size HxW	Subpanel Type
<b>WA60P24F1</b>	\$276.00	<b>WA60P24F1G</b>	\$276.00	12	48.00 x 20.00 [1219 x 508]	Full
<b>WA60P24F2</b>	\$183.00	<b>WA60P24F2G</b>	\$183.00	10	24.88 x 20.00 [632 x 508]	Half
<b>WA60P36F1</b>	\$356.00	<b>WA60P36F1G</b>	\$356.00	12	48.00 x 32.00 [1219 x 813]	Full
<b>WA60P36F2</b>	\$224.00	<b>WA60P36F2G</b>	\$224.00	12	24.88 x 32.00 [632 x 813]	Half
<b>WA72P24F1</b>	\$309.00	<b>WA72P24F1G</b>	\$309.00	12	60.00 x 20.00 [1524 x 508]	Full
<b>WA72P24F2</b>	\$199.00	<b>WA72P24F2G</b>	\$199.00	12	30.88 x 20.00 [784 x 508]	Half
<b>WA72P30F1</b>	\$359.00	<b>WA72P30F1G</b>	\$359.00	12	60.00 x 26.00 [1524 x 660]	Full
<b>WA72P30F2</b>	\$224.00	<b>WA72P30F2G</b>	\$224.00	10	30.88 x 26.00 [784 x 660]	Half
<b>WA72P36F1</b>	\$409.00	<b>WA72P36F1G</b>	\$409.00	12	60.00 x 32.00 [1524 x 813]	Full
<b>WA72P36F2</b>	\$250.00	<b>WA72P36F2G</b>	\$250.00	12	30.88 x 32.00 [784 x 813]	Half
<b>WA90P24F1</b>	\$359.00	<b>WA90P24F1G</b>	\$359.00	12	78.00 x 20.00 [1981 x 508]	Full
<b>WA90P24F2</b>	\$224.00	<b>WA90P24F2G</b>	\$224.00	10	39.88 x 20.00 [1013 x 508]	Half
<b>WA90P36F1</b>	\$489.00	<b>WA90P36F1G</b>	\$489.00	12	78.00 x 32.00 [1981 x 813]	Full
<b>WA90P36F2</b>	\$290.00	<b>WA90P36F2G</b>	\$290.00	10	39.88 x 32.00 [1013 x 813]	Half


**Notes: Dimensions in inches (millimeters).**  
 Letters in table correspond to letters on dimensional drawing.  
 If used in a two-door enclosure, a center panel support must be ordered.  
 Suffix F1= full panel, F2 = half panel

## Dimensions in [mm]



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com)  
for complete engineering drawings.

# WA-F1/F2 Panels for Two Door Freestanding Enclosures



## Description

- Panels for two-door single-access and two-door dual-access, freestanding NEMA 12 enclosures
- Manufactured of 10 gauge steel and can be positioned anywhere along horizontal depth-wise mounting channels
- Half-height panels can be located in the upper or lower portion of the enclosure
- Mounting hardware is furnished with each panel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)

Enclosure Shipping Schedule					
Same day	1 - 5 days	1 - 7 days	1 - 10 days	1 - 15 days	1 - 20 days


Color indicates shipping lead time in business days.

Painted Steel	Price	Galvanized	Price	Panel Size AxB	Subpanel Type
<b>WA60P48F1</b>	\$571.00	<b>WA60P48F1G</b>	\$571.00	48.00 x 44.00 [1219 x 1118]	Full
<b>WA60P48F2</b>	\$311.00	<b>WA60P48F2G</b>	\$311.00	24.88 x 44.00 [632 x 1118]	Half
<b>WA72P48F1</b>	\$645.00	<b>WA72P48F1G</b>	\$645.00	60.00 x 44.00 [1524 x 1118]	Full
<b>WA72P48F2</b>	\$413.00	<b>WA72P48F2G</b>	\$413.00	30.88 x 44.00 [784 x 1118]	Half
<b>WA72P60F1</b>	\$748.00	<b>WA72P60F1G</b>	\$748.00	60.00 x 56.00 [1524 x 1422]	Full
<b>WA72P60F2</b>	\$465.00	<b>WA72P60F2G</b>	\$465.00	30.88 x 56.00 [784 x 1422]	Half
<b>WA72P72F1</b>	\$851.00	-	-	68.00 x 68.00 [1727 x 1727]	Full
<b>WA72P72F2</b>	\$518.00	<b>WA72P72F2G</b>	\$518.00	30.88 x 68.88 [784 x 1727]	Half
<b>WA90P48F1</b>	\$759.00	<b>WA90P48F1G</b>	\$759.00	78.00 x 44.00 [1981 x 1118]	Full
<b>WA90P48F2</b>	\$470.00	<b>WA90P48F2G</b>	\$470.00	39.88 x 44.00 [1013 x 1118]	Half
<b>WA90P72F1</b>	\$1,025.00	-	-	78.00 x 68.00 [1981 x 1727]	Full
<b>WA90P72F2</b>	\$605.00	<b>WA90P72F2G</b>	\$605.00	39.88 x 68.00 [1013 x 1727]	Half

**Notes:** Dimensions in inches [millimeters].  
Letters in table correspond to letters on dimensional drawing.  
Suffix F1 = full panel, F2 = half panel

## Dimensions


in [mm]



**IMPORTANT NOTE:** CENTER PANEL SUPPORT IS SUPPLIED WITH A REGULAR TWO-DOOR ENCLOSURE PANEL. THIS SUPPORT IS USED ONLY AS A BRACE. IT IS NOT INTENDED TO BE USED AS A SUPPORT FOR SINGLE-DOOR SUBPANELS, RELAY RACKS, ETC. USE WA\_FSCPS PANEL SUPPORTS FOR THIS PURPOSE.

See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.

# WA-SMP Series Side-Mount Panels for Freestanding Enclosures



## Description

- Panels for freestanding NEMA 4 and freestanding NEMA 12 enclosures
- Panels are fabricated from 12 gauge steel
- They provide extra mounting space on the sides of the enclosure
- Mounting hardware is furnished with each panel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Panels attach securely to mounting channels


Enclosure Shipping Schedule					
Same day	1 - 5 days	1 - 7 days	1 - 10 days	1 - 15 days	1 - 20 days
Color indicates shipping lead time in business days.					

Painted Steel	Price	Galvanized	Price	Panel Size AxB
<b>WA60SMP14</b>	\$167.00	<b>WA60SMP14G</b>	\$167.00	48.00 x 14.00 [1219 x 356]
<b>WA72SMP14</b>	\$190.00	<b>WA72SMP14G</b>	\$190.00	60.00 x 14.00 [1524 x 356]
<b>WA72SMP20</b>	\$232.00	<b>WA72SMP20G</b>	\$232.00	60.00 x 20.00 [1524 x 508]
<b>WA90SMP14</b>	\$273.00	<b>WA90SMP14G</b>	\$273.00	78.00 x 14.00 [1981 x 356]
<b>WA90SMP20</b>	\$285.00	<b>WA90SMP20G</b>	\$285.00	78.00 x 20.00 [1981 x 508]

*Note: Dimensions in inches [millimeters]*


## Dimensions

in [mm]



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.

# WASP-F3/F4 Series Accessory Swing-Out Panels For Freestanding Enclosures



## Description

- Panels for freestanding NEMA 12 enclosures and freestanding NEMA 4 enclosures
- Full-height and half-height swing-out panels are available
- Half-height panels can be located in the upper or lower portion of the enclosure
- Mounting can be on either side of the enclosure
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- May be used in two-door enclosures along with other freestanding accessories
- Fabricated from 12 gauge steel
- Mounting hardware is furnished with each panel

### Enclosure Shipping Schedule

Same day	1 - 5 days	1 - 7 days	1 - 10 days	1 - 15 days	1 - 20 days
----------	------------	------------	-------------	-------------	-------------

Color indicates shipping lead time in business days.

Painted Steel	Price	Galvanized	Price	Panel Size AxB	Subpanel Type
<b>WA60SP24F3</b>	\$436.00	<b>WA60SP24F3G</b>	\$436.00	48.00 x 19.00 [1219 x 483]	Full
<b>WA60SP24F4</b>	\$307.00	<b>WA60SP24F4G</b>	\$307.00	24.88 x 19.00 [632 x 483]	Half
<b>WA60SP36F3</b>	\$537.00	<b>WA60SP36F3G</b>	\$537.00	48.00 x 31.00 [1219 x 787]	Full
<b>WA60SP36F4</b>	\$356.00	<b>WA60SP36F4G</b>	\$356.00	24.88 x 31.00 [632 x 787]	Half
<b>WA72SP24F3</b>	\$539.00	<b>WA72SP24F3G</b>	\$539.00	60.00 x 19.00 [1524 x 483]	Full
<b>WA72SP24F4</b>	\$366.00	<b>WA72SP24F4G</b>	\$366.00	30.88 x 19.00 [784 x 483]	Half
<b>WA72SP30F3</b>	\$625.00	<b>WA72SP30F3G</b>	\$625.00	60.00 x 25.00 [1524 x 635]	Full
<b>WA72SP30F4</b>	\$414.00	<b>WA72SP30F4G</b>	\$414.00	30.88 x 25.00 [784 x 635]	Half
<b>WA72SP36F3</b>	\$711.00	<b>WA72SP36F3G</b>	\$711.00	60.00 x 31.00 [1524 x 787]	Full
<b>WA72SP36F4</b>	\$461.00	<b>WA72SP36F4G</b>	\$461.00	30.88 x 31.00 [784 x 787]	Half
<b>WA90SP36F3</b>	\$844.00	<b>WA90SP36F3G</b>	\$844.00	78.00 x 31.00 [1981 x 787]	Full
<b>WA90SP36F4</b>	\$532.00	<b>WA90SP36F4G</b>	\$532.00	39.88 x 31.00 [1013 x 787]	Half


Notes: Dimensions in inches [millimeters].

Note 1: If used in a two-door enclosure, a center panel support must be ordered.

Note 2: Suffix F3 =full panel, F4 =half panel

## Dimensions

in [mm]



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.