



PARTEX Slide-on Wire Markers



Overview


The Partex MDH2010 blue key ring wire marker dispenser holds 20 marker carrier wands. Each carrier wand contains 25 slide-on PVC markers suitable for 16–10 AWG [1.5–4 mm²] wire with a diameter range of 0.098–0.197in [2.5–5mm]. Markers are available in ten standard colors — black, brown, red, orange, yellow, green, blue, violet, gray, and white. Markers can be ordered blank or pre-printed with a wide range of characters including numerals (0–9), letters (A–C), and symbols such as plus, minus, ground, dot, and slash. Yellow and white markers offer the broadest character selection, while the remaining colors follow IEC 60445 wire color coding conventions, each available with its designated numeral. A pre-sorted 0–9 assortment set is also available in yellow, white, and IEC color-coded versions for quick mixed-character installations.

The Partex MDH2002 red key ring wire marker dispenser holds 20 marker carrier wands. Each carrier wand contains 25 slide-on PVC markers suitable for 22–16 AWG [0.5–1.5 mm²] wire with a diameter range of 0.051–0.118in [1.3–3mm]. Marker colors, character options, and assortment sets mirror those available for the MDH2010, making the two dispensers a complementary pair. Together they cover a broad range of wire gauges commonly found in industrial wiring. Both dispensers feature a key ring design for convenient bench or belt mounting, keeping the full range of marker carrier wands organized and accessible during installation.


Features

- Slide-on marker ensures permanent identification and prevents the marker from falling off
- Key ring dispenser keeps 20 carrier wands accessible and ready
- Each package contains 10 carrier wands with 25 markers per wand for a total of 250 markers per package
- PVC construction is flexible, durable, and resistant to common industrial fluids and UV light
- Durable hot-stamped characters — built for long-lasting, highly legible identification
- Available in ten marker colors with a broad range of pre-printed characters including numerals, letters, and symbols
- Follows IEC 60445 wire color coding conventions for color-designated numeral markers
- Temperature range: -30 to +60 °C [-22 to +140 °F]
- Flame resistant — UL 94 V-0 rated
- RoHS compliant


Carrier Wand Installation




Carrier Wand Removal



Wire Marker Installation



PARTEX Slide-on Wire Markers



Partex Blue Key Ring Wire Dispenser

Part Number	Part Image	Price	Description	Qty
<u>MDH2010</u>		\$18.00	Partex marker applicator holder, blue. For use with Partex MD markers. Wire markers not included.	1

Partex Blue Wire Carriers with Markers



Part Number	Part Image	Price	Marker Color	Character	Wire Size Range	Wire Diameter Range	Qty/Pack
Marker Color: Black							
MD-10003-0		\$14.50	Black	Blank	16–10 AWG MTW wire 14–10 AWG THHN wire	2.5–5mm [0.09–0.19in]	250 markers per pack (10 carrier wands with 25 markers per wand)
MD-10003-09.0		\$14.50	White On Black	0			
Marker Color: Brown							
MD-10003-1		\$14.50	Brown	Blank	16–10 AWG MTW wire 14–10 AWG THHN wire	2.5–5mm [0.09–0.19in]	250 markers per pack (10 carrier wands with 25 markers per wand)
MD-10003-19.1		\$14.50	White On Brown	1			
Marker Color: Red							
MD-10003-2		\$14.50	Red	Blank	16–10 AWG MTW wire 14–10 AWG THHN wire	2.5–5mm [0.09–0.19in]	250 markers per pack (10 carrier wands with 25 markers per wand)
MD-10003-29.2		\$14.50	White On Red	2			
MD-10003-29.PLUS		\$14.50	White On Red	Plus (+)			
Marker Color: Orange							
MD-10003-3		\$14.50	Orange	Blank	16–10 AWG MTW wire 14–10 AWG THHN wire	2.5–5mm [0.09–0.19in]	250 markers per pack (10 carrier wands with 25 markers per wand)
MD-10003-30.3		\$14.50	Black On Orange	3			

table continued on next page

PARTEX Slide-on Wire Markers

Partex Blue Wire Carriers with Markers (cont'd)							
Part Number	Part Image	Price	Marker Color	Character	Wire Size Range	Wire Diameter Range	Qty/Pack
Marker Color: Yellow							
<u>MD-10S40.0-9</u>		\$14.50	Black On Yellow	0-9 Set	16-10 AWG MTW wire 14-10 AWG THHN wire	2.5-5mm [0.09-0.19in]	250 markers per pack (10 carrier wands with 25 markers per wand)
<u>MD-10003-4</u>		\$14.50	Yellow	Blank			
<u>MD-10003-40.0</u>		\$14.50	Black On Yellow	0			
<u>MD-10003-40.1</u>		\$14.50	Black On Yellow	1			
<u>MD-10003-40.2</u>		\$14.50	Black On Yellow	2			
<u>MD-10003-40.3</u>		\$14.50	Black On Yellow	3			
<u>MD-10003-40.4</u>		\$14.50	Black On Yellow	4			
<u>MD-10003-40.5</u>		\$14.50	Black On Yellow	5			
<u>MD-10003-40.6</u>		\$14.50	Black On Yellow	6			
<u>MD-10003-40.7</u>		\$14.50	Black On Yellow	7			
<u>MD-10003-40.8</u>		\$14.50	Black On Yellow	8			
<u>MD-10003-40.9</u>		\$14.50	Black On Yellow	9			
<u>MD-10003-40.A</u>		\$14.50	Black On Yellow	A			
<u>MD-10003-40.B</u>		\$14.50	Black On Yellow	B			
<u>MD-10003-40.C</u>		\$14.50	Black On Yellow	C			
<u>MD-10003-40.DOT</u>		\$14.50	Black On Yellow	Dot (·)			
<u>MD-10003-40.GRD</u>		\$14.50	Black On Yellow	Ground (⏏)			
<u>MD-10003-40.MINUS</u>		\$14.50	Black On Yellow	Minus (-)			
<u>MD-10003-40.PLUS</u>		\$14.50	Black On Yellow	Plus (+)			
<u>MD-10003-40.SLASH</u>		\$14.50	Black On Yellow	Slash (/)			

table continued on next page

PARTEX Slide-on Wire Markers

Partex Blue Wire Carriers with Markers (cont'd)							
Part Number	Part Image	Price	Marker Color	Character	Wire Size Range	Wire Diameter Range	Qty/Pack
Marker Color: Green							
<u>MD-10003-5</u>		\$14.50	Green	Blank	16–10 AWG MTW wire 14–10 AWG THHN wire	2.5–5mm [0.09–0.19in]	250 markers per pack (10 carrier wands with 25 markers per wand)
<u>MD-10003-59.5</u>		\$14.50	White On Green	5			
Marker Color: Blue							
<u>MD-10003-6</u>		\$14.50	Blue	Blank	16–10 AWG MTW wire 14–10 AWG THHN wire	2.5–5mm [0.09–0.19in]	250 markers per pack (10 carrier wands with 25 markers per wand)
<u>MD-10003-69.6</u>		\$14.50	White On Blue	6			
Marker Color: Violet							
<u>MD-10003-7</u>		\$14.50	Violet	Blank	16–10 AWG MTW wire 14–10 AWG THHN wire	2.5–5mm [0.09–0.19in]	250 markers per pack (10 carrier wands with 25 markers per wand)
<u>MD-10003-79.7</u>		\$14.50	White On Violet	7			
Marker Color: Gray							
<u>MD-10003-8</u>		\$14.50	Gray	Blank	16–10 AWG MTW wire 14–10 AWG THHN wire	2.5–5mm [0.09–0.19in]	250 markers per pack (10 carrier wands with 25 markers per wand)
<u>MD-10003-80.8</u>		\$14.50	Black On Gray	8			

table continued on next page

PARTEX Slide-on Wire Markers

Partex Blue Wire Carriers with Markers (cont'd)							
Part Number	Part Image	Price	Marker Color	Character	Wire Size Range	Wire Diameter Range	Qty/Pack
Marker Color: White							
<u>MD-10S90.0-9</u>		\$14.50	Black On White	0-9 Set	16-10 AWG MTW wire 14-10 AWG THHN wire	2.5-5mm [0.09-0.19in]	250 markers per pack (10 carrier wands with 25 markers per wand)
<u>MD-10003-9</u>		\$14.50	White	Blank			
<u>MD-10003-90.0</u>		\$14.50	Black On White	0			
<u>MD-10003-90.1</u>		\$14.50	Black On White	1			
<u>MD-10003-90.2</u>		\$14.50	Black On White	2			
<u>MD-10003-90.3</u>		\$14.50	Black On White	3			
<u>MD-10003-90.4</u>		\$14.50	Black On White	4			
<u>MD-10003-90.5</u>		\$14.50	Black On White	5			
<u>MD-10003-90.6</u>		\$14.50	Black On White	6			
<u>MD-10003-90.7</u>		\$14.50	Black On White	7			
<u>MD-10003-90.8</u>		\$14.50	Black On White	8			
<u>MD-10003-90.9</u>		\$14.50	Black On White	9			
<u>MD-10003-90.A</u>		\$14.50	Black On White	A			
<u>MD-10003-90.B</u>		\$14.50	Black On White	B			
<u>MD-10003-90.C</u>		\$14.50	Black On White	C			
<u>MD-10003-90.DOT</u>		\$14.50	Black On White	Dot (·)			
<u>MD-10003-90.GRD</u>		\$14.50	Black On White	Ground (≡)			
<u>MD-10003-90.MINUS</u>		\$14.50	Black On White	Minus (-)			
<u>MD-10003-90.PLUS</u>		\$14.50	Black On White	Plus (+)			
<u>MD-10003-90.SLASH</u>		\$14.50	Black On White	Slash (/)			

table continued on next page

PARTEX Slide-on Wire Markers

Partex Blue Wire Carriers with Markers (cont'd)

Part Number	Part Image	Price	Marker Color	Character	Wire Size Range	Wire Diameter Range	Qty/Pack
Marker Color: IEC Colors*							
<u>MD-10SCC.0-9</u>	See table below	\$14.50	IEC Colors	0-9 Set	16-10 AWG MTW wire 14-10 AWG THHN wire	2.5-5mm [0.09-0.19in]	250 markers per pack (10 carrier wands with 25 markers per wand)

IEC Colors*		
Character	Part Image	Marker Color
0		White On Black
1		White On Brown
2		White On Red
3		Black On Orange
4		Black On Yellow
5		White On Green
6		White On Blue
7		White On Violet
8		Black On Gray
9		Black On White