


WA-F1/F2 Panels for Single-Door Freestanding Enclosures



Description

- Panels for single-door single-access and single-door dual-access, freestanding NEMA 12, and freestanding NEMA 4 enclosures
- Can be positioned anywhere along horizontal depth-wise mounting channels
- Half-height panels can be located in the upper or lower portion of the enclosure
- Mounting hardware is furnished with each panel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- May be used in two-door enclosures along with other freestanding accessories




Enclosure Shipping Schedule	
1 - 7 days	1 -10 days
Color indicates shipping lead time in business days.	

Painted Steel	Price	Galvanized	Price	Steel Gauge	Panel Size AxB	Subpanel Type
WA60P24F1	\$220.00	WA60P24F1G	\$220.00	12	48.00 x 20.00 [1219 x 508]	Full
WA60P24F2	\$146.00	WA60P24F2G	\$146.00	10	24.88 x 20.00 [632 x 508]	Half
WA60P36F1	\$284.00	WA60P36F1G	\$284.00	12	48.00 x 32.00 [1219 x 813]	Full
WA60P36F2	\$179.00	WA60P36F2G	\$179.00	12	24.88 x 32.00 [632 x 813]	Half
WA72P24F1	\$246.00	WA72P24F1G	\$246.00	12	60.00 x 20.00 [1524 x 508]	Full
WA72P24F2	\$158.00	WA72P24F2G	\$158.00	12	30.88 x 20.00 [784 x 508]	Half
WA72P30F1	\$286.00	WA72P30F1G	\$286.00	12	60.00 x 26.00 [1524 x 660]	Full
WA72P30F2	\$179.00	WA72P30F2G	\$179.00	10	30.88 x 26.00 [784 x 660]	Half
WA72P36F1	\$326.00	WA72P36F1G	\$326.00	12	60.00 x 32.00 [1524 x 813]	Full
WA72P36F2	\$199.00	WA72P36F2G	\$199.00	12	30.88 x 32.00 [784 x 813]	Half
WA90P24F1	\$286.00	WA90P24F1G	\$286.00	12	78.00 x 20.00 [1981 x 508]	Full
WA90P24F2	\$179.00	WA90P24F2G	\$179.00	10	39.88 x 20.00 [1013 x 508]	Half
WA90P36F1	\$383.00	WA90P36F1G	\$383.00	12	78.00 x 32.00 [1981 x 813]	Full
WA90P36F2	\$231.00	WA90P36F2G	\$231.00	10	39.88 x 32.00 [1013 x 813]	Half

Notes: Dimensions in inches [millimeters].
 If used in a two-door enclosure, a center panel support must be ordered.
 Suffix F1= full panel, F2 = half panel


Dimensions

in [mm]



See our website: www.AutomationDirect.com for complete engineering drawings.

WA-F1/F2 Panels for Two-door Freestanding Enclosures



Description

- Panels for two-door single-access and two-door dual-access, freestanding NEMA 12 enclosures
- Manufactured of 10 gauge steel and can be positioned anywhere along horizontal depth-wise mounting channels
- Half-height panels can be located in the upper or lower portion of the enclosure
- Mounting hardware is furnished with each panel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)


Enclosure Shipping Schedule	
1 - 7 days	1 -10 days
Color indicates shipping lead time in business days.	

Painted Steel	Price	Galvanized	Price	Panel Size AxB	Subpanel Type
WA60P48F1	\$456.00	WA60P48F1G	\$456.00	48.00 x 44.00 [1219 x 1118]	Full
WA60P48F2	\$254.00	WA60P48F2G	\$254.00	24.88 x 44.00 [632 x 1118]	Half
WA72P48F1	\$515.00	WA72P48F1G	\$515.00	60.00 x 44.00 [1524 x 1118]	Full
WA72P48F2	\$329.00	WA72P48F2G	\$329.00	30.88 x 44.00 [784 x 1118]	Half
WA72P60F1	\$597.00	WA72P60F1G	\$597.00	60.00 x 56.00 [1524 x 1422]	Full
WA72P60F2	\$371.00	WA72P60F2G	\$371.00	30.88 x 56.00 [784 x 1422]	Half
WA72P72F1	\$679.00	-	-	68.00 x 68.00 [1727 x 1727]	Full
WA72P72F2	\$413.00	WA72P72F2G	\$413.00	30.88 x 68.88 [784 x 1727]	Half
WA90P48F1	\$606.00	WA90P48F1G	\$606.00	78.00 x 44.00 [1981 x 1118]	Full
WA90P48F2	\$375.00	WA90P48F2G	\$375.00	39.88 x 44.00 [1013 x 1118]	Half
WA90P72F1	\$818.00	-	-	78.00 x 68.00 [1981 x 1727]	Full
WA90P72F2	\$483.00	WA90P72F2G	\$483.00	39.88 x 68.00 [1013 x 1727]	Half

Notes: Dimensions in inches [millimeters].
Suffix F1 = full panel, F2 = half panel

Dimensions


in [mm]



IMPORTANT NOTE: CENTER PANEL SUPPORT IS SUPPLIED WITH A REGULAR TWO-DOOR ENCLOSURE PANEL. THIS SUPPORT IS USED ONLY AS A BRACE. IT IS NOT INTENDED TO BE USED AS A SUPPORT FOR SINGLE-DOOR SUBPANELS, RELAY RACKS, ETC. USE WA_FSCPS PANEL SUPPORTS FOR THIS PURPOSE.

See our website: www.AutomationDirect.com for complete engineering drawings.

WA-SMP Series Side-Mount Panels for Freestanding Enclosures



Description

- Panels for freestanding NEMA 4 and freestanding NEMA 12 enclosures
- Panels are fabricated from 12 gauge steel
- They provide extra mounting space on the sides of the enclosure
- Mounting hardware is furnished with each panel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Panels attach securely to mounting channels

Enclosure Shipping Schedule

1 - 7 days	1 -10 days
------------	------------


Color indicates shipping lead time in business days.

Painted Steel	Price	Galvanized	Price	Panel Size AxB
WA60SMP14	\$133.00	WA60SMP14G	\$133.00	48.00 x 14.00 [1219 x 356]
WA72SMP14	\$151.00	WA72SMP14G	\$151.00	60.00 x 14.00 [1524 x 356]
WA72SMP20	\$185.00	WA72SMP20G	\$185.00	60.00 x 20.00 [1524 x 508]
WA90SMP14	\$217.00	WA90SMP14G	\$217.00	78.00 x 14.00 [1981 x 356]
WA90SMP20	\$227.00	WA90SMP20G	\$227.00	78.00 x 20.00 [1981 x 508]

Note: Dimensions in inches (millimeters)


Dimensions

in [mm]



See our website: www.AutomationDirect.com for complete engineering drawings.

WASP-F3/F4 Series Accessory Swing-Out Panels For Freestanding Enclosures



Description

- Panels for freestanding NEMA 12 enclosures and freestanding NEMA 4 enclosures
- Full-height and half-height swing-out panels are available
- Half-height panels can be located in the upper or lower portion of the enclosure
- Mounting can be on either side of the enclosure
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- May be used in two-door enclosures along with other freestanding accessories
- Fabricated from 12 gauge steel
- Mounting hardware is furnished with each panel



Enclosure Shipping Schedule


1 - 7 days	1 -10 days
Color indicates shipping lead time in business days.	

Painted Steel	Price	Galvanized	Price	Panel Size AxB	Subpanel Type
WA60SP24F3	\$355.00	WA60SP24F3G	\$355.00	48.00 x 19.00 [1219 x 483]	Full
WA60SP24F4	\$250.00	WA60SP24F4G	\$250.00	24.88 x 19.00 [632 x 483]	Half
WA60SP36F3	\$437.00	WA60SP36F3G	\$437.00	48.00 x 31.00 [1219 x 787]	Full
WA60SP36F4	\$290.00	WA60SP36F4G	\$290.00	24.88 x 31.00 [632 x 787]	Half
WA72SP24F3	\$430.00	WA72SP24F3G	\$430.00	60.00 x 19.00 [1524 x 483]	Full
WA72SP24F4	\$292.00	WA72SP24F4G	\$292.00	30.88 x 19.00 [784 x 483]	Half
WA72SP30F3	\$499.00	WA72SP30F3G	\$499.00	60.00 x 25.00 [1524 x 635]	Full
WA72SP30F4	\$330.00	WA72SP30F4G	\$330.00	30.88 x 25.00 [784 x 635]	Half
WA72SP36F3	\$568.00	WA72SP36F3G	\$568.00	60.00 x 31.00 [1524 x 787]	Full
WA72SP36F4	\$368.00	WA72SP36F4G	\$368.00	30.88 x 31.00 [784 x 787]	Half
WA90SP36F3	\$674.00	WA90SP36F3G	\$674.00	78.00 x 31.00 [1981 x 787]	Full
WA90SP36F4	\$425.00	WA90SP36F4G	\$425.00	39.88 x 31.00 [1013 x 787]	Half

Notes: Dimensions in inches [millimeters].
 Note 1: If used in a two-door enclosure, a center panel support must be ordered.
 Note 2: Suffix F3 =full panel, F4 =half panel

Dimensions

in [mm]



See our website: www.AutomationDirect.com for complete engineering drawings.