

# OKK Series Base and Roof Sets



## Application

Each set provides the base and roof for one OKK Series enclosure.

Requires the following compatible components for a completed OKK Series enclosure:

- Vertical frame rail set
- Exterior side panels
- Door
- Exterior rear panel or additional door
- Subpanel

Easily find compatible OKK Series parts for your enclosure using the link button or QR code below:

## Configuration Tool



## Features

- Bases have removable flanges for easy cable and wire entry.
- Roof bolts can be replaced with eyebolts (GLF812-K4 for enclosure lifting).
- Base is compatible with [OKK Series Plinth Kits](#) for cable ingress and management.
- Vertical rails are connected with included hardware.

*\*Assembly requires a T30 bit.*

## Material and Finish

- Sendzimir galvanized frame rails
- Zamak corner joints
- Exterior portions are RAL7035 light gray textured powder coat finish

## Listings

- Fully-assembled OKK Series Enclosures are rated as follows:
  - UL 508a Type 12 [UL File E503249]
  - CSA Type 12 [CSA File 115232]
- Complies with
  - NEMA Type 12
  - IEC EN60529 IP55



Base and Roof Sets			
Part Number	Price	Enclosure Size WxD	Drawing Link
<a href="#">OKKTB6040</a>	\$278.00	600 x 400 [23.62 x 15.75]	<a href="#">PDF</a>
<a href="#">OKKTB6080</a>	\$364.00	600 x 600 [23.62 x 23.62]	<a href="#">PDF</a>
<a href="#">OKKTB6060</a>	\$469.00	600 x 800 [23.62 x 31.50]	<a href="#">PDF</a>
<a href="#">OKKTB8040</a>	\$325.00	800 x 400 [31.50 x 15.75]	<a href="#">PDF</a>
<a href="#">OKKTB8060</a>	\$367.00	800 x 600 [31.50 x 23.62]	<a href="#">PDF</a>
<a href="#">OKKTB8080</a>	\$478.00	800 x 800 [31.50 x 31.50]	<a href="#">PDF</a>
<a href="#">OKKTB1040</a>	\$346.00	1000 x 400 [39.37 x 15.75]	<a href="#">PDF</a>
<a href="#">OKKTB1060</a>	\$398.00	1000 x 600 [39.37 x 23.62]	<a href="#">PDF</a>
<a href="#">OKKTB1080</a>	\$524.00	1000 x 800 [39.37 x 31.50]	<a href="#">PDF</a>
<a href="#">OKKTB1240</a>	\$492.00	1200 x 400 [47.24 x 15.75]	<a href="#">PDF</a>
<a href="#">OKKTB1260</a>	\$544.00	1200 x 600 [47.24 x 23.62]	<a href="#">PDF</a>
<a href="#">OKKTB1280</a>	\$700.00	1200 x 800 [47.24 x 31.50]	<a href="#">PDF</a>

Note: Dimensions in millimeters [inches].