

# Enclosure Subpanels



## Subpanels for Ultimate Series Wall-Mount Enclosures

### Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

### Subpanels for Ultimate Series Wall-Mount Enclosures

Painted Steel	Price	Galvanized	Price	304 Stainless Steel	Price	Nominal Enclosure Size HxW*	Subpanel Size HxW
<a href="#">NP1212C</a>	\$13.75	<a href="#">NP1212CG</a>	\$11.50	—	—	12 x 12	10.20 x 10.20 [259 x 259]
<a href="#">NP1612C</a>	\$14.75	<a href="#">NP1612CG</a>	\$14.75	<a href="#">NP1612SSC</a>	\$76.00	16 x 12	14.20 x 10.20 [361 x 259]
<a href="#">NP1616C</a>	\$35.50	<a href="#">NP1616CG</a>	\$35.50	<a href="#">NP1616SSC</a>	\$93.00	16 x 16	14.20 x 14.20 [361 x 361]
<a href="#">NP2016C</a>	\$42.50	<a href="#">NP2016CG</a>	\$42.50	<a href="#">NP2016SSC</a>	\$112.00	16 x 20 20 x 16	18.20 x 14.20 [462 x 361]
<a href="#">NP2020C</a>	\$51.00	<a href="#">NP2020CG</a>	\$51.00	<a href="#">NP2020SSC</a>	\$145.00	20 x 20	18.20 x 18.20 [462 x 462]
<a href="#">NP2416C</a>	\$49.00	<a href="#">NP2416CG</a>	\$49.00	<a href="#">NP2416SSC</a>	\$139.00	24 x 16	22.20 x 14.20 [564 x 361]
<a href="#">NP2420C</a>	\$49.00	<a href="#">NP2420CG</a>	\$66.00	<a href="#">NP2420SSC</a>	\$176.00	24 x 20	22.20 x 18.20 [564 x 462]
<a href="#">NP2424C</a>	\$76.00	<a href="#">NP2424CG</a>	\$76.00	<a href="#">NP2424SSC</a>	\$205.00	24 x 24	22.20 x 22.20 [564 x 564]
<a href="#">NP3020C</a>	\$79.00	<a href="#">NP3020CG</a>	\$79.00	—	—	30 x 20	28.20 x 18.20 [716 x 462]
<a href="#">NP3024C</a>	\$92.00	<a href="#">NP3024CG</a>	\$79.00	<a href="#">NP3024SSC</a>	\$269.00	30 x 24	28.20 x 22.20 [716 x 564]
<a href="#">NP3030C</a>	\$129.00	<a href="#">NP3030CG</a>	\$129.00	<a href="#">NP3030SSC</a>	\$367.00	30 x 30	28.20 x 28.20 [716 x 716]
<a href="#">NP3624C</a>	\$110.00	<a href="#">NP3624CG</a>	\$110.00	<a href="#">NP3624SSC</a>	\$313.00	24 x 36 36 x 24	34.20 x 22.20 [869 x 564]
<a href="#">NP3630C</a>	\$147.00	<a href="#">NP3630CG</a>	\$147.00	<a href="#">NP3630SSC</a>	\$389.00	36 x 30	34.20 x 28.20 [869 x 716]
<a href="#">NP3636C</a>	\$172.00	<a href="#">NP3636CG</a>	\$172.00	<a href="#">NP3636SSC</a>	\$470.00	36 x 36	34.20 x 34.20 [869 x 869]
<a href="#">NP4224C</a>	\$214.00	—	—	—	—	24 x 42	40.20 x 22.20 [1021 x 564]
<a href="#">NP4024C</a>	\$132.00	<a href="#">NP4024CG</a>	\$132.00	—	—	40 x 24	38.20 x 22.20 [970 x 564]
<a href="#">NP4242C</a>	\$367.00	—	—	—	—	42 x 42	40.20 x 40.20 [1021 x 1021]
<a href="#">NP4230C</a>	\$198.00	—	—	—	—	30 x 42 42 x 32	40.20 x 28.20 [1021 x 716]
<a href="#">NP4236C</a>	\$198.00	<a href="#">NP4236CG</a>	\$198.00	<a href="#">NP4236SSC</a>	\$593.00	36 x 42 42 x 36	40.20 x 34.20 [1021 x 869]
<a href="#">NP4824C</a>	\$143.00	<a href="#">NP4824CG</a>	\$143.00	—	—	24 x 48 48 x 24	46.20 x 22.20 [1173 x 564]
<a href="#">NP4830C</a>	\$295.00	—	—	—	—	30 x 48	46.20 x 28.20 [1173 x 716]
<a href="#">NP4842C</a>	\$493.00	—	—	—	—	42 x 48	46.20 x 40.20 [1173 x 1021]
<a href="#">NP4836C</a>	\$223.00	<a href="#">NP4836CG</a>	\$223.00	<a href="#">NP4836SSC</a>	\$594.00	36 x 48 48 x 36	46.20 x 34.20 [1173 x 869]
<a href="#">NP4848C</a>	\$549.00	—	—	—	—	48 x 48	46.20 x 46.20 [1173 x 1173]
<a href="#">NP6030C</a>	\$391.00	—	—	—	—	30 x 60	58.20 x 28.20 [1478 x 716]
<a href="#">NP6036C</a>	\$275.00	<a href="#">NP6036CG</a>	\$275.00	<a href="#">NP6036SSC</a>	\$848.00	36 x 30 60 x 36	58.20 x 34.20 [1478 x 869]
<a href="#">NP6042C</a>	\$551.00	—	—	—	—	42 x 60	58.20 x 40.20 [1478 x 1021]

Notes: Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawing.

Disconnect enclosures will be up to 2 inches [51mm] wider than width dimensions in this table.