

# Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Freestanding



## Applications

Designed to house electrical and electronic controls, instruments and components. Provides a degree of protection from dust, oil and water. For outdoor application a drip shield is recommended.

## Construction

- 12-gauge stainless steel Type 304 and 316/316L
- Seams continuously welded and ground smooth
- Flange trough collar around all sides of door opening Stainless steel concealed hinges
- Black zinc diecast keylocking/padlocking handle
- Removable and interchangeable doors
- Black, 1/4-turn latches, as required
- Removable print pocket
- Lifting eyes for easy handling
- Ground studs on door and body
- Mounting channels are welded horizontally on sides of interior body at top, bottom and middle for mounting optional panels or rack mounting angles.
- No door stiffeners are required.
- Provisions for light kit
- Poured in place oil- and water-resistant gasket

## Finish

- #4 brushed finish on all exterior surfaces
- Optional subpanels are powder coated white.

## Listings

- NEMA Type 3R, 4, 4X, 12, and 13
- cULus Listed Type 3R, 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



### Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

## Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Freestanding

304 Stainless Steel	Price	316L Stainless Steel	Price	Size HxWxD	Drawing Link	Subpanel	Price
<a href="#">SCE-60EL2418SSFS</a>	\$3,406.00	<a href="#">SCE-60EL2418SS6FS</a>	\$4,070.00	60.00 x 24.00 x 19.05 [1524 x 610 x 484]	<a href="#">PDF</a>	<a href="#">SCE-60P24F1</a>	\$241.00
<a href="#">SCE-72EL2418SSFS</a>	\$3,643.00	<a href="#">SCE-60EL3624SS6FS</a>	\$4,911.00	72.00 x 24.00 x 19.05 [1829 x 610 x 484]	<a href="#">PDF</a>	<a href="#">SCE-72P24F1</a>	\$272.00
<a href="#">SCE-72EL3018SSFS</a>	\$3,928.00	<a href="#">SCE-72EL2418SS6FS</a>	\$4,315.00	72.00 x 30.00 x 19.05 [1829 x 762 x 484]	<a href="#">PDF</a>	<a href="#">SCE-72P30F1</a>	\$317.00
<a href="#">SCE-72EL2424SSFS</a>	\$3,944.00	<a href="#">SCE-72EL2424SS6FS</a>	\$4,668.00	72.00 x 24.00 x 25.05 [1829 x 610 x 636]	<a href="#">PDF</a>	<a href="#">SCE-72P24F1</a>	\$272.00
<a href="#">SCE-60EL3624SSFS</a>	\$4,149.00	<a href="#">SCE-72EL3018SS6FS</a>	\$4,649.00	60.00 x 36.00 x 25.05 [1524 x 914 x 636]	<a href="#">PDF</a>	<a href="#">SCE-60P36F1</a>	\$314.00
<a href="#">SCE-90EL2420SSFS</a>	\$4,487.00	<a href="#">SCE-72EL3024SS6FS</a>	\$5,162.00	90.00 x 24.00 x 21.05 [2286 x 610 x 535]	<a href="#">PDF</a>	<a href="#">SCE-90P24F1</a>	\$317.00
<a href="#">SCE-72EL3618SSFS</a>	\$4,341.00	<a href="#">SCE-72EL3618SS6FS</a>	\$5,139.00	72.00 x 36.00 x 19.05 [1829 x 914 x 484]	<a href="#">PDF</a>	<a href="#">SCE-72P36F1</a>	\$359.00
<a href="#">SCE-72EL3024SSFS</a>	\$4,361.00	<a href="#">SCE-72EL3624SS6FS</a>	\$5,761.00	72.00 x 30.00 x 25.05 [1829 x 762 x 636]	<a href="#">PDF</a>	<a href="#">SCE-72P30F1</a>	\$317.00
<a href="#">SCE-72EL3624SSFS</a>	\$4,868.00	<a href="#">SCE-72EL3630SS6FS</a>	\$6,361.00	72.00 x 36.00 x 25.05 [1829 x 914 x 636]	<a href="#">PDF</a>	<a href="#">SCE-72P36F1</a>	\$359.00
<a href="#">SCE-72EL3630SSFS</a>	\$5,374.00	<a href="#">SCE-72EL3636SS6FS</a>	\$6,972.00	72.00 x 36.00 x 31.05 [1829 x 914 x 789]	<a href="#">PDF</a>	<a href="#">SCE-72P36F1</a>	\$359.00
<a href="#">SCE-90EL3620SSFS</a>	\$5,532.00	<a href="#">SCE-90EL2420SS6FS</a>	\$5,282.00	90.00 x 36.00 x 21.05 [2286 x 914 x 535]	<a href="#">PDF</a>	<a href="#">SCE-90P36F1</a>	\$431.00
<a href="#">SCE-90EL3624SSFS</a>	\$5,987.00	<a href="#">SCE-90EL3620SS6FS</a>	\$6,520.00	90.00 x 36.00 x 25.05 [2286 x 914 x 636]	<a href="#">PDF</a>	<a href="#">SCE-90P36F1</a>	\$431.00
<a href="#">SCE-72EL3636SSFS</a>	\$5,890.00	<a href="#">SCE-90EL3624SS6FS</a>	\$7,060.00	72.00 x 36.00 x 37.05 [1829 x 914 x 941]	<a href="#">PDF</a>	<a href="#">SCE-72P36F1</a>	\$359.00
<a href="#">SCE-90EL3636SSFS</a>	\$6,979.00	<a href="#">SCE-90EL3636SS6FS</a>	\$8,231.00	90.00 x 36.00 x 37.05 [2286 x 914 x 941]	<a href="#">PDF</a>	<a href="#">SCE-90P36F1</a>	\$431.00

Note: Dimensions in inches [millimeters].

# Enviroline Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Single-Door Freestanding



## Dimensions

