

NEMA 4,12, and 13 Pushbutton Console



Applications

Designed to offer protection for all standard brands of oil-tight pushbuttons, switches, and pilot lights where slanted surfaces are desired. It offers protection from dust, dirt, oil and water.

Construction

- 16-gauge carbon steel
- Continuously-welded seams
- Captivated cover screws thread into sealed wells.
- 4-way pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights
- Hole diameter is 1.20in [30.5mm] or 0.87in [22.5mm]
- Fully-removable cover
- Poured-in-place oil- and water-resistant gasket
- Mounting feet included
- Provisions for subpanel

Finish

- ANSI 61 gray powder coated inside and out
- Optional subpanels are powder coated white.

Listings

- NEMA Type 4, 12, and 13
- cULus Listed Type 4 and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

| | |
|----------|-------------|
| Same day | 1 - 15 days |
|----------|-------------|

Color indicates shipping lead time in business days.

NEMA 4, 12, and 13 Pushbutton Console

| 22mm | 30mm | Price | Size HxWxD | Holes | Drawing Link | Optional Subpanel | Price |
|-----------------------------|----------------------------|----------|--|-------|---------------------|---------------------------|---------|
| SCE-1PBAI | SCE-1PBA | \$86.00 | 4.08 x 3.56 x 5.08 [104 x 90 x 129] | 1 | PDF | — | — |
| SCE-2PBAI | SCE-2PBA | \$99.00 | 4.08 x 5.81 x 5.08 [104 x 148 x 129] | 2 | PDF | — | — |
| SCE-3PBAI | SCE-3PBA | \$112.00 | 4.08 x 8.06 x 5.08 [104 x 205 x 129] | 3 | PDF | — | — |
| SCE-4PBAI | SCE-4PBA | \$127.00 | 4.08 x 10.31 x 5.08 [104 x 262 x 129] | 4 | PDF | — | — |
| SCE-4SPBAI | SCE-4SPBA | \$142.00 | 7.32 x 6.56 x 6.95 [186 x 167 x 177] | 4 | PDF | SCE-6P6 | \$5.50 |
| SCE-6PBAI | SCE-6PBA | \$165.00 | 7.32 x 8.81 x 6.95 [186 x 224 x 177] | 6 | PDF | SCE-8P6 | \$6.50 |
| SCE-8PBAI | SCE-8PBA | \$187.00 | 7.32 x 11.06 x 6.95 [186 x 281 x 177] | 8 | PDF | SCE-10P6 | \$7.50 |
| SCE-9PBAI | SCE-9PBA | \$208.00 | 7.32 x 13.31 x 6.95 [186 x 338 x 177] | 9 | PDF | SCE-12P6 | \$8.25 |
| SCE-10PBAI | SCE-10PBA | \$195.00 | 9.27 x 8.81 x 8.07 [235 x 224 x 205] | 10 | PDF | SCE-8P8 | \$7.50 |
| SCE-12PBAI | SCE-12PBA | \$226.00 | 7.32 x 15.56 x 6.95 [186 x 395 x 177] | 12 | PDF | SCE-14P6 | \$9.25 |
| SCE-12SPBAI | SCE-12SPBA | \$216.00 | 11.22 x 8.81 x 9.21 [285 x 224 x 234] | 12 | PDF | SCE-10P8 | \$8.75 |
| SCE-16PBAI | SCE-16PBA | \$241.00 | 11.22 x 11.06 x 9.21 [285 x 281 x 234] | 16 | PDF | SCE-10P10 | \$10.50 |

Note: Dimensions in inches [millimeters].

NEMA 4,12, and 13 Pushbutton Console



Dimensions

