

NEMA 4, 12, and 13 Wall-Mount Pushbutton



Applications

Designed to offer protection for oil-tight pushbuttons, switches, and pilot lights from dust, water, dirt and oil.

Construction

- 16-gauge carbon steel
- Continuously-welded seams
- Captivated cover screws thread into sealed wells.
- 4-way pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights.
- Hole diameter is 1.20in [30.5 mm] or 0.87in [22.5 mm]
- Fully-removable cover
- Poured-in-place oil- and water-resistant gasket
- Welded mounting provision top and bottom of back

Finish

- ANSI 61 gray or RAL 1018 yellow powder coated inside and out

Listings

- NEMA Type 4, 12, and 13
- cULus Listed Type 4 and 12 [File E69392]
- IEC 60529 IP66



Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

NEMA 4, 12, and 13 Wall-Mount Pushbutton

| ANSI 61 Gray | | | RAL 1018 Yellow | | Size HxWxD | Holes | Drawing Link |
|---------------------------|---------------------------|----------|---------------------------------|----------|--------------------------------------|-------|---------------------|
| 22mm | 30mm | Price | 30mm | Price | | | |
| SCE-1PBI | SCE-1PB | \$56.00 | SCE-1PB-RAL1018 | \$69.00 | 3.81 x 3.56 x 2.91 [97 x 90 x 74] | 1 | PDF |
| SCE-2PBI | SCE-2PB | \$65.00 | SCE-2PB-RAL1018 | \$79.00 | 6.06 x 3.56 x 2.91 [154 x 90 x 74] | 2 | PDF |
| SCE-3PBI | SCE-3PB | \$73.00 | SCE-3PB-RAL1018 | \$89.00 | 8.31 x 3.56 x 2.91 [211 x 90 x 74] | 3 | PDF |
| SCE-4PBI | SCE-4PB | \$81.00 | SCE-4PB-RAL1018 | \$98.00 | 10.56 x 3.56 x 2.91 [268 x 90 x 74] | 4 | PDF |
| SCE-4SPBI | SCE-4SPB | \$90.00 | — | — | 7.56 x 6.56 x 3.16 [192 x 167 x 80] | 4 | PDF |
| SCE-5PBI | SCE-5PB | \$89.00 | SCE-5PB-RAL1018 | \$108.00 | 12.81 x 3.56 x 2.91 [325 x 90 x 74] | 5 | PDF |
| SCE-6PBI | SCE-6PB | \$103.00 | — | — | 9.81 x 6.56 x 3.16 [249 x 167 x 80] | 6 | PDF |
| SCE-6PBVL | SCE-6PBVL | \$97.00 | — | — | 15.06 x 3.56 x 2.91 [383 x 90 x 74] | 6 | PDF |
| SCE-8PBI | SCE-8PB | \$116.00 | — | — | 20.56 x 3.56 x 2.91 [522 x 90 x 74] | 8 | PDF |
| SCE-9PBI | SCE-9PB | \$119.00 | — | — | 9.81 x 8.81 x 3.16 [249 x 224 x 80] | 9 | PDF |
| SCE-12PBI | SCE-12PB | \$134.00 | — | — | 12.06 x 8.81 x 3.16 [306 x 224 x 80] | 12 | PDF |

Note: Dimensions in inches [millimeters].

NEMA 4, 12, and 13 Wall-Mount Pushbutton



Dimensions

