

# NEMA 4, 12, and 13 Wall-Mount Pushbutton



## Applications

Designed to offer protection for oil-tight pushbuttons, switches, and pilot lights from dust, water, dirt and oil.

## Construction

- 16 gauge carbon steel.
- Continuously-welded seams.
- Captivated cover screws thread into sealed wells.
- 4-way pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights.
- Hole diameter is 1.20in [30.5 mm] or 0.87in [22.5 mm].
- Fully-removable cover.
- Poured-in-place oil- and water-resistant gasket.
- Welded mounting provision top and bottom of back.

## Finish

- ANSI 61 gray powder coated inside and out.

## Listings

- NEMA Type 4, 12, and 13
- cULus Listed Type 4 and 12 [File E69392]
- IEC 60529 IP66



### Shipping Schedule

Same day 1 - 15 days

Color indicates shipping lead time in business days.

NEMA 4, 12, and 13 Wall-Mount Pushbutton						
22mm	30mm	Price	Size HxWxD	Holes	Drawing Link	
<b>SCE-1PBI</b>	<b>SCE-1PB</b>	\$44.00	3.81 x 3.56 x 2.91 [97 x 90 x 74]	1	<a href="#">PDF</a>	
<b>SCE-2PBI</b>	<b>SCE-2PB</b>	\$50.00	6.06 x 3.56 x 2.91 [154 x 90 x 74]	2	<a href="#">PDF</a>	
<b>SCE-3PBI</b>	<b>SCE-3PB</b>	\$56.00	8.31 x 3.56 x 2.91 [211 x 90 x 74]	3	<a href="#">PDF</a>	
<b>SCE-4PBI</b>	<b>SCE-4PB</b>	\$63.00	10.56 x 3.56 x 2.91 [268 x 90 x 74]	4	<a href="#">PDF</a>	
<b>SCE-4SPBI</b>	<b>SCE-4SPB</b>	\$70.00	7.56 x 6.56 x 3.16 [192 x 167 x 80]	4	<a href="#">PDF</a>	
<b>SCE-5PBI</b>	<b>SCE-5PB</b>	\$69.00	12.81 x 3.56 x 2.91 [325 x 90 x 74]	5	<a href="#">PDF</a>	
<b>SCE-6PBI</b>	<b>SCE-6PB</b>	\$80.00	9.81 x 6.56 x 3.16 [249 x 167 x 80]	6	<a href="#">PDF</a>	
<b>SCE-6PBVLI</b>	<b>SCE-6PBVL</b>	\$75.00	15.06 x 3.56 x 2.91 [383 x 90 x 74]	6	<a href="#">PDF</a>	
<b>SCE-8PBI</b>	<b>SCE-8PB</b>	\$90.00	20.56 x 3.56 x 2.91 [522 x 90 x 74]	8	<a href="#">PDF</a>	
<b>SCE-9PBI</b>	<b>SCE-9PB</b>	\$93.00	9.81 x 8.81 x 3.16 [249 x 224 x 80]	9	<a href="#">PDF</a>	
<b>SCE-12PBI</b>	<b>SCE-12PB</b>	\$104.00	12.06 x 8.81 x 3.16 [306 x 224 x 80]	12	<a href="#">PDF</a>	

*Note: Dimensions in inches [millimeters]*

# NEMA 4, 12, and 13 Wall-Mount Pushbutton



## Dimensions

