

Enclosure Subpanels

Stainless Steel

Designed to mount in the back of an enclosure.



Your Enclosure Source®



Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

Stainless Steel Subpanels

Part Number	Price	Size HxW	Fits Enclosure(s)	Drawing Link
304 Stainless Steel				
SCE-16P16SS	\$91.00	13.00 x 13.00 [330 x 330]	SCE-16EL16xxxx	PDF
SCE-20P16SS	\$100.00	17.00 x 13.00 [432 x 330]	SCE-16EL20xxxx, SCE-20EL16xxxx, SCE-16H20xxxx and SCE-20H16xxxx	PDF
SCE-20P20SS	\$117.00	17.00 x 17.00 [432 x 432]	SCE-20EL20xxxx, SCE-20XEL21xxxx, SCE-20SA22xxxx and SCE-20H20xxxx	PDF
SCE-24P16SS	\$109.00	21.00 x 13.00 [533 x 330]	SCE-24EL16xxxx and SCE-24H16xxLP	PDF
SCE-24P20SS	\$146.00	21.00 x 17.00 [533 x 432]	SCE-20EL24xxxx, SCE-24EL20xxxx, SCE-24XEL21xxxx, SCE-24SA22xxxx, SCE-20H24xxxx and SCE-24H20xxxx	PDF
SCE-24P24SS	\$176.00	21.00 x 21.00 [533 x 533]	SCE-24EL24xxxx, SCE-24XEL25xxxx, SCE-24SA26xxxx, SCE-24HS2508xxxx, SCE29VR24xx, SCE-24R24xxxx and SCE-24H24xxxx	PDF
SCE-30P24SS	\$209.00	27.00 x 21.00 [686 x 533]	SCE-402516Sxxxx, SCE-24EL30xxxx, SCE-30EL24xxxx, SCE-30XEL25xxxx, SCE-30SA26xxxx, SCE-30HS2508xxxx, SCE-35VR2412, SCE-30R24xxxx, SCE-24H30xxxx and SCE-30H24xxxx	PDF
SCE-30P30SS	\$276.00	27.00 x 27.00 [686 x 686]	SCE-30EL30xxxx and SCE-30H30xxxx	PDF
SCE-36P16SS	\$176.00	33.00 x 13.00 [838 x 330]	SCE-36H1606LP	PDF
SCE-36P24SS	\$251.00	33.00 x 21.00 [838 x 533]	SCE-36EL24xxxx, SCE-36XEL25xxxx, SCE-36SA26xxxx, SCE-36HS2508xxxx, SCE41VR2412, SCE-36R24xxLP and SCE-36H24xxxx	PDF
SCE-36P30SS	\$334.00	33.00 x 27.00 [838 x 686]	SCE-403716xxxx, SCE-30EL36xxxx, SCE-36EL30xxxx, SCE-36XEL31xxxx, SCE-36SA32xxLPPL, SCE-36HS31xxxx, SCE-36R30xxLP, SCE-30H36xxxx and SCE-36H30xxxx	PDF
SCE-36P36SS	\$393.00	33.00 x 33.00 [838 x 838]	SCE-463719xxxx, SCE-36EL36xxxx and SCE-36H36xxxx	PDF
SCE-42P30SS	\$384.00	39.00 x 27.00 [991 x 686]	SCE-42EL30xxxx, SCE-30EL4210xxWFLP, SCE-42XEL31xxxx, SCE-42SA32xxLPPL, SCE-42HS3112xxxx, SCE-42R30xxLP and SCE-42H30xxxx	PDF
SCE-42P36SS	\$451.00	39.00 x 33.00 [991 x 838]	SCE-42EL36xxxx, SCE-36EL4216xxWFLP, SCE-364216WFLP, SCE-42XEL37xxxx, SCE-42SA38xxLPPL, SCE-42HS3712xxxx and SCE-42H36xxxx	PDF
SCE-48P24SS	\$326.00	45.00 x 21.00 [1143 x 533]	SCE-48EL24xxxx, SCE-2448xxWFLP, SCE-24EL4810xxWFLP, SCE-48SA2610LPPL and SCE-48H2408LP	PDF
SCE-48P36SS	\$510.00	45.00 x 33.00 [1143 x 838]	SCE-464919xxxx, SCE-48EL36xxxx, SCE-36EL48xxxx, SCE-3648xxWFLP, SCE-48XEL37xxxx, SCE-48SA38xxLPPL, SCE-48HS37xxxx, SCE-53VR36xx, SCE-53XVR37xx and SCE-48H36xxxx	PDF
SCE-60P30SS	\$527.00	57.00 x 27.00 [1448 x 686]	SCE-30EL6010xxWFLP and SCE-3060xxWFLP	PDF
SCE-60P36SS	\$627.00	57.00 x 33.00 [1448 x 838]	SCE-60EL36xxxx, SCE-36EL60xxxx, SCE-3660xxWFLP, SCE-60XEL37xxxx, SCE-60SA38xxLPPL, SCE-60HS37xxxx, SCE-65VR36xx, SCE-65XVR37xx and SCE-60H36xxxx	PDF
316/316L Stainless Steel				
SCE-6P4SS	\$10.00	5.00 x 3.00 [127 x 76]	SCE-604ELJxx, SCE-604xCHNFxx and SCE-604xSC	PDF
SCE-6P6SS	\$12.00	5.00 x 5.00 [127 x 127]	SCE-606ELJxx, SCE-606CHNFxx, SCE-606SC and SCE-4SPBAx	PDF
SCE-8P6SS	\$13.75	7.00 x 5.00 [178 x 127]	SCE-806xELJxx, SCE-806xCHNFxx, SCE-806xSC and SCE-6PBAx	PDF
SCE-10P8SS	\$18.75	9.00 x 7.00 [229 x 178]	SCE-1008xELJxx, SCE-1008xCHNFxx, SCE-1008xSC, SCE-6PBHx and SCE-12PBAx	PDF
SCE-10P10SS	\$22.00	9.00 x 9.00 [229 x 229]	SCE-10106ELJxx, SCE-10106CHNF, SCE-1010xSC, SCE-9PBHxxx and SCE-16PBAx	PDF
SCE-12P10SS	\$25.50	11.00 x 9.00 [279 x 229]	SCE-1210xELJxx, SCE-1210xCHNF, SCE-1210xSC and SCE-12PBHx	PDF
SCE-12P12SS	\$30.00	11.00 x 11.00 [279 x 279]	SCE-1212ELJxx, SCE-1212CHNF, SCE-1212SC and SCE-16PBHxxx	PDF
SCE-16P12SS	\$49.00	13.00 x 9.00 [330 x 229]	SCE-16EL120xxxx, SCE-16H12xxxxLP and SCE-16R120xLP	PDF
SCE-14P12SS	\$33.50	13.00 x 11.00 [330 x 279]	SCE-1412xELJxx, SCE-1412xCHNF and SCE-1412SC	PDF
SCE-16P14SS	\$66.00	15.00 x 13.00 [381 x 330]	SCE-1614xELJxxx, SCE-1614xxCHxNFxx, SCE-1614SC and SCE-16C16ELJxx	PDF

Note: Dimensions in inches [millimeters].