



# Vacuum Spring Plungers and Couplers



Part No. 10.01.02.00609  
Model No. FSTE-M5-IG-20



Part No. 10.01.02.00604  
Model No. FSTE-G1/8-AG-50



Part No. 10.01.02.00568  
Model No. FSTE-G1/4-AG-50

Schmalz vacuum spring plungers mount to suction cups and are an excellent option for pick and place operations where the product varies in height. Strokes range from 10 to 50mm.

## Features:

- Barrel mounting jam nuts included
- Cup connections M5, G1/8 and G1/4
- Couplers in G1/8 and G1/4

Vacuum Spring Plungers							
Part No.	Schmalz Model No.	Price	Cup Connection	Vacuum Connection	Stroke	Drawing Link	Manufacturer Specs
10.01.02.00608	FSTE-M5-IG-10	\$50.00	M5 female	M5 female	10mm [0.39 in]	<a href="#">PDF</a>	<a href="#">PDF</a>
10.01.02.00609	FSTE-M5-IG-20	\$51.00			20mm [0.79 in]	<a href="#">PDF</a>	<a href="#">PDF</a>
10.01.02.00603	FSTE-G1/8-AG-25	\$60.00	G1/8 male BSPP	G1/8 female BSPP	25mm [0.98 in]	<a href="#">PDF</a>	<a href="#">PDF</a>
10.01.02.00604	FSTE-G1/8-AG-50	\$62.00			50mm [1.97 in]	<a href="#">PDF</a>	<a href="#">PDF</a>
10.01.02.00567	FSTE-G1/4-AG-25	\$67.00	G1/4 male BSPP		25mm [0.98 in]	<a href="#">PDF</a>	<a href="#">PDF</a>
10.01.02.00568	FSTE-G1/4-AG-50	\$70.00			50mm [1.97 in]	<a href="#">PDF</a>	<a href="#">PDF</a>

For additional details see manufacturer's technical specifications, manuals and inserts (where applicable).



Part No. 10.08.05.00125  
Model No. MUF-S-G1/8-IG-18-SW14-MS-V



Part No. 10.08.05.00126  
Model No. MUF-S-G1/4-IG-26-SW17-MS-V

Vacuum Couplers					
Part No.	Schmalz Model No.	Price	Fitting Connection	Drawing Link	Manufacturer Specs
10.08.05.00125	MUF-S-G1/8-IG-18-SW14-MS-V	\$2.75	G1/8 female BSPP to G1/8 female BSPP	<a href="#">PDF</a>	<a href="#">PDF</a>
10.08.05.00126	MUF-S-G1/4-IG-26-SW17-MS-V	\$3.50	G1/4 female BSPP to G1/4 female BSPP	<a href="#">PDF</a>	<a href="#">PDF</a>

For additional details see manufacturer's technical specifications, manuals and inserts (where applicable).