



# Vacuum Suction Cups with Fittings - Nitrile Rubber

Schmalz nitrile suction cups are an excellent choice for many general purpose vacuum applications. AutomationDirect.com's offering includes bellows cups with G-thread (BSPP) fittings. Sizes range from 14 to 78mm. Replacement cups are available for all sizes.



Part No. [10.01.06.00390](#)  
Model No. FSGA-20-NBR-55-G1/8-AG



Part No. [10.01.06.00083](#)  
Model No. FSGA-53-NBR-55-G1/4-AG

## Features:

- Durable nitrile cup material for a large range of uses
- Single bellows style for uneven surfaces
- Sizes 14 to 78mm diameter
- Fitting sizes G1/8 to G1/4

Vacuum Suction Cups with Fittings - Nitrile Rubber								
Part No.	Schmalz Model No.	Price	Style	Fold(s)	Size	Fitting Connection	Drawing Link	Manufacturer Specs
<a href="#">10.01.06.00381</a>	FSGA-14-NBR-55-G1/8-AG	\$9.00	Bellows	1	14mm	G1/8 male BSPP	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">10.01.06.00390</a>	FSGA-20-NBR-55-G1/8-AG	\$10.50			20mm		<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">10.01.06.00081</a>	FSGA-33-NBR-55-G1/4-AG	\$14.00			33mm	G1/4 male BSPP	<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">10.01.06.00082</a>	FSGA-43-NBR-55-G1/4-AG	\$16.50			43mm		<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">10.01.06.00083</a>	FSGA-53-NBR-55-G1/4-AG	\$18.50			53mm		<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">10.01.06.00685</a>	FSGA 63 NBR-55 G1/4-AG	\$23.50			63mm		<a href="#">PDF</a>	<a href="#">PDF</a>
<a href="#">10.01.06.00084</a>	FSGA-78-NBR-55-G1/4-AG	\$28.00			78mm	<a href="#">PDF</a>	<a href="#">PDF</a>	



Part No. [10.01.06.00130](#)  
Model No. FGA-33-NBR-55-N018



Part No. [10.01.06.00133](#)  
Model No. FGA-78-NBR-55-N019

Replacement Vacuum Suction Cups - Nitrile Rubber						
Part No.	Schmalz Model No.	Price	Style	Fold(s)	Size	Manufacturer Specs
<a href="#">10.01.06.00370</a>	FGA-14-NBR-55-N016	\$5.75	Bellows	1	14mm	<a href="#">PDF</a>
<a href="#">10.01.06.00373</a>	FGA-20-NBR-55-N016	\$7.25			20mm	<a href="#">PDF</a>
<a href="#">10.01.06.00130</a>	FGA-33-NBR-55-N018	\$7.50			33mm	<a href="#">PDF</a>
<a href="#">10.01.06.00131</a>	FGA-43-NBR-55-N018	\$10.50			43mm	<a href="#">PDF</a>
<a href="#">10.01.06.00132</a>	FGA-53-NBR-55-N018	\$13.00			53mm	<a href="#">PDF</a>
<a href="#">10.01.06.00688</a>	FGA-63-NBR-55-N018	\$17.50			63mm	<a href="#">PDF</a>
<a href="#">10.01.06.00133</a>	FGA-78-NBR-55-N019	\$22.50			78mm	<a href="#">PDF</a>

For additional details see manufacturer's technical specifications, manuals and inserts (where applicable).