Subpanels for AttaBox Series Enclosures

Aluminum Subpanels

- Material: 3003-H14 aluminum
- Finish: Mill

Aluminum Subpanels				
Part Number	**Price**	**Subpanel Size HxW**	**Fits Enclosures**	**Drawing Link**
BP66AL	$13.00	4.88 x 4.88 [124 x 124]	AH6*, AHF6*, CL7*, DS6*, DSCC60604HPL, F4PBW, J606*, JW606HPL and RJ606*	PDF
BP86AL	$15.50	6.88 x 4.88 [175 x 124]	AH86*, AHF86*, CL9*, DS806*, F6PBW, J806*, JW806*, RJ806* and RJW806HPL	PDF
BP88AL	$20.50	6.88 x 6.88 [175 x 175]	AH88*, AHF88*, DS808*, DSCC80804HPL, J8088SSH, J808*, J808W and RJ808HPL	PDF
BP108AL	$22.50	8.88 x 6.88 [226 x 175]	AH108*, AHF108*, CL11*, DS10*, DSCC1008HLL, DSW10*, F9PBW, J10*, JW10*, RJ10*, RJW1008HPL and WH-J1008HPL	PDF
BP1010AL	$28.00	8.88 x 8.88 [226 x 226]	AH1010*, AHF1010* and AHWD10106	PDF
BP1210AL	$28.50	10.88 x 8.88 [276 x 226]	AH12*, AHF12*, AHWD12106, CL13*, DS12*, DSCC121006HPL, DSW121006HPL, J1210*, JW12*, RJ12*, RJW1210HPL and WH-J1210HPL	PDF
BP1412AL	$34.50	12.88 x 10.88 [327 x 276]	AH14*, AHF14*, AHWD14126, CL15*, DS1412*, DSCC141206HPL, DSW14*, J14*, JW14*, RJ14*, RJW14* and WH-J1412HPL	PDF
BP1614AL	$45.00	14.88 x 12.88 [378 x 327]	AH16*, AHF16*, AHWD16148, DS1614*, DSCC161408HPL, DSW1614*, J16*, JW16*, RJ16*, RJW16* and WH-J1614HPL	PDF
BP1816AL	$58.00	16.88 x 14.88 [429 x 378]	AH18*, AHF18*, AHWD181610, DS18*, DSW18*, J18*, JW1816*, RJ18*, RJW18* and WH-J1816HPL	PDF
BPJ2016AL	$74.00	18.88 x 14.88 [480 x 378]	AH20*, AHF20*, AHWD20168, DS20*, J20*, JW2016HLL, RJ20* and RJW2016HPL	PDF
BP2424PCAL	$106.00	22.88 x 22.88 [581 x 581]	AH24* and AHWD242410	PDF

Note: Dimensions in inches (millimeters).



BP66AL

Aluminum Swing Panel Kits

- Material: 3003-H14 aluminum
- Finish: Mill
- Includes swing panel, (4) AHSPM brackets and mounting screws

Aluminum Swing Panel Kits				
Part Number	**Price**	**Subpanel Size HxW**	**Fits Enclosures**	**Drawing Link**
AH66SPK	$61.00	5.63 x 5.63 [143 x 143]	AH66* and AHF66*	PDF
AH86SPK	$62.00	7.63 x 5.63 [194 x 143]	AH86* and AHF86*	PDF
AH108SPK	$68.00	9.63 x 7.63 [245 x 194]	AH108* and AHF108*	PDF
AH1010SPK	$98.00	9.63 x 9.63 [245 x 245]	AH1010*, AHF1010* and AHWD10106	PDF
AH1210SPK	$73.00	11.63 x 9.63 [295 x 245]	AH12*, AHF12* and AHWD12106	PDF
AH1412SPK	$79.00	13.63 x 11.63 [346 x 295]	AH14*, AHF14* and AHWD14126	PDF
AH1614SPK	$84.00	15.63 x 13.63 [397 x 346]	AH16*, AHF16* and AHWD16148	PDF
AH1816SPK	$90.00	17.63 x 15.63 [448 x 397]	AH18*, AHF18* and AHWD181610	PDF
AH2016SPK	$140.00	19.63 x 15.63 [499 x 397]	AH20*, AHF20* and AHWD20168	PDF
AH2424SPK	$101.00	23.63 x 23.63 [600 x 600]	AH24* and AHWD242410	PDF

Note: Dimensions in inches (millimeters).
Not compatible with AttaBox SL enclosures



AH66SPK

Subpanels for AttaBox Series Enclosures

Aluminum Side Panels

- Material: 3003-H14 aluminum
- Finish: Mill

Aluminum Subpanels				
Part Number	*Price*	*Subpanel Size HxW*	*Fits Enclosures*	*Drawing Link*
SP6	$62.00	5.00 x 3.00 [127 x 76]	AH6* and AHF6*	PDF
SP8	$63.00	7.00 x 3.00 [178 x 76]	AH8* and AHF8*	PDF
SP10	$66.00	9.00 x 3.50 [229 x 89]	AH1084*, AH1086*, AH1010*, AHF1084*, AHF1086* and AHF1010*	PDF
SP12	$71.00	11.00 x 5.00 [279 x 127]	AH12106* and AHF12106*	PDF
SP14	$72.00	13.00 x 5.00 [330 x 127]	AH14126* and AHF14126*	PDF
SP16	$82.00	15.00 x 7.00 [381 x 178]	AH16148* and AHF16148*	PDF
SP18	$95.00	17.00 x 9.00 [432 x 229]	AH181610* and AHF181610*	PDF
SP20	$97.00	19.00 x 7.00 [483 x 178]	AH20168* and AHF20168*	PDF
SP24	$106.00	23.00 x 9.00 [584 x 229]	AH24*	PDF

Note: Dimensions in inches (millimeters).
Corrosion resistant slot nut fastening hardware kit included



SP8

ABS Plastic Subpanels

- Material: ABS plastic
- Finish: Mill

ABS plastic Subpanels				
Part Number	*Price*	*Subpanel Size HxW*	*Fits Enclosures*	*Drawing Link*
BP66ABS	$17.00	4.75 x 4.75 [121 x 121]	AH6*, AHF6*, CL7*, DS6*, DSCC60604HPL, F4PBW, J606*, JW606HPL and RJ606*	PDF
BP86ABS	$18.00	6.75 x 4.75 [171 x 121]	AH86*, AHF86*, CL9*, DS806*, F6PBW, J806*, JW806*, RJ806* and RJW806HPL	PDF
BP108ABS	$21.50	8.75 x 6.75 [222 x 171]	AH108*, AHF108*, CL11*, DS10*, DSCC1008HLL, DSW10*, F9PBW, J10*, JW10*, RJ10*, RJW1008HPL and WH-J1008HPL	PDF
BP1010ABS	$23.50	8.75 x 8.75 [222 x 222]	AH1010*, AHF1010* and AHWD10106	PDF
BP1210ABS	$25.50	10.75 x 8.75 [273 x 222]	AH12*, AHF12*, AHWD12106, CL13*, DS12*, DSCC121006HPL, DSW121006HPL, J1210*, JW12*, RJ12*, RJW1210HPL and WH-J1210HPL	PDF
BP1412ABS	$29.50	12.75 x 10.75 [324 x 273]	AH14*, AHF14*, AHWD14126, CL15*, DS1412*, DSCC141206HPL, DSW14*, J14*, JW14*, RJ14*, RJW14* and WH-J1412HPL	PDF
BP1614ABS	$34.00	14.75 x 12.75 [375 x 324]	AH16*, AHF16*, AHWD16148, DS1614*, DSCC161408HPL, DSW1614*, J16*, JW16*, RJ16*, RJW16* and WH-J1614HPL	PDF
BP1816ABS	$45.50	16.75 x 14.75 [425 x 375]	AH18*, AHF18*, AHWD181610, DS18*, DSW18*, J18*, JW1816*, RJ18*, RJW18* and WH-J1816HPL	PDF
BP2016ABS	$60.00	18.75 x 14.75 [476 x 375]	AH20*, AHF20*, AHWD20168, DS20*, J20*, JW2016HLL, RJ20* and RJW2016HPL	PDF
BP2424ABS	$66.00	22.75 x 22.75 [578 x 578]	AH24* and AHWD242410	PDF

Note: Dimensions in inches (millimeters).



BP108ABS