


# Subpanels for Diamond Shield, J, JW, RJ, RJW, and Classic Series Fiberglass Enclosures

**STAHLIN**  
A ROBROY ENCLOSURES® BRAND



## Carbon steel subpanels

- Material: Carbon steel
- Finish: White polyester powder finish

Part Number	Price	Subpanel Size HxW	Enclosure Nominal Size HxW
<a href="#">BP64CS</a>	\$17.25	4.88 x 2.88 [124 x 73]	6 x 4 [152 x 102]
<a href="#">BP66CS</a>	\$11.25	4.88 x 4.88 [124 x 124]	6 x 6 [152 x 152]
<a href="#">BP86CS</a>	\$13.50	6.75 x 4.88 [171 x 124]	8 x 6 [203 x 152]
<a href="#">BP88CS</a>	\$21.00	6.88 x 6.88 [175 x 175]	8 x 8 [203 x 203]
<a href="#">BP108CS</a>	\$20.50	8.75 x 6.88 [222 x 175]	10 x 8 [254 x 203]
<a href="#">BP1210CS</a>	\$25.00	10.88 x 8.75 [276 x 222]	12 x 10 [305 x 254]
<a href="#">BP1412CS</a>	\$30.00	12.88 x 10.88 [327 x 276]	14 x 12 [356 x 305]
<a href="#">BP1614CS</a>	\$39.00	14.88 x 12.88 [378 x 327]	16 x 14 [406 x 356]
<a href="#">BP1816CS</a>	\$50.50	16.88 x 14.88 [429 x 378]	18 x 16 [457 x 406]
<a href="#">BPJ2016CS</a>	\$64.00	18.88 x 14.88 [480 x 378]	20 x 16 [508 x 406]
<a href="#">BPJ2020CS</a>	\$187.00	18.88 x 18.88 [480 x 480]	20 x 20 [508 x 508]
<a href="#">BPJ2420CS</a>	\$226.00	22.88 x 18.88 [581 x 480]	24 x 20 [610 x 508]
<a href="#">BPJ2424CS</a>	\$277.00	22.88 x 22.88 [581 x 581]	24 x 24 [610 x 610]

Note: Dimensions in inches [millimeters].

## Fiberglass subpanels

- Material: Fiberglass reinforced polyester (FRP)
- Color: Gray

Part Number	Price	Subpanel Size HxW	Enclosure Nominal Size HxW
<a href="#">BP86FG</a>	\$20.25	6.88 x 4.88 [175 x 124]	8 x 6 [203 x 152]
<a href="#">BP108FG</a>	\$27.00	8.88 x 6.88 [226 x 175]	10 x 8 [254 x 203]
<a href="#">BP1210FG</a>	\$34.50	10.88 x 8.88 [276 x 226]	12 x 10 [305 x 254]
<a href="#">BP1412FG</a>	\$43.50	12.88 x 10.88 [327 x 276]	14 x 12 [356 x 305]
<a href="#">BP1614FG</a>	\$54.00	14.88 x 12.88 [378 x 327]	16 x 14 [406 x 356]
<a href="#">BP1816FG</a>	\$59.00	16.88 x 14.88 [429 x 378]	18 x 16 [457 x 406]

Note: Dimensions in inches [millimeters].

# Subpanels for Diamond Shield, J, JW, RJ, RJW, and Classic Series Fiberglass Enclosures



## Aluminum subpanels

- Material: 3003H14 aluminum
- Finish: Mill

Part Number	Price	Subpanel Size HxWxD	Enclosure Nominal Size HxW	Drawing Link
<a href="#">BP64AL</a>	\$11.00	4.88 x 2.88 [124 x 73]	6 x 4 [152 x 102]	<a href="#">PDF</a>
<a href="#">BP66AL</a>	\$11.25	4.88 x 4.88 [124 x 124]	6 x 6 [152 x 152]	<a href="#">PDF</a>
<a href="#">BP86AL</a>	\$13.50	6.88 x 4.88 [175 x 124]	8 x 6 [203 x 152]	<a href="#">PDF</a>
<a href="#">BP108AL</a>	\$20.50	8.88 x 6.88 [226 x 175]	10 x 8 [254 x 203]	<a href="#">PDF</a>
<a href="#">BP1210AL</a>	\$25.00	10.88 x 8.88 [276 x 226]	12 x 10 [305 x 254]	<a href="#">PDF</a>
<a href="#">BP1412AL</a>	\$30.00	12.88 x 10.88 [327 x 276]	14 x 12 [356 x 305]	<a href="#">PDF</a>
<a href="#">BP1614AL</a>	\$39.00	14.88 x 12.88 [378 x 327]	16 x 14 [406 x 356]	<a href="#">PDF</a>
<a href="#">BP1816AL</a>	\$50.50	16.88 x 14.88 [429 x 378]	18 x 16 [457 x 406]	<a href="#">PDF</a>
<a href="#">BPJ2016AL</a>	\$64.00	18.88 x 14.88 [480 x 378]	20 x 16 [508 x 406]	<a href="#">PDF</a>
<a href="#">BPJ2020AL</a>	\$179.00	18.88 x 18.88 [480 x 480]	20 x 20 [508 x 508]	<a href="#">PDF</a>
<a href="#">BPJ2420AL</a>	\$216.00	22.88 x 18.88 [581 x 480]	24 x 20 [610 x 508]	<a href="#">PDF</a>
<a href="#">BPJ2424AL</a>	\$265.00	22.88 x 22.88 [581 x 581]	24 x 24 [610 x 610]	<a href="#">PDF</a>
<a href="#">BPJ3024AL</a>	\$313.00	27.00 x 21.00 [686 x 533]	30 x 24 [762 x 610]	<a href="#">PDF</a>

Note: Dimensions in inches (millimeters).

