

Swivellink Mounting System XS Series (Imperial/English Units)



Swivellink Mounts are a better way to mount vision cameras, lights, and sensors. Because of the flexibility and range of Swivellink's patented design, you can fine-tune each installation to just about any position required. Components are made from aluminum alloy for light weight and structural rigidity. Both Metric and Imperial/English versions are available; however, they are not interchangeable.

This page describes Swivellink's AFSB components, which are blue in color and are in Imperial/English units.

Consider the following when selecting your components:

- Amount of weight the mount will be holding
- The overall length of the mount
- The area you have to work with

Carrying capacity varies with overall length and system configuration. The XS Series can hold up 3lb [1.36 kg] at 1ft [0.3m] with all screws torqued to 50 in•lb [5.65 N•m].



AFSB-1XS

Swivellink Bases (Imperial/English) Selection Guide				
Part Number	Price	Description	Weight (oz [g])	Drawing
AFSB-1XS	\$15.00	Round ball base	0.67 [19.1]	PDF

Recommended Screw Sizes for Attaching to SureFrame (T-Slot Nuts Also Required)											
Part Number	Qty	10 Series		15 Series		30 Series		40 Series		45 Series	
		Screw	Part Number	Screw	Part Number	Screw	Part Number	Screw	Part Number	Screw	Part Number
AFSB-1XS	2	Socket head socket cap screw 10-32, 1/2 in	162995	Button head socket cap screw 10-32, 5/8 in	161047	Socket head cap screw M5-0.8, 12mm	161091	Socket head cap screw M5-0.8, 16mm	Not available from ADC	Socket head cap screw M5-0.8, 16mm	Not available from ADC



AFSB-2XS

Swivellink Knuckle (Imperial/English) Selection Guide				
Part Number	Price	Description	Weight (oz [g])	Drawing
AFSB-2XS	\$31.00	Knuckle	1.46 [41.3]	PDF
AFSB-2-2XS	\$44.00	Standard to XS Series coupler	1.95 [55.3]	

Swivellink Tee (Imperial/English) Selection Guide					
Part Number	Price	Description	Length (in [mm])	Weight (oz [g])	Drawing
AFSB-3XST	\$13.00	Tee link	3 [76.2]	0.77 [21.8]	PDF
AFSB-2XS90	\$32.50	Tee knuckle	NA	1.71 [48.5]	PDF



AFSB-3XST



AFSB-2XS90



AFSB-3-2XS

Swivellink Links (Imperial/English) Selection Guide					
Part Number	Price	Description	Length (in [mm])	Weight (oz [g])	Drawing
AFSB-3-2XS	\$16.00	Ball link	2 [50.8]	0.54 [15.4]	PDF
AFSB-3-4XS	\$23.00		4 [101.6]	0.83 [23.6]	PDF

Swivellink Handle Kit (Imperial/English) Selection Guide				
Part Number	Price	Description	Weight (oz [g])	Drawing
AFSB-CLAMP-HANDLE	\$21.50	Clamp handle kit	1.44 [40.8]	PDF



AFSB-CLAMP-HANDLE