



Ratchets & Sockets



Impact Socket Adapters


Titan impact-rated socket adapters adapt your drive tools to reach and turn fasteners other setups can't. Chrome-vanadium steel construction with a black manganese-phosphate finish stands up to impact-driver duty, and patent-pending stepped adapters combine several drive sizes in one tool.

Features

- Impact-rated for use with impact wrenches and drivers
- Stepped adapters combine 1/4in, 3/8in, and 1/2in drives, with wobble or straight action
- Stubby adapter design reaches fasteners in tight or offset locations
- Locking adapter's sliding collar and ball-detent retention hold sockets securely



Impact Socket Adapters & Extension Bars						
Part Number	Product Image	Type	Drive Size	Pcs.	Set Includes	Price
T49004		3-in-1 stepped socket adapter	1/4in 3/8in	1	TITAN wobble and straight socket adapter, impact rated, 1/4in and 3/8in drive, 2.5in (64mm) overall length. 1/4in drive features wobble or straight action.	\$6.50
T49005		3-in-1 stepped socket adapter	3/8in 1/2in	1	TITAN wobble and straight socket adapter, impact rated, 3/8in and 1/2in drive, 3.8in (97mm) overall length. 3/8in drive features wobble or straight action.	\$7.50
T12061		Stubby socket adapter set	1/4in 3/8in 1/2in	3	(3) 1/4in hex shank stubby adapters: 1/4in, 3/8in and 1/2in	\$5.25
T12082		Socket adapter set	1/4in 3/8in 1/2in	3	(3) 1/4in hex shank socket adapter: 1/4in, 3/8in, and 1/2in	\$7.00
T15210		Locking socket adapter set	1/4in 3/8in 1/2in	3	(3) 1/4in hex shank locking socket adapter: 1/4in, 3/8in, and 1/2in	\$23.00





Ratchets & Sockets



Impact Socket Adapters & Extensions

Titan impact-rated socket adapters and extension bars adapt and extend your drive tools to reach and turn fasteners other setups can't. Chrome-vanadium steel construction with a black manganese-phosphate finish resists impact and corrosion, in stubby, wobble, and long-reach adapter styles plus a 9-piece extension bar set.

Features

- Impact-rated for use with impact wrenches and drivers
- Stubby-and-wobble and long-reach socket adapter sets extend reach in tight or offset locations
- Magnetic bit holder adapts hex-shank driver bits for square-drive impact tools
- Extension bars add reach, with ball-detent retention and a reusable storage tray



Impact Socket Adapters & Extension Bars						
Part Number	Product Image	Type	Drive Size	Pcs.	Set Includes	Price
T12002		Impact driver bit and socket adapter set	1/4in 3/8in 1/2in	4	(3) 1/4in hex shank socket adapter: 1/4in, 3/8in, and 1/2in; (1) 1/4 in. hex shank magnetic bit holder	\$8.00
T12001		Stubby and wobble socket adapter set	1/4in 3/8in 1/2in	6	(3) 1/4in hex shank stubby adapter: 1/4in, 3/8in and 1/2in; (3) 1/4in hex shank wobble adapters: 1/4in, 3/8in and 1/2in	\$11.00
T12087		Socket adapter set	1/4in 3/8in 1/2in	6	(2) 1/4in square drive socket adapter: 2.5in and 6in length; (2) 3/8in square drive socket adapter: 2.5in and 6in; (2) 1/2in square drive socket adapter: 2.75in and 6in	\$18.50
T40109		Assorted Impact extension bar set	1/4in 3/8in 1/2in	9	(3) 1/4in square drive extension bar: 2in, 4in and 6in length; (2) 3/8in square drive extension bar: 3in, 5in and 10in; (2) 1/2in square drive extension bar: 1.75in, 3in and 6in, reusable storage tray	\$49.50

Impact Socket Adapter/Extension Set

Long Lasting Durable Construction

Detent ball for secure socket retention

Rust and corrosion resistant finish

T12087

Durable chrome vanadium steel

9 pc. Assorted Impact Extension Bar Set

Chrome Molybdenum Construction For Strength & Durability

Detent balls for secure retention

Rust and corrosion resistant finish

Size markings for easy identification

Through-holes for use with locking drive tang

T40109