

# IP69K Sanitary Pushbutton



## Finish

- Cover and enclosure are natural stainless steel with a smooth #4 dairy finish.

## Listings

- UL 508A Type 3R, 12, 4, 4X [UL File E65324]
- CSA Type 3R, 12, 4, 4X [CSA File LR21001]
- Complies with:
  - NEMA Type 3R, 12, 4, 4X
  - IEC 60529, IP69, IP69K



## Applications

Designed to accept pushbuttons and indicators while protecting against harsh, sanitary environments.

## Construction

- Formed 304 gauge steel.
- Sloped 3° on all four sides to prevent water from resting on top regardless of orientation.
- Smooth continuously welded seams.
- Hex head screw cover can be completely removed for modifications.
- Silicone gasket mounted around entire door edge and hex-head screws allow for efficient cleaning in sanitary environments.
- Gasket can be easily removed and re-installed for cleaning or replacement.
- Additional silicone gaskets can be ordered separately.
- Multiple pushbutton hole configurations with either 22 mm [0.87in] or 30 mm [1.18in] notched pushbutton holes.
- No pre-drilled wall mounting holes allow for flexible mounting alternatives.
- May be installed with standoffs (sold separately) to allow for cleaning of back of enclosure, or welded in place.
- Bonding stud provided on cover and grounding stud installed in enclosure.

IP69K Sanitary Pushbutton								
22 mm	Price	30 mm	Price	Dimensions HxWxD	Drawing Link	# Holes	Replacement Gasket	Price
<a href="#">HYMPB1SS</a>	\$934.00	<a href="#">HYPB1SS</a>	\$934.00	7.94 x 4.98 x 4.53 [202 x 126 x 115]	<a href="#">PDF</a>	1	<a href="#">HYG85</a>	\$130.00
<a href="#">HYMPB2SS</a>	\$982.00	<a href="#">HYPB2SS</a>	\$982.00	7.94 x 4.98 x 4.53 [202 x 126 x 115]	<a href="#">PDF</a>	2	<a href="#">HYG85</a>	\$130.00
<a href="#">HYMPB3SS</a>	\$1,036.00	<a href="#">HYPB3SS</a>	\$1,036.00	9.94 x 4.98 x 4.53 [252 x 126 x 115]	<a href="#">PDF</a>	3	<a href="#">HYG105</a>	\$125.00
<a href="#">HYMPB4VSS</a>	\$1,122.00	<a href="#">HYPB4VSS</a>	\$1,122.00	11.94 x 4.98 x 4.53 [303 x 126 x 115]	<a href="#">PDF</a>	4	<a href="#">HYG125</a>	\$151.00
<a href="#">HYMPB4SS</a>	\$1,175.00	<a href="#">HYPB4SS</a>	\$1,175.00	9.94 x 6.98 x 4.53 [252 x 177 x 115]	<a href="#">PDF</a>	4	<a href="#">HYG107</a>	\$133.00
<a href="#">HYMPB6SS</a>	\$1,368.00	<a href="#">HYPB6SS</a>	\$1,368.00	11.94 x 8.98 x 4.53 [303 x 228 x 115]	<a href="#">PDF</a>	6	<a href="#">HYG129</a>	\$161.00

Note: Dimensions in inches [millimeters].

# IP69K Sanitary Pushbutton



## Dimensions

