

Enclosure Subpanels

N1A Enclosures



Construction


- 14 gauge steel finished in RAL 9003 white powder coat.
- Subpanels and mounting hardware are included with N1A Series enclosures.



Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

Subpanels for N1A Enclosures			
Part Number	Price	Dimensions HxW	For Use With
AP1612	\$11.50	13.00 x 10.50 [330 x 267]	16x12 N1A1612x
AP1616	\$14.75	13.00 x 14.50 [330 x 368]	16x16 N1A16167
AP1620	\$18.25	13.00 x 18.50 [330 x 470]	16x20 N1A16207
AP2016	\$18.25	17.00 x 14.50 [432 x 368]	20x16 N1A2016x
AP2020	\$24.50	17.00 x 18.50 [432 x 470]	20x20 N1A2020x
AP2024	\$28.00	17.00 x 22.50 [432 x 572]	20x24 N1A20249
AP2416	\$22.50	21.00 x 14.50 [533 x 368]	24x16 N1A24167
AP2420	\$28.00	21.00 x 18.50 [533 x 470]	24x20 N1A2420xx
AP2424	\$52.00	21.00 x 22.50 [533 x 572]	24x24 N1A2424xx
AP3020	\$55.00	26.00 x 18.50 [660 x 470]	30x20 N1A3020x
AP3024	\$69.00	26.00 x 22.50 [660 x 572]	30x24 N1A3024xx
AP3030	\$70.00	26.00 x 28.50 [660 x 724]	30x30 N1A30309
AP3624	\$67.00	32.00 x 22.50 [813 x 572]	36x24 N1A3624x
AP3630	\$103.00	32.00 x 28.50 [813 x 724]	36x30 N1A3630xx
AP4224	\$92.00	38.00 x 22.50 [965 x 572]	42x24 N1A42249
AP4230	\$99.00	38.00 x 28.50 [965 x 724]	42x30 N1A423012
AP4236	\$111.00	38.00 x 34.50 [965 x 876]	42x36 N1A423612
AP4836	\$124.00	44.00 x 34.50 [1118 x 876]	48x36 N1A483612

Note: Dimensions in inches [millimeters].



See our website: www.AutomationDirect.com for complete engineering drawings.


Perforated Subpanels

N1A Enclosures



Construction


- Made from 16 gauge steel.
- Accepts self-tapping screws eliminating timely measurement, marking and drilling of component mounting holes.
- 1/8in diameter holes on 1/4in staggered centers.
- ANSI 61 gray powder finish.



Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

Perforated Subpanels for N1A Enclosures			
Part Number	Price	Dimensions HxW	For Use With
AP1612PP	\$11.75	13.00 x 10.50 [330 x 267]	16x12 N1A1612x
AP1616PP	\$15.25	13.00 x 14.50 [330 x 368]	16x16 N1A16167
AP1620PP	\$18.75	13.00 x 18.50 [330 x 470]	16x20 N1A16207
AP2016PP	\$18.75	17.00 x 14.50 [432 x 368]	20x16 N1A2016x
AP2020PP	\$25.50	17.00 x 18.50 [432 x 470]	20x20 N1A2020x
AP2024PP	\$28.50	17.00 x 22.50 [432 x 572]	20x24 N1A20249
AP2416PP	\$23.00	21.00 x 14.50 [533 x 368]	24x16 N1A24167
AP2420PP	\$28.50	21.00 x 18.50 [533 x 470]	24x20 N1A2420xx
AP2424PP	\$54.00	21.00 x 22.50 [533 x 572]	24x24 N1A2424xx
AP3020PP	\$63.00	26.00 x 18.50 [660 x 470]	30x20 N1A3020x
AP3024PP	\$72.00	26.00 x 22.50 [660 x 572]	30x24 N1A3024xx
AP3030PP	\$87.00	26.00 x 28.50 [660 x 724]	30x30 N1A30309
AP3624PP	\$74.00	32.00 x 22.50 [813 x 572]	36x24 N1A3624x
AP3630PP	\$106.00	32.00 x 28.50 [813 x 724]	36x30 N1A3630xx
AP4224PP	\$125.00	38.00 x 22.50 [965 x 572]	42x24 N1A42249

Note: Dimensions in inches (millimeters).



See our website: www.AutomationDirect.com for complete engineering drawings.