

Enclosure Accessories - Hole Seals and Plugs



Hole Seals for Metal Enclosures

Designed to seal extra pushbutton holes, conduit openings, and knockout openings in metal enclosures from dirt, dust, oil and water. Conduit hole sizes are nominal trade sizes, not actual hole sizes. (Example: 1 in. conduit actual diameter = 1.315 in.)



Enclosure Shipping Schedule

Same day

Color indicates shipping lead time in business days.

Steel Hole Seals with ANSI 61 Gray Polyester Powder	Price	Stainless Steel Hole Seals with Grained Finish	Price	Description	Hole Diameter in [mm]	Wt. [lb]
WAS050	\$5.25	WAS050SS	\$15.00	Hubbell-Wiegmann conduit hole seal, 1/2 inch, quick wing nut, oil-resistant gasket	0.87 [22]	0.1
WAS075	\$6.75	WAS075SS	\$19.50	Hubbell-Wiegmann conduit hole seal, 3/4 inch, quick wing nut, oil-resistant gasket	1.14 [29]	
WAS100	\$8.00	WAS100SS	\$24.00	Hubbell-Wiegmann conduit hole seal, 1 inch, quick wing nut, oil-resistant gasket	1.38 [35]	
WAS125	\$10.25	WAS125SS	\$27.50	Hubbell-Wiegmann conduit hole seal, 1.25 inch, quick wing nut, oil-resistant gasket	1.61 [41]	0.2
WAS150	\$11.75	WAS150SS	\$31.00	Hubbell-Wiegmann conduit hole seal, 1.5 inch, quick wing nut, oil-resistant gasket	2.00 [51]	
WAS200	\$13.00	WAS200SS	\$34.25	Hubbell-Wiegmann conduit hole seal, 2 inch, quick wing nut, oil-resistant gasket	2.52 [64]	0.3
WAS250	\$16.75	-	\$11.50	Hubbell-Wiegmann conduit hole seal, 2.5 inch, quick wing nut, oil-resistant gasket	3.00 [76]	0.4
WAS300	\$22.00	-	\$11.50	Hubbell-Wiegmann conduit hole seal, 3 inch, quick wing nut, oil-resistant gasket	3.62 [92]	0.5
WAS350	\$28.50	-	\$11.50	Hubbell-Wiegmann conduit hole seal, 3.5 inch, quick wing nut, oil-resistant gasket	4.13 [105]	
WAS400	\$36.75	-	\$11.50	Hubbell-Wiegmann conduit hole seal, 4 inch, quick wing nut, oil-resistant gasket	4.64 [118]	0.6
WASPB	\$7.25	WASPBSS	\$19.50	Hubbell-Wiegmann hole seal, for 30mm pushbutton cutout, quick wing nut, oil-resistant gasket	1.18 [30]	0.1
WASPBG	\$5.25	WASPBGSS	\$14.00	Hubbell-Wiegmann hole seal, for 22mm pushbutton cutout, quick wing nut, oil-resistant gasket	0.87 [22]	

Note: Dimensions in inches [millimeters]

Enclosure Accessories - Hole Seals and Plugs



Hole Plugs for Non-Metal Enclosures

Designed to seal extra pushbutton holes, conduit openings, and knockout openings in Hubbell-Wiegman fiberglass enclosures from dirt, dust, oil, and water. Conduit hole sizes are nominal trade sizes, not actual hole sizes. (Example: 1 in. conduit actual diameter = 1.315 in.)



Hole Plugs	Price	Description	Nominal Hole Diameter Range in [mm]	Wt. [oz]
HW-FGHP	\$4.75	Hubbell-Wiegmann hole plug, fiber-reinforced plastic (FRP), closed-cell neoprene gasket, for 1/2 to 3/4-inch hole in non-metallic enclosure	0.50 - 0.81 [12.7 - 20.6]	2
HW-FGHP-PB-000	\$11.50	Hubbell-Wiegmann hole plug, fiberglass-reinforced plastic (FRP), closed-cell neoprene gasket. For use with 1/2in conduit holes in non-metallic enclosures.	0.88 [22.4]	2
HW-FGHP-PB-075	\$5.75	Hubbell-Wiegmann hole plug, fiber-reinforced plastic (FRP), closed-cell neoprene gasket, for 1/2- to 3/4-inch conduit holes and 22 or 30mm pushbutton holes in non-metallic enclosure	0.88 - 1.28 [22.4 - 32.5]	2
HW-FGHP-100-125	\$9.50	Hubbell-Wiegmann hole plug, fiber-reinforced plastic (FRP), closed-cell neoprene gasket, for 1 to 1-1/4 inch conduit holes in non-metallic enclosure	1.38 - 1.75 [35.1 - 44.5]	2
HW-FGHP-150-200*	\$11.50	Hubbell-Wiegmann hole plug, fiber-reinforced plastic (FRP), closed-cell neoprene gasket, for 1-1/2 to 2-inch conduit holes in non-metallic enclosure	2.00 - 2.56 [50.1 - 65.0]	2
HW-FGHP-200-275	\$21.50	Hubbell-Wiegmann hole plug, fiberglass-reinforced plastic (FRP), closed-cell neoprene gasket. For use with 2-1/2in conduit holes in non-metallic enclosures.	3.00 [76.2]	2
HW-FGHP-250-350	\$28.50	Hubbell-Wiegmann hole plug, fiberglass-reinforced plastic (FRP), closed-cell neoprene gasket. For use with 3in conduit holes in non-metallic enclosures.	3.62 [92.0]	2
HW-FGHP-300-425	\$37.00	Hubbell-Wiegmann hole plug, fiberglass-reinforced plastic (FRP), closed-cell neoprene gasket. For use with 3-1/2in conduit holes in non-metallic enclosures.	4.12 [104.7]	2
HW-FGHP-350-500	\$47.50	Hubbell-Wiegmann hole plug, fiberglass-reinforced plastic (FRP), closed-cell neoprene gasket. For use with 4in conduit holes in non-metallic enclosures.	4.62 [117.4]	2

**Note: Will maintain NEMA 4X rating.*

Enclosure Shipping Schedule			
Same day	1-7 days	1-10 days	1 - 15 days

Color indicates shipping lead time in business days.