Wera Screwdrivers

Medium Ratcheting Rapidaptor Multi-Bit Screwdrivers

Wera's Rapidaptor ratcheting multi-bit screwdrivers feature a packed bitholding screwdriver built into a small footprint. The driver's quick-release chuck allows lightning-fast bit changes without any extra tools. The ratchet mechanism with fine toothing is integrated in the handle (36 teeth/return angle 10°). This innovative function eases and accelerates screwdriving without having to reposition the tool, boasting three positions (clockwise/counterclockwise/no ratcheting).

Directional Ratchet Switch



Rapidaptor Rapid In Technology

Medium Ratcheting Rapidaptor Multi-Bit Screwdrivers								
Part Number	*Number of Pieces*	*Part Image*	*Drive Size*	*Handle Length*	*Overall Length*	*Handle Type*	*Locking Mechanism*	*Price*
05051493001	1		1/4in	3.9in [99mm]	4.8in [122mm]	Kraftform ergonomic handle	Rapidaptor quick-release bit holder	$46.00

Wera Screwdrivers

Medium Ratcheting Multi-Bit Screwdriver Sets

Wera's Rapidaptor ratcheting multi-bit screwdrivers feature a packed bitholding screwdriver built into a small footprint. The driver's Rapidaptor quick-release chuck allows lightning-fast bit changes without any extra tools. The ratchet mechanism with fine toothing is integrated in the handle (36 teeth/return angle 10°). This innovative function eases and accelerates screwdriving without having to reposition the tool, boasting three positions (clockwise/counterclockwise/no ratcheting).

Directional Ratchet Switch

Self-Locking Mechanisn



Rapidaptor Technology

Medium Ratcheting Rapidaptor Multi-Bit Screwdriver Sets

Part Number	Number of Pieces	Part Image	Type	Bit Size	Set Includes	Price
05051061001	15		Phillips	#1, #2, #3	(1) Kraftform Kompakt Rapidaptor bit holding ratcheting screwdriver, (14) 3.5in standard bits (Phillips: #1, #2, #3 Pozidriv: #1, #2, #3, torx: T10, T15, T20, T25, hex: 3mm, 4mm, 5mm, slotted: 5.5mm), (1) robust textile pouch, (1) hook and loop fastener strip for storage	$113.00
			Slotted	5.5mm		
			External Hex	3mm, 4mm, 5mm		
			Torx	T10, T15, T20, T25		
			Pozidriv	#1, #2, #3		
05051066001	15		Phillips	#1, #2, #3	(1) Kraftform Kompakt Rapidaptor bit holding ratcheting screwdriver, (14) 3.5in standard bits (Phillips: #1, #2, #3, torx: T10, T15, T20, T25, hex: 1/8in, 5/32in, 3/16in, square: #1, #2, #3,slotted: 5.5mm), (1) robust textile pouch, (1) hook and loop fastener strip for storage	$103.00
			Slotted	5.5mm		
			External Hex	1/8in, 5/32in, 3/16in		
			Torx	T10, T15, T20, T25		
			Square	#1, #2, #3		

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.