



# Wera Bit Drivers, Bits, & Adapters

## Tool-Check Tool Sets


Wera Tool-Check systems deliver very compact tool organization for manual and machine use. Green locking elements secure tools during transport, preventing movement and loss. The 1/4" bit ratchet features drop-forged solid steel construction with fine 60-tooth mechanism for a 6° return angle, enabling precise work in confined spaces. Ergonomically shaped ratchet head with easy clockwise/counterclockwise switching ensures comfortable operation. Zykllop sockets include ball stop grooves and rear-end knurling for secure retention and manual screwdriving control. Take it easy tool finder system uses color coding by size and profile for quick tool identification. BiTorsion bits feature integrated torsion zones that prevent premature breakage during high-torque applications. The 870/1 adapter enables 1/4" socket compatibility for all Tool-Check systems. Matte chrome-plated chrome-vanadium construction provides corrosion resistance and durability.



Lockable Storage



Socket and Driver Bit Set




Rapidaotor Quick-Release System

## Features

- Green locking elements secure tools during transport and prevent loss
- Drop-forged 60-tooth bit ratchet with 6° return angle for precise work
- Ergonomically shaped ratchet head with easy clockwise/ counterclockwise switching
- BiTorsion bits feature torsion zones that prevent premature breakage
- Take it easy tool finder color coding for quick tool identification
- Zykllop sockets with ball stop grooves for secure retention
- Matte chrome-plated chrome-vanadium construction for corrosion resistance
- Includes 870/1 adapter for 1/4" socket compatibility
- Super-compact storage maximizes space efficiency
- Available in metric and imperial configurations



05049055001



Take-It-Easy Tool Finder



Great for Confined Spaces



# Wera Bit Drivers, Bits, & Adapters



## Tool-Check PLUS Socket and Driver Bit Sets

[05049055001](#)

Product Image	Type	Bit Size
	Bitholding screwdriver	1/4in x 87mm
	Zyklop mini bit ratchet	1/4in x 78mm
	Rapidaptor bit holder	1/4in x 50mm
	Socket adaptor	1/4in x 25mm
	+	Phillips bit, 25mm long (2) #1, (3) #2, #3
	★	Torx bit, 25mm long T10, T15, T20, T25, T30, T40
	●	Tamperproof Torx bit 25mm long T10, T15, T20, T25, T30
	—	Slotted bit 25mm long 1.0 x 5.5mm
	○	Hex-Plus bit 25mm long 3mm, 4mm, 5mm, 6mm, 8mm
	●	5.5mm, 6mm, 7mm, 8mm, 10mm, 12mm, 13mm
<b>Description</b>	<b>Price</b>	
Wera Tool-Check PLUS standard socket and driver bit set, ratcheting, Phillips, Pozidriv, Torx, tamperproof torx, internal hex, external hex, slotted and square, 39 pieces, 1in bit length, 1/4in drive, metric, compact Tool-Check storage system.	\$150.00	6-point socket

## Tool-Check PLUS Socket and Driver Bit Sets

[05049060001](#)

Product Image	Type	Bit Size
	Bitholding screwdriver	1/4in x 78mm
	Zyklop mini bit ratchet	1/4in
	Rapidaptor bit holder	1/4in x 50mm
	Socket adaptor	1/4in x 25mm
	+	Phillips bit, 25mm long (2) #1, (3) #2, #3
	—	Slotted bit 25mm long 1.0 x 5.5mm
	★	Torx bit, 25mm long T10, T15, T20, T25, T30, T40
	●	Tamperproof Torx bit 25mm long T10, T15, T20, T25, T30
	□	Square bit 25mm long #1, (3) #2, #3
	○	3/32in, 1/8in, 5/32in, 3/16in, 1/4in
<b>Description</b>	<b>Price</b>	
Wera Tool-Check PLUS standard socket and driver bit set, ratcheting, Phillips, Torx, tamperproof torx, internal hex, external hex, slotted and square, 39 pieces, 1in bit length, 1/4in drive, imperial, compact Tool-Check storage system.	\$150.00	6-point socket
		3/16in, 1/4in, 5/16in, 11/32in, 3/8in, 7/16in, 1/2in

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.



# Wera Bit Drivers, Bits, & Adapters



## Tool-Check PLUS Socket and Driver Bit Sets

05056490001

Product Image	Type	Bit Size
	Bitholding screwdriver	1/4in x 78mm
	Zyklop mini bit ratchet	1/4in
	Rapidaptor bit holder	1/4in x 50mm
	Socket adaptor	1/4in x 25mm
	+	Phillips bit, 25mm long
	*	Pozidriv bit, 25mm long
	◆	Torx bit, 25mm long
	◆◆	Tamperproof Torx bit, 25mm long
	●	Slotted bit, 25mm long
	○	Hex-Plus bit, 25mm long
	○○	3.0, 4.0, 5.0, 6.0, 8.0mm
<b>Description</b>	<b>Price</b>	
Wera Tool-Check PLUS standard socket and driver bit set, ratcheting, Phillips, slotted, Torx, tamperproof torx, internal hex, external hex and Pozidriv, 39 pieces, 1in bit length, 1/4in drive, metric.	Retired	5.5, 6.0, 7.0, 8.0, 10.0, 12.0, 13.0mm

## Tool-Check Socket and Driver Bit Sets

05056491001

Product Image	Type	Bit Size
	Bitholding screwdriver	1/4in x 78mm
	Zyklop mini bit ratchet	1/4in
	Rapidaptor bit holder	1/4in x 50mm
	Socket adaptor	1/4in x 25mm
	+	Phillips bit, 25mm long
	◆	Torx bit, 25mm long
	◆◆	Tamperproof Torx bit, 25mm long
	●	Slotted bit, 25mm long
	○	Hex-Plus bit, 25mm long
	○○	3/32, 1/8, 5/32, 3/16, 1/4in
<b>Description</b>	<b>Price</b>	
Wera Tool-Check standard socket and driver bit set, ratcheting, Phillips, slotted, Torx, tamperproof torx, internal hex, square and external hex, 39 pieces, 1in bit length, 1/4in drive, imperial.	Retired	3/16, 1/4, 5/16, 11/32, 3/8, 7/16, 1/2in

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.



# Wera Bit Drivers, Bits, & Adapters



## Tool-Check Socket and Driver Bit Sets

05049050001

Product Image	Type	Bit Size
	Zyklop Mini bit ratchet	1/4in
	Rapidaptor bit holder	1/4in x 50mm
	Socket adaptor	1/4in x 25mm
	Phillips bit, 25mm long	(2) #1, (3) #2, #3
	Slotted bit 25mm long	1.0 x 5.5mm
	Tamperproof Torx bit, 25mm long	T10, T15, T20, T25, T30
	Pozidriv bit, 25mm long	#1, (3) #2, #3
	Hex-Plus bit 25mm long	3mm, 4mm, 5mm, 6mm, 8mm
	6-point socket	5.5mm, 6mm, 7mm, 8mm, 10mm, 12mm, 13mm
<b>Description</b>	<b>Price</b>	
Wera Tool-Check standard socket and driver bit set, ratcheting, Phillips, Pozidriv, Torx, tamperproof torx, external hex, internal hex, slotted and square, 38 pieces, 1in bit length, 1/4in drive, metric, compact Tool-Check storage system.	\$143.00	

## Tool-Check Socket and Driver Bit Sets

05073220055

Product Image	Type	Bit Size
	Zyklop Mini bit ratchet	1/4in
	Rapidaptor bit holder	1/4in x 50mm
	Socket adaptor	1/4in x 25mm
	Slotted bit 25mm long	1.0 x 5.5mm
	Hex-Plus bit 25mm long	3, 4, 5, 6, 8mm
	Phillips bit, 25mm long	(2) P#1, (3) #2, #3
	Torx bit, 25mm long	T10, T15, T20, T25, T30, T40
	Tamperproof Torx bit, 25mm long	T10, T15, T20, T25, T30
	Pozidriv bit 25mm long	#1, (3) #2, #3
	6-point socket	5.5, 6.0, 7.0, 8.0, 10.0, 12.0, 13.0mm
<b>Description</b>	<b>Price</b>	
Wera Tool-Check standard driver bit and socket set, ratcheting, Phillips, Pozidriv, slotted, Torx, tamperproof torx, internal hex and external hex, 38 pieces, 1in bit length, 1/4in drive, metric.	\$112.00	

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.



# Wera Bit Drivers, Bits, & Adapters



## Bit-Check Socket and Driver Bit Sets

### TW-DB-SET-28R

Product Image	Type	Bit Size
	Zyklop Mini bit ratchet	1/4in
	Rapidaptor bit holder	1/4in x 50mm
	Socket adaptor	1/4in x 25mm
	+	Phillips bit, 25mm long (2) PH1, (3) PH2, PH3
	★	Torx bit, 25mm long T10, T15, T20, T25, T30, T40
	◆	Tamperproof Torx bit, 25mm long T10, T15, T20, T25, T30
	●	Slotted bit 25mm long 1.0 x 5.5mm
	○	Hex-Plus bit 25mm long 3/32, 1/8, 5/32, 3/16, 1/4in
Wera Bit-Check standard driver bit set, ratcheting, Phillips, Torx, tamperproof torx, external hex, slotted and square, 31 pieces, 1in bit length, 1/4in drive, imperial.	\$85.00	■ Square bit 25mm long #1, (3) #2, #3

Note: Screwdriver bits and bit-holders are warranted against manufacturer defect only.