


30mm Pushbutton NEMA 12 and 13 Operator Console



Applications

Designed for use where slanted control surfaces are wanted. Enclosures may be mounted in a variety of ways to meet specific requirements. Receives standard 30mm oil-tight pushbuttons, switches and pilot lights. Provides protection from dirt, dust, oil and water.



Construction

- Fabricated from 14 gauge steel
- Closed cell oil- resistant neoprene gasket
- Continuously welded seams ground smooth
- External mounting feet, top and bottom of enclosure
- Captivated cover screws thread into sealed wells
- Standard "4-way" pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights
- Enclosures with 2 or more rows of holes have internal detachable hinges to hold cover open during wiring, yet permit quick removal
- Grounding provisions provided

Finish

- ANSI 61 gray polyester powder inside and out over phosphatized surfaces

Listings

- UL 508, Types 12 & 13 [UL File E64791]
- NEMA/EEMAC Types 12 & 13



Enclosure Shipping Schedule					
Same day	1 - 5 days	1 - 7 days	1 - 10 days	1 - 15 days	1 - 20 days

Color indicates shipping lead time in business days.

30mm Pushbutton NEMA 12 and 13 Operator Console			
Part Number	Price	# Holes	Enclosure Size HxWxD
WPBA1	\$74.00	1	3.77 x 3.59 x 4.88 [96 x 91 x 124]
WPBA2	\$86.00	2	3.77 x 5.84 x 4.88 [96 x 148 x 124]
WPBA3	\$98.00	3	3.77 x 8.09 x 4.88 [96 x 205 x 124]
WPBA4	\$110.00	4	3.77 x 10.34 x 4.88 [96 x 263 x 124]
WPBA4S	\$124.00	4	7.52 x 6.59 x 6.76 [191 x 167 x 172]
WPBA6	\$143.00	6	7.52 x 8.84 x 6.76 [191 x 225 x 172]
WPBA8	\$163.00	8	7.52 x 11.09 x 6.76 [191 x 282 x 172]
WPBA9	\$170.00	9	9.77 x 8.84 x 7.88 [248 x 225 x 200]
WPBA10	\$180.00	10	7.52 x 13.34 x 6.76 [191 x 339 x 172]
WPBA12	\$197.00	12	7.52 x 15.59 x 6.76 [191 x 396 x 172]
WPBA12S	\$189.00	12	12.02 x 8.84 x 9.01 [305 x 225 x 229]
WPBA16	\$211.00	16	7.52 x 20.09 x 6.76 [191 x 510 x 172]
WPBA16S	\$244.00	16	12.02 x 11.09 x 9.01 [305 x 282 x 229]
WPBA20	\$243.00	20	12.02 x 13.34 x 9.01 [305 x 339 x 229]
WPBA25	\$276.00	25	14.27 x 13.34 x 10.13 [362 x 339 x 257]
WPBA30	\$302.00	30	14.27 x 15.59 x 10.13 [362 x 396 x 257]


Note: Dimensions in inches [millimeters].

30mm Pushbutton NEMA 12 and 13 Operator Consolelet






Dimensions

in [mm]



WPBA HOLE ARRANGEMENTS



See our website: www.AutomationDirect.com for complete engineering drawings.