

30mm Pushbutton NEMA 12 and 13 Operator Consolelet



Applications

Designed for use where slanted control surfaces are wanted. Enclosures may be mounted in a variety of ways to meet specific requirements. Receives standard 30mm [1.18 in] oil-tight pushbuttons, switches and pilot lights. Provides protection from dirt, dust, oil, and water.



Construction

- Fabricated from 14-gauge steel
- Closed-cell oil- resistant neoprene gasket
- Continuously-welded seams ground smooth
- External mounting feet, top and bottom of enclosure
- Captivated cover screws thread into sealed wells
- Standard "4-way" pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights
- Enclosures with 2 or more rows of holes have internal detachable hinges to hold cover open during wiring, yet permit quick removal
- Grounding provisions provided

Finish

- ANSI 61 gray polyester powder inside and out over phosphatized surfaces

Listings

- UL 508 12 and 13 [UL File E64791]
- NEMA/EEMAC 12 and 13

Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

30mm Pushbutton NEMA 12 and 13 Operator Consolelet

Part Number	Price	# Holes	Enclosure Size HxWxD
WPBA1	\$101.00	1	3.77 x 3.59 x 4.88 [96 x 91 x 124]
WPBA2	\$118.00	2	3.77 x 5.84 x 4.88 [96 x 148 x 124]
WPBA3	\$134.00	3	3.77 x 8.09 x 4.88 [96 x 205 x 124]
WPBA4	\$151.00	4	3.77 x 10.34 x 4.88 [96 x 263 x 124]
WPBA4S	\$169.00	4	7.52 x 6.59 x 6.76 [191 x 167 x 172]
WPBA6	\$196.00	6	7.52 x 8.84 x 6.76 [191 x 225 x 172]
WPBA8	\$222.00	8	7.52 x 11.09 x 6.76 [191 x 282 x 172]
WPBA9	\$232.00	9	9.77 x 8.84 x 7.88 [248 x 225 x 200]
WPBA10	\$246.00	10	7.52 x 13.34 x 6.76 [191 x 339 x 172]
WPBA12	\$269.00	12	7.52 x 15.59 x 6.76 [191 x 396 x 172]
WPBA12S	\$258.00	12	12.02 x 8.84 x 9.01 [305 x 225 x 229]
WPBA16	\$288.00	16	7.52 x 20.09 x 6.76 [191 x 510 x 172]
WPBA16S	\$333.00	16	12.02 x 11.09 x 9.01 [305 x 282 x 229]
WPBA20	\$332.00	20	12.02 x 13.34 x 9.01 [305 x 339 x 229]
WPBA25	\$378.00	25	14.27 x 13.34 x 10.13 [362 x 339 x 257]
WPBA30	\$412.00	30	14.27 x 15.59 x 10.13 [362 x 396 x 257]


Note: Dimensions in inches [millimeters].



30mm Pushbutton NEMA 12 and 13 Operator Consolelet



Dimensions



WPBA HOLE ARRANGEMENTS

