




Brass Adapter Fittings

NITRA brass fittings are machined from quality brass bar stock or forgings. They work well with air, water, oil, oxygen, nitrogen and argon. Available in most popular styles and sizes, the fittings all have NPT threaded connections.


Features

- 10 different styles
- Machined from yellow brass bar stock or forging
- Work with water, oil, air and other gases
- Maximum pressure of 800 psi

Note: Actual product dimensions and appearance may vary




BFMC-14N



NITRA™ Male Brass Connectors									
Inch Sizes - dimensions in inches									
Part No.	Price	Description	Parts Per Pkg	Weight	T1	T2	C Hex	L	Flow Dia. D
<u>BFMC-18N</u>	\$5.75	Male connector, 1/8 inch NPT to 1/8 inch NPT	5	0.1	1/8	1/8	7/16	0.97	0.22
<u>BFMC-14N-18N</u>	\$8.25	Male connector, 1/4 inch NPT to 1/8 inch NPT	5	0.1	1/4	1/8	9/16	1.19	0.22
<u>BFMC-14N</u>	\$8.50	Male connector, 1/4 inch NPT to 1/4 inch NPT	5	0.1	1/4	1/4	9/16	1.38	0.31
<u>BFMC-38N-18N</u>	\$11.00	Male connector, 3/8 inch NPT to 1/8 inch NPT	5	0.3	3/8	1/8	11/16	1.22	0.22
<u>BFMC-38N-14N</u>	\$12.00	Male connector, 3/8 inch NPT to 1/4 inch NPT	5	0.3	3/8	1/4	11/16	1.41	0.31
<u>BFMC-38N</u>	\$13.50	Male connector, 3/8 inch NPT to 3/8 inch NPT	5	0.3	3/8	3/8	11/16	1.41	0.44
<u>BFMC-12N-14N</u>	\$7.50	Male connector, 1/2 inch NPT to 1/4 inch NPT	2	0.3	1/2	1/4	7/8	1.62	0.31
<u>BFMC-12N-38N</u>	\$7.50	Male connector, 1/2 inch NPT to 3/8 inch NPT	2	0.2	1/2	3/8	7/8	1.62	0.44
<u>BFMC-12N</u>	\$8.50	Male connector, 1/2 inch NPT to 1/2 inch NPT	2	0.3	1/2	1/2	7/8	1.81	0.56



BFFC-12N-14N



NITRA™ Female Brass Connectors									
Inch Sizes - dimensions in inches									
Part No.	Price	Description	Parts Per Pkg	Weight	T1	T2	C Hex	L	Flow Dia. D
<u>BFFC-18N</u>	\$6.25	Female connector, 1/8 inch NPT to 1/8 inch NPT	5	0.1	1/8	1/8	9/16	0.75	0.34
<u>BFFC-14N-18N</u>	\$10.50	Female connector, 1/4 inch NPT to 1/8 inch NPT	5	0.1	1/4	1/8	3/4	0.97	0.34
<u>BFFC-14N</u>	\$13.00	Female connector, 1/4 inch NPT to 1/4 inch NPT	5	0.2	1/4	1/4	3/4	1.12	0.44
<u>BFFC-38N-14N</u>	\$22.00	Female connector, 3/8 inch NPT to 1/4 inch NPT	5	0.2	3/8	1/4	7/8	1.16	0.44
<u>BFFC-38N</u>	\$16.50	Female connector, 3/8 inch NPT to 3/8 inch NPT	5	0.3	3/8	3/8	7/8	1.12	0.52
<u>BFFC-12N-14N</u>	\$9.50	Female connector, 1/2 inch NPT to 1/4 inch NPT	2	0.4	1/2	1/4	1-1/16	1.28	0.44
<u>BFFC-12N-38N</u>	\$12.50	Female connector, 1/2 inch NPT to 3/8 inch NPT	2	0.2	1/2	3/8	15/16	1.32	0.52
<u>BFFC-12N</u>	\$11.00	Female connector, 1/2 inch NPT to 1/2 inch NPT	2	0.4	1/2	1/2	1-1/16	1.50	0.70




Brass Adapter Fittings

Note: Actual product dimensions and appearance may vary



BFMFR-38N-14N




NITRA™ Male to Female Brass Connectors

Inch Sizes - dimensions in inches

Part No.	Price	Description	Parts Per Pkg	Weight	T1	T2	C Hex	L	Flow Dia. D
BFMFR-14N-18N	\$12.00	Male to female connector, 1/8 inch NPT male to 1/4 inch NPT female	5	0.1	1/4	1/8	3/4	1.06	0.22
BFMFR-38N-18N	\$21.00	Male to female connector, 1/8 inch NPT male to 3/8 inch NPT female	5	0.1	3/8	1/8	7/8	1.1	0.22
BFMFR-38N-14N	\$13.00	Male to female connector, 1/4 inch NPT male to 3/8 inch NPT female	5	0.1	3/8	1/4	7/8	1.25	0.314
BFMFR-12N-38N	\$10.50	Male to female connector, 3/8 inch NPT male to 1/2 inch NPT female	5	0.4	1/2	3/8	1-1/16	1.47	0.44



BFHB-12N-14N




NITRA™ Brass Hex Bushing

Inch Sizes - dimensions in inches

Part No.	Price	Description	Parts Per Pkg	Weight	T1	T2	C Hex	L	Flow Dia. D
BFHB-14N-18N	\$6.25	Hex bushing, 1/4 inch NPT male to 1/8 inch NPT female	5	0.3	1/4	1/8	9/16	0.75	0.34
BFHB-38N-18N	\$9.50	Hex bushing, 3/8 inch NPT male to 1/8 inch NPT female	5	0.3	3/8	1/8	11/16	0.75	0.34
BFHB-38N-14N	\$9.50	Hex bushing, 3/8 inch NPT male to 1/4 inch NPT female	5	0.3	3/8	1/4	3/4	0.75	0.44
BFHB-12N-18N	\$6.50	Hex bushing, 1/2 inch NPT male to 1/8 inch NPT female	2	0.3	1/2	1/8	7/8	1.0	0.34
BFHB-12N-14N	\$6.00	Hex bushing, 1/2 inch NPT male to 1/4 inch NPT female	2	0.3	1/2	1/4	7/8	1.0	0.44
BFHB-12N-38N	\$6.00	Hex bushing, 1/2 inch NPT male to 3/8 inch NPT female	2	0.2	1/2	3/8	7/8	1.0	0.57



BFFE-14N




NITRA™ Brass Female Elbow

Inch Sizes - dimensions in inches

Part No.	Price	Description	Parts Per Pkg	Weight	T	M	Flow Dia. D	L
BFFE-18N	\$5.25	Female elbow, 1/8 inch NPT female	2	0.2	1/8	0.55	0.339	0.83
BFFE-14N	\$7.25	Female elbow, 1/4 inch NPT female	2	0.2	1/4	0.78	0.441	1.06
BFFE-38N	\$11.00	Female elbow, 3/8 inch NPT female	2	0.4	3/8	0.84	0.571	1.30



BFSE-38N



NITRA™ Female to Male Brass Street Elbow

Inch Sizes - dimensions in inches

Part No.	Price	Description	Parts Per Pkg	Weight	T	M	N	Flow Dia. D	L
BFSE-18N	\$3.00	Street elbow, 1/8 inch NPT female to 1/8 male	2	0.2	1/8	0.66	0.35	0.22	0.81
BFSE-14N	\$5.75	Street elbow, 1/4 inch NPT female to 1/4 male	2	0.2	1/4	0.91	0.47	0.34	1.25
BFSE-38N	\$8.50	Street elbow, 3/8 inch NPT female to 3/8 male	2	0.3	3/8	0.97	0.49	0.41	1.42
BFSE-12N	\$18.50	Street elbow, 1/2 inch NPT female to 1/2 male	2	0.4	1/2	1.25	1.03	0.56	1.61




Brass Adapter Fittings

• **Note: Actual product dimensions and appearance may vary**




BFMT-14N



NITRA™ Brass Male Tee Fittings										
Inch Sizes - dimensions in inches										
Part No.	Price	Description	Parts Per Pkg	Weight	T1	T2	L	M	N	Flow Dia. D
BFMT-18N	\$6.25	Male tee, 1/8 inch NPT male	2	0.3	1/8	1/8	1.06	0.53	0.66	0.22
BFMT-14N	\$12.00	Male tee, 1/4 inch NPT male	2	0.3	1/4	1/4	1.52	0.76	0.91	0.31
BFMT-38N	\$13.00	Male tee, 3/8 inch NPT male	2	0.4	3/8	3/8	1.68	0.84	0.97	0.44




BFFT-14N



NITRA™ Brass Female Tee Fittings									
Inch Sizes - dimensions in inches									
Part No.	Price	Description	Parts Per Pkg	Weight	T	L	M	Flow Dia. D	
BFFT-18N	\$6.50	Female tee, 1/8 inch NPT female	2	0.3	1/8	1.06	0.53	0.34	
BFFT-14N	\$11.50	Female tee, 1/4 inch NPT female	2	0.3	1/4	1.52	0.76	0.44	
BFFT-38N	\$13.50	Female tee, 3/8 inch NPT female	2	0.5	3/8	1.68	0.84	0.57	
BFFT-12N	\$25.50	Female tee, 1/2 inch NPT female	2	0.9	1/2	2.14	1.07	0.70	




BFRHP-38N



NITRA™ Brass Recessed Hex Plug Fittings						
Inch Sizes - dimensions in inches						
Part No.	Price	Description	Parts Per Pkg	Weight	C Hex	L
BFRHP-14N	\$4.25	Recessed hex plug, 1/4 inch NPT male	5	0.1	1/4	0.46
BFRHP-38N	\$6.00	Recessed hex plug, 3/8 inch NPT male	5	0.2	5/16	0.46
BFRHP-12N	\$12.00	Recessed hex plug, 1/2 inch NPT male	5	0.2	3/8	0.61



BFHHP-38N



NITRA™ Brass Hex Plug Fittings							
Inch Sizes - dimensions in inches							
Part No.	Price	Description	Parts Per Pkg	Weight	T	C Hex	L
BFHHP-18N	\$4.00	Hex head plug, 1/8 inch NPT male	5	0.1	1/8	7/16	0.56
BFHHP-14N	\$6.00	Hex head plug, 1/4 inch NPT male	5	0.1	1/4	9/16	0.75
BFHHP-38N	\$9.25	Hex head plug, 3/8 inch NPT male	5	0.1	3/8	11/16	0.78
BFHHP-12N	\$12.50	Hex head plug, 1/2 inch NPT male	5	0.2	1/2		0.97




Brass Adapter Fittings

• **Note: Actual product dimensions and appearance may vary**



BAHB-316-18N



NITRA™ Brass Straight Barb Fitting							
Inch Sizes - dimensions in inches							
Part No.	Price	Description	Weight	T	L	ØD	C Hex
BAHB-316-18N	\$12.50	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 3/16in hose to (1) 1/8in male NPT connection(s). Package of 5.	0.1	1/8	1.20 [305]	0.20 [5.1]	0.44 [11.1]
BAHB-316-14N	\$12.50	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 3/16in hose to (1) 1/4in male NPT connection(s). Package of 5.	0.2	1/4	1.43 [36.2]	0.20 [5.1]	0.56 [14.3]
BAHB-14-18N	\$8.25	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 1/4in hose to (1) 1/8in male NPT connection(s). Package of 5.	0.1	1/8	1.49 [37.7]	0.24 [6.1]	0.44 [11.1]
BAHB-14-14N	\$10.50	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 1/4in hose to (1) 1/4in male NPT connection(s). Package of 5.	0.2	1/4	1.69 [42.9]	0.24 [6.1]	0.56 [14.3]
BAHB-14-38N	\$13.50	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 1/4in hose to (1) 3/8in male NPT connection(s). Package of 5.	0.3	3/8	1.70 [43.3]	0.24 [6.1]	0.69 [17.5]
BAHB-516-18N	\$12.00	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 5/16in hose to (1) 1/8in male NPT connection(s). Package of 5.	0.1	1/8	1.40 [35.6]	0.29 [7.4]	0.44 [11.1]
BAHB-516-14N	\$9.75	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 5/16in hose to (1) 1/4in male NPT connection(s). Package of 5.	0.2	1/4	1.70 [43.3]	0.29 [7.4]	0.56 [14.3]
BAHB-516-38N	\$22.50	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 5/16in hose to (1) 3/8in male NPT connection(s). Package of 5.	0.3	3/8	1.49 [37.8]	0.29 [7.4]	0.69 [17.5]
BAHB-38-14N	\$10.50	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 3/8in hose to (1) 1/4in male NPT connection(s). Package of 5.	0.2	1/4	1.70 [43.3]	0.36 [9.2]	0.56 [14.3]
BAHB-38-38N	\$13.50	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 3/8in hose to (1) 3/8in male NPT connection(s). Package of 5.	0.3	3/8	1.70 [43.3]	0.36 [9.2]	0.69 [17.4]
BAHB-38-12N	\$24.00	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 3/8in hose to (1) 1/2in male NPT connection(s). Package of 5.	0.5	1/2	1.89 [48.0]	0.36 [9.2]	0.88 [22.2]
BAHB-12-14N	\$13.50	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 1/2in hose to (1) 1/4in male NPT connection(s). Package of 5.	0.3	1/4	1.70 [43.3]	0.48 [12.3]	0.56 [14.3]
BAHB-12-38N	\$15.00	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 1/2in hose to (1) 3/8in male NPT connection(s). Package of 5.	0.3	3/8	1.76 [44.8]	0.48 [12.3]	0.69 [17.5]
BAHB-12-12N	\$22.50	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 1/2in hose to (1) 1/2in male NPT connection(s). Package of 5.	0.5	1/2	1.86 [47.2]	0.48 [12.3]	0.88 [22.2]
BAHB-58-38N	\$13.50	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 5/8in hose to (1) 3/8in male NPT connection(s). Package of 3.	0.2	3/8	1.84 [46.7]	0.60 [15.3]	0.88 [22.2]
BAHB-58-12N	\$15.50	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 5/8in hose to (1) 1/2in male NPT connection(s). Package of 3.	0.4	1/2	1.98 [50.4]	0.60 [15.3]	0.88 [22.2]
BAHB-58-34N	\$26.00	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 5/8in hose to (1) 3/4in male NPT connection(s). Package of 3.	0.5	3/4	1.89 [48.1]	0.60 [15.3]	1.06 [27.0]
BAHB-34-12N	\$17.00	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 3/4in hose to (1) 1/2in male NPT connection(s). Package of 3.	0.4	1/2	1.99 [50.5]	0.73 [18.5]	0.88 [22.2]
BAHB-34-34N	\$22.50	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 3/4in hose to (1) 3/4in male NPT connection(s). Package of 3.	0.3	3/4	2.03 [51.6]	0.73 [18.5]	1.06 [27.0]
BAHB-34-1N	\$43.00	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 3/4in hose to (1) 1in male NPT connection(s). Package of 3.	0.8	1	2.25 [57.2]	0.73 [18.5]	1.38 [34.9]
BAHB-1-34N	\$8.50	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 1in hose to (1) 3/4in male NPT connection(s). Package of 1.	0.2	3/4	2.17 [55.0]	0.99 [25.1]	1.06 [27.0]
BAHB-1-1N	\$15.50	NITRA threaded fitting, hose barb, brass body, brass threads, (1) 1in hose to (1) 1in male NPT connection(s). Package of 1.	0.3	1	2.36 [60.0]	0.99 [25.1]	1.38 [34.9]




Brass Adapter Fittings

• Note: Actual product dimensions and appearance may vary




BAHBL-316-18N



NITRA™ Brass Male Elbow Barb Fitting								
Inch Sizes - dimensions in inches								
Part No.	Price	Description	Weight	T	M	N	ØD	
BAHBL-316-18N	\$24.00	NITRA threaded fitting, hose barb elbow, brass body, brass threads, (1) 3/16in hose to (1) 1/8in male NPT connection(s). Package of 5.	0.1	1/8	0.95 [24.0]	0.71 [18.2]	0.20 [5.1]	
BAHBL-316-14N	\$30.00	NITRA threaded fitting, hose barb elbow, brass body, brass threads, (1) 3/16in hose to (1) 1/4in male NPT connection(s). Package of 5.	0.3	1/4	1.00 [25.4]	0.83 [21.1]	0.20 [5.1]	
BAHBL-14-18N	\$24.00	NITRA threaded fitting, hose barb elbow, brass body, brass threads, (1) 1/4in hose to (1) 1/8in male NPT connection(s). Package of 5.	0.2	1/8	1.25 [31.8]	0.60 [15.3]	0.24 [6.1]	
BAHBL-14-14N	\$30.00	NITRA threaded fitting, hose barb elbow, brass body, brass threads, (1) 1/4in hose to (1) 1/4in male NPT connection(s). Package of 5.	0.3	1/4	1.33 [33.8]	0.84 [21.4]	0.24 [6.1]	
BAHBL-14-38N	\$51.00	NITRA threaded fitting, hose barb elbow, brass body, brass threads, (1) 1/4in hose to (1) 3/8in male NPT connection(s). Package of 5.	0.4	3/8	1.22 [31.0]	0.94 [23.9]	0.24 [6.1]	
BAHBL-516-38N	\$56.00	NITRA threaded fitting, hose barb elbow, brass body, brass threads, (1) 5/16in hose to (1) 3/8in male NPT connection(s). Package of 5.	0.4	3/8	1.22 [31.1]	0.90 [22.9]	0.29 [7.4]	
BAHBL-38-14N	\$24.00	NITRA threaded fitting, hose barb elbow, brass body, brass threads, (1) 3/8in hose to (1) 1/4in male NPT connection(s). Package of 5.	0.4	1/4	1.32 [33.4]	0.83 [21.1]	0.36 [9.2]	
BAHBL-38-38N	\$31.00	NITRA threaded fitting, hose barb elbow, brass body, brass threads, (1) 3/8in hose to (1) 3/8in male NPT connection(s). Package of 5.	0.6	3/8	1.42 [35.9]	0.95 [24.0]	0.36 [9.2]	
BAHBL-12-14N	\$31.50	NITRA threaded fitting, hose barb elbow, brass body, brass threads, (1) 1/2in hose to (1) 1/4in male NPT connection(s). Package of 5.	0.4	1/4	1.29 [32.7]	0.98 [24.9]	0.48 [12.3]	
BAHBL-12-38N	\$54.00	NITRA threaded fitting, hose barb elbow, brass body, brass threads, (1) 1/2in hose to (1) 3/8in male NPT connection(s). Package of 5.	0.5	3/8	1.36 [34.6]	1.01 [25.5]	0.48 [12.3]	
BAHBL-12-12N	\$46.00	NITRA threaded fitting, hose barb elbow, brass body, brass threads, (1) 1/2in hose to (1) 1/2in male NPT connection(s). Package of 5.	0.6	1/2	1.14 [28.8]	1.10 [28.0]	0.48 [12.3]	
BAHBL-58-38N	\$37.00	NITRA threaded fitting, hose barb elbow, brass body, brass threads, (1) 5/8in hose to (1) 3/8in male NPT connection(s). Package of 3.	0.4	3/8	1.45 [37.0]	1.16 [29.5]	0.60 [15.3]	
BAHBL-58-12N	\$42.50	NITRA threaded fitting, hose barb elbow, brass body, brass threads, (1) 5/8in hose to (1) 1/2in male NPT connection(s). Package of 3.	0.5	1/2	1.45 [37.0]	1.14 [29.1]	0.60 [15.3]	
BAHBL-34-12N	\$54.00	NITRA threaded fitting, hose barb elbow, brass body, brass threads, (1) 3/4in hose to (1) 1/2in male NPT connection(s). Package of 3.	0.6	1/2	1.35 [34.4]	1.25 [31.8]	0.73 [18.5]	
BAHBL-34-34N	\$79.00	NITRA threaded fitting, hose barb elbow, brass body, brass threads, (1) 3/4in hose to (1) 3/4in male NPT connection(s). Package of 3.	0.7	3/4	1.54 [39.0]	1.31 [33.2]	0.73 [18.5]	
BAHBL-1-34N	\$31.00	NITRA threaded fitting, hose barb elbow, brass body, brass threads, (1) 1in hose to (1) 3/4in male NPT connection(s). Package of 1.	0.4	3/4	1.70 [43.1]	1.42 [36.2]	0.99 [25.1]	
BAHBL-1-1N	\$56.00	NITRA threaded fitting, hose barb elbow, brass body, brass threads, (1) 1in hose to (1) 1in male NPT connection(s). Package of 1.	0.4	1	1.78 [45.2]	1.63 [41.5]	0.99 [25.1]	

BAHM-58



NITRA™ Brass Hose Mender Fitting							
Inch Sizes - dimensions in inches							
Part No.	Price	Description	Weight	L	ØD1	ØD2	
BAHM-316	\$7.50	NITRA barbed fitting, hose mender, brass body, (2) 3/16in hose connection(s). Package of 5.	0.1	1.45 [36.7]	0.20 [5.1]	0.23 [5.8]	
BAHM-14	\$9.75	NITRA barbed fitting, hose mender, brass body, (2) 1/4in hose connection(s). Package of 5.	0.1	2.00 [50.8]	0.24 [6.1]	0.50 [12.7]	
BAHM-516	\$12.50	NITRA barbed fitting, hose mender, brass body, (2) 5/16in hose connection(s). Package of 5.	0.1	1.67 [42.4]	0.29 [7.4]	0.36 [9.1]	
BAHM-38	\$13.50	NITRA barbed fitting, hose mender, brass body, (2) 3/8in hose connection(s). Package of 5.	0.2	2.00 [50.8]	0.36 [9.2]	0.50 [12.7]	
BAHM-12	\$18.50	NITRA barbed fitting, hose mender, brass body, (2) 1/2in hose connection(s). Package of 5.	0.3	2.01 [51.1]	0.48 [12.3]	0.63 [15.9]	
BAHM-58	\$13.00	NITRA barbed fitting, hose mender, brass body, (2) 5/8in hose connection(s). Package of 3.	0.3	2.29 [58.0]	0.60 [15.3]	0.75 [19.1]	
BAHM-34	\$16.50	NITRA barbed fitting, hose mender, brass body, (2) 3/4in hose connection(s). Package of 3.	0.3	2.00 [50.8]	0.73 [18.5]	0.88 [22.2]	
BAHM-1	\$30.50	NITRA barbed fitting, hose mender, brass body, (2) 1in hose connection(s). Package of 3.	0.6	2.49 [63.2]	0.99 [25.1]	1.19 [30.2]	