

Heartland Series Enclosure Accessories



Heartland Series – Enclosure Pole Mount Kits			
Part Number	Price	For Pole Diameter	Fits Enclosure Width
PM6-8		3.00 -12.00 [76- 305]	6.00 - 8.00 [152 - 203]
PM10-12			10.00 - 12.00 [254 - 305]
PM14-16			14.00 - 16.00 [356 - 406]
PM18-24			18.00 - 24.00 [457 - 610]
Note: Dimensions in inches [millimeters].			



PM14-16



REV60



REV80

Heartland Series – Enclosure Vents		
Part Number	Price	Description
REAH-V60		vent, 60 mm, polycarbonate, maintains NEMA 3R rating.
REAH-V80		vent, 80 mm, polycarbonate, not UL rated, enclosure is NEMA 1 when vent is installed

Heartland Series Enclosure Accessories



Enclosure Latch Kits		
Part Number	Price	Description
<u>AHLKSS</u>		latch, replacement, quick-release, 304 stainless steel. Package of 2.
<u>AHLK</u>		latch, replacement, quick-release, polycarbonate. Package of 2.



[AHLKSS](#)

[AHLK](#)

Accessory Kit		
Part Number	Price	Description
<u>AHAK</u>		mounting feet kit, polycarbonate. Includes (4) mounting feet and mounting hardware.



[AHAK](#)

Enclosure Replacement Fasteners		
Part Number	Price	Description
<u>AHSNK</u>		slot nut kit, #10-32 UNF x 0.375 in, Phillips pan head, zinc plated steel. Package of 2. Includes screw and galvanized steel slot nut.
<u>AHTSKSS</u>		thumb screw, replacement, #10-32 UNF x 0.375 in, stainless steel. Package of 2. Nylon washer included.
<u>AHTSKAL</u>		thumb screw, replacement, #10-32 UNF x 0.375 in, aluminum. Package of 2. Nylon washer included.
<u>RE2PKTBS</u>		trilobular self-tapping screw, replacement, #10-14 x 0.375 in, Phillips pan head, aluminum. Package of 2.



[AHSNK](#)

[AHTSKSS](#)



[AHTSKAL](#)

[RE2PKTBS](#)

Enclosure Swing Panel Mounts		
Part Number	Price	Description
<u>AHSPM</u>		AttaBox Heartland series swing panel bracket, polycarbonate. Package of 4. For use with Heartland series enclosures. Mounting screws included.



[AHSPM](#)

Heartland Series Enclosure Accessories



Mounting Flanges		
Part Number	Price	Description
MFK6		mounting flanges, replacement, polycarbonate. For use with 6 in wide Heartland series enclosures. Includes (2) mounting flanges and mounting hardware.
MFK8		mounting flanges, replacement, polycarbonate. For use with 8 in wide Heartland series enclosures. Includes (2) mounting flanges and mounting hardware.
MFK10		mounting flanges, replacement, polycarbonate. For use with 10 in wide Heartland series enclosures. Includes (2) mounting flanges and mounting hardware.
MFK12		mounting flanges, replacement, polycarbonate. For use with 12 in wide Heartland series enclosures. Includes (2) mounting flanges and mounting hardware.
MFK14		mounting flanges, replacement, polycarbonate. For use with 14 in wide Heartland series enclosures. Includes (2) mounting flanges and mounting hardware.
MFK16		mounting flanges, replacement, polycarbonate. For use with 16 in wide Heartland series enclosures. Includes (2) mounting flanges and mounting hardware.

[MFK6](#)

Internal Shelf		
Part Number	Price	Description
WD105		shelf, weight distribution, 10 x 5 in, aluminum. (2) screws and (2) slot nuts included.
WD106		shelf, weight distribution, 10 x 6 in, aluminum. (2) screws and (2) slot nuts included.
WD12		shelf, weight distribution, 12 x 6 in, aluminum. (2) screws and (2) slot nuts included.
WD14		shelf, weight distribution, 14 x 6 in, aluminum. (2) screws and (2) slot nuts included.
WD168		shelf, weight distribution, 16 x 8 in, aluminum. (2) screws and (2) slot nuts included.
WD1610		shelf, weight distribution, 16 x 10 in, aluminum. (2) screws and (2) slot nuts included.
WD24		shelf, weight distribution, 24 x 10 in, aluminum. (2) screws and (2) slot nuts included.

[WD106](#)

Din Rail			
Part Number	Price	Length (in)	For use with
AH6DR		4.9	AHx664xxx AHx864xxx
AH8DR		6.9	AHx864xxx AHx884xxx AHx108xxxx
AH10DR		8.9	AHx108xxxx AHxx1010xxxx AHxx1210xxxx
AH12DR		10.8	AHxx1210xxxx AHxx1412xxxx
AH14DR		12.8	AHxx1412xxxx AHxx1614xxxx
AH16DR		14.7	AHxx1614xxxx AHxx1816xxxx AHxx2016xxxx
AH18DR		16.7	AHxx1816xxxx
AH20DR		18.6	AHxx2016xxx
AH24DR		22.5	AHxx2424xxxx

[AH8DR](#)