

# Accessories

| DL05, DL06 and Option Module Accessories |                                                                                                                                                                  |       |
|------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|
| Part Number                              | Description                                                                                                                                                      | Price |
| <a href="#"><u>D0-MC-BAT</u></a>         | Replacement battery for Do-more H2 and T1H series CPU modules, and D0-01MC optional memory cartridge for DL05 PLCs.                                              |       |
| <a href="#"><u>D2-BAT-1</u></a>          | Replacement RAM retentive memory backup battery for the DL06.                                                                                                    |       |
| <a href="#"><u>F0-IOCON</u></a>          | DL05 or DL06 replacement terminal blocks, 8-position, for the F0-04AD-1, F0-04AD-2, F0-2AD2DA-2, F0-4AD2DA-1, F0-4AD2DA-2 and H0-CTRIO2 option modules (qty. 2). |       |
| <a href="#"><u>F0-IOCON-THM</u></a>      | DL05 or DL06 thermocouple option module replacement terminal block, quantity one.                                                                                |       |
| <a href="#"><u>D0-CBL</u></a>            | 12ft. (3.66m) RS-232C shielded networking cable without RTS connections for DL05 or DL06 RJ12 networking ports. Enables direct networking of two PLCs.           |       |
| <a href="#"><u>D0-ACC-1</u></a>          | DL05 accessory pack includes one each of the I/O terminal block, I/O terminal block cover, and option slot cover.                                                |       |
| <a href="#"><u>D0-ACC-2</u></a>          | DL06 replacement terminal blocks (qty. 2), terminal block covers (qty. 2), terminal block labels (qty. 2) and short bar (qty. 1).                                |       |
| <a href="#"><u>D0-ACC-3</u></a>          | DL06 replacement option module slot covers (qty. 4), DL06 top covers (qty. 4), and LCD slot cover.                                                               |       |
| <a href="#"><u>D0-ACC-4</u></a>          | DL05 or DL06 discrete I/O option module replacement terminal blocks, includes 13-position (qty. 2) and 10-position (qty. 2).                                     |       |
| <a href="#"><u>D2-FUSE-1</u></a>         | DL05 or DL06 F0-04TRS replacement fuse                                                                                                                           |       |
| <a href="#"><u>ZL-CMA15</u></a>          | <b>ZIPLink</b> PLC communication adapter for 15-pin port                                                                                                         |       |
| <a href="#"><u>ZL-CMA15L</u></a>         | <b>ZIPLink</b> PLC communication adapter for 15-pin port with surge protection plus Power, Transmit, and Receive LED indicators                                  |       |




ZL-CMA15




ZL-CMA15L

DL06 replacement terminal blocks, terminal block covers, terminal block labels and short bar  
[D0-ACC-2](#)



Discrete and analog option module terminal blocks  
[D0-ACC-4](#)



DL05 option module slot cover, I/O terminal block, and I/O terminal block cover  
[D0-ACC-1](#)



DL06 replacement option module slot covers, DL06 top covers, and LCD slot cover  
[D0-ACC-3](#)



See the Wiring Solutions section in this catalog for more information.