


# Pedestal Columns and Bases for Operator Consolets



WA44CCOL shown with optional base



WA44BPCOL shown with optional base

## Applications

Designed to permit floor-mounting of many types of enclosures and boxes. Four column and two base sizes are available. Columns can be mounted on either base. Wiring connections can be made through the base, through the vertical column, or directly to the enclosure. Columns have flanges at each end and a gasketed access plate. Screws, oil-resistant gaskets, and box connector fitting are furnished with each column for joining an enclosure to the top of the column. A cutout must be made in the enclosure if the wires are to come through the column.

## Construction

### Column

- Columns fabricated from 14-gauge steel with 10-gauge flanges
- Gasket, screws and connective fittings are furnished for mounting console
- Columns feature gasketed access plate

### Base

- 18" bases are fabricated from 10-gauge steel
- 24 in [610 mm] bases are fabricated from 7 gauge steel
- Both bases have added reinforcing, leveling screws and holes for securing to floor

## Finish

- Painted Steel: ANSI 61 gray polyester powder inside and out over phosphatized surfaces
- Stainless Steel: #3 intermediate polished finish

## Listings

- UL 508 12 and 13 [UL File E64791]



| Shipping Schedule                                    |            |            |           |             |             |
|--|------------|------------|-----------|-------------|-------------|
| Same day   | 1 - 5 days | 1 - 7 days | 1-10 days | 1 - 15 days | 1 - 20 days |
| Color indicates shipping lead time in business days. |            |            |           |             |             |

| Pedestal Columns and Bases for Operator Consolets |       |                 |         |             |                         |                                       |                          |
|---|-------|-----------------|---------|-------------|-------------------------|---------------------------------------|--------------------------|
| Painted Steel                                     | Price | Stainless Steel | Price   | Steel Gauge | Pedestal Size           | Pedestal or Base HxWxD                | Description              |
| WA44CCOL  | —     | WA44CCOLSS      | —       | 14          | 4.00 x 4.00 [102 x 102] | 35.00 x 4.00 x 4.00 [889 x 102 x 102] | Straight pedestal column |
| WA66CCOL  | —     | WA66CCOLSS      | —       | 14          | 6.00 x 6.00 [152 x 152] | 35.00 x 6.00 x 6.00 [889 x 152 x 152] | Straight pedestal column |
| WA44BPCOL   | —     | WA44BPCOLSS     | —       | 14          | 4.00 x 4.00 [102 x 102] | 43.8 x 4.00 x 4.00 [1113 x 102 x 102] | Angled pedestal column   |
| WA66BPCOL   | —     | WA66BPCOLSS     | —       | 14          | 6.00 x 6.00 [152 x 152] | 44.5 x 6.00 x 6.00 [1130 x 152 x 152] | Angled pedestal column   |
| WA18SBASE   | —     | WA18SBASESS     | Retired | 10          | —                       | 18.00 x 18.00 x 1.13 [457 x 457 x 29] | Pedestal base            |
| WA24SBASE   | —     | WA24SBASESS     | Retired | 7           | —                       | 24.00 x 24.00 x 1.31 [610 x 610 x 33] | Pedestal base            |

Notes: Dimensions in inches [millimeters].  
 Letters in table correspond to letters on dimensional drawings.  
 The user would normally remove the mounting feet from the enclosure if the enclosure is mounted on a pedestal.

# Pedestal Columns and Bases for Operator Consoles



## Dimensions

