

























Tools – Deburring Tools

Deburring Tools					
Part #	Pcs/ Pkg	Price	Description	Common Uses	
<u>107010</u>	1		Universal deburring Handle, with spare blade storage compartment	–	
<u>107011</u>	1		Steel blade holder for B blades	–	
<u>107012</u>	1		Deburring blade - B10	HSS blade most commonly used for internal and external deburring work on long-chipping materials such as steel, aluminum, plastics etc.	
<u>107014</u>	1		Deburring blade - B20	HSS blade used for short-chipping materials such as brass and cast iron. Can be used in both directions.	
<u>107015</u>	1		Deburring blade - B30	HSS blade suitable for the simultaneous deburring of inside and outside bores in material up to 5/32" thick.	
<u>107016</u>	1		Deburring blade - B50	Scriber with carbide-tipped point, regrindable.	
<u>107019</u>	1		Steel blade holder for C blades	–	
<u>107020</u>	1		Deburring blade - C40	Small HSS triangular scraper for precision work on surfaces up to 5/32" wide.	
<u>107021</u>	1		Deburring blade - C42	Large HSS triangular scraper for precision work on surfaces up to 5/16" wide.	
<u>107025</u>	1		Steel blade holder for E blades	–	
<u>107026</u>	1		Deburring blade - E100	HSS blade with B 10 cutting edge, long shank only. For internal and external deburring work on long-chipping materials such as steel, aluminum, plastics etc.	
<u>107027</u>	1		Deburring blade - E200	HSS blade with B 20 cutting edge, long shank only. For short-chipping materials such as brass and cast iron. Usable in both directions.	
<u>107028</u>	1		Deburring blade - E300	HSS blade with B 30 cutting edge, long shank only. For simultaneous deburring of internal and external bores in materials up to 5/32" thick.	
<u>107029</u>	1		Deburring blade - E350	HSS blade suitable for deburring straight edges, keyways etc.	
<u>107031</u>	1		Steel blade holder for F countersinks	–	
<u>107032</u>	1		Countersink F12	HSS countersink for deburring holes up to 1/2" Dia	
<u>107033</u>	1		Countersink F20	HSS countersink for deburring holes up to 3/4" Dia	
<u>107034</u>	1		Countersink F30	HSS countersink for deburring holes up to 1-3/16" Dia	
<u>107054</u>	1		Deburring tool with changeable E100 Blade	Internal and External deburring on long-chipping materials such as steel, aluminum and plastic.	



Tools – Deburring Tool Kits

Deburring Tool Kits					
Part #	Pcs/Pkg	Price	Description	Includes	
<u>107003</u>	1		Deburring Kit including Universal Handle, B Holder, B10 and B20 Blades	<u>107010</u> , <u>107011</u> , <u>107012</u> , <u>107014</u>	
<u>107004</u>	1		Deburring Kit including Universal Handle, C Holder, and C42 Blade	<u>107010</u> , <u>107019</u> , <u>107021</u>	
<u>107006</u>	1		Deburring Kit including Universal Handle, E Holder, E100, E200, and E300 Blades	<u>107010</u> , <u>107025</u> , <u>107026</u> , <u>107027</u> , <u>107028</u>	
<u>107007</u>	1		Deburring Kit including Universal Handle, F Holder and F20 Countersink	<u>107010</u> , <u>107031</u> , <u>107033</u>	