



Wera

Zyklop Speed Ratchet and Socket Sets

1/2 inch Drive Imperial Ratchet Sets



1/2 inch Drive Imperial Ratchet Sets			
Part Number	Description	Pcs/Pkg	Price Each
05003646055	Wera socket set with Zyklop Speed ratchet, 1/2 inch drive, SAE, 23 pieces, includes ratchet, 125 mm and 250 mm extensions with free-turning sleeves, 250 mm sliding T-handle, universal joint, (18) sockets (3/8, 7/16, 1/2, 9/16, 19/32, 5/8, 11/16, 3/4, 25/32, 13/16, 7/8, 15/16, 31/32, 1, 1-1/16, 1-1/8, 1-3/16 and 1-1/4 inch). Manufacturer part number: 003646. Sturdy metal case included.	1 set	
05003647055	Wera driver bit and socket set with Zyklop Speed ratchet, 1/2 inch drive, SAE, 38 pieces, includes ratchet, 125 mm and 250 mm locking extensions with free-turning sleeves, 250 mm sliding T-handle, universal joint, 52 mm wobble extension, 1/2 inch x 5/16 inch x 50 mm long bit adaptor, (18) sockets (3/8, 7/16, 1/2, 9/16, 19/32, 5/8, 11/16, 3/4, 25/32, 13/16, 7/8, 15/16, 31/32, 1, 1-1/16, 1-1/8, 1-3/16 and 1-1/4 inch), #3 Phillips bit, #3 Pozidriv bit, (4) Hex-Plus bits (7/32, 1/4, 5/16 and 3/8 inch), (7) Torx bits (TX20, TX25, TX30, TX40, TX45, TX50 and TX55). Manufacturer part number: 003647. Sturdy metal case included.	1 set	



Wera socket set with Zyklop Speed ratchet, 1/2 inch drive, SAE, 23 pieces. Includes the pieces listed in the table below.

05003646055 Ratchet Set Contents		
	1/2 Zyklop ratchet	
	Sliding T-handle	1/2 x 10
	6-point socket	3/8, 7/16, 1/2, 9/16, 19/32, 5/8, 11/16, 3/4, 25/32, 13/16, 7/8, 15/16, 31/32, 1, 1-1/16, 1-1/8, 1-3/16, 1-1/4
	Extension	1/2 x 10, 1/2 x 5
	Universal joint	1/2 x 2.7

Note: All dimensions are in inches.



Wera driver bit and socket set with Zyklop Speed ratchet, 1/2 inch drive, SAE, 38 pieces. Includes the pieces listed in the table below.

05003647055 Ratchet Set Contents		
	1/2 Zyklop ratchet	
	Sliding T-handle	1/2 x 10
	6-point socket	3/8, 7/16, 1/2, 9/16, 19/32, 5/8, 11/16, 3/4, 25/32, 13/16, 7/8, 15/16, 31/32, 1, 1-1/16, 1-1/8, 1-3/16, 1-1/4
	Wobble extension	1/2 x 2
	Universal joint	1/2 x 2.7
	Lockable extension	1/2 x 10, 1/2 x 5
	Bit adaptor	5/16 x 1/2 x 50.0
	Hex bit	7/32, 1/4, 5/16, 3/8
	Phillips bit	PH 3
	Pozidriv bit	PZ 3
	Torx® bit	TX 20, TX 25, TX 30, TX 40, TX 45, TX 50, TX 55


Wera

Zyklop Speed Ratchet and Socket Sets

1/2 inch Drive Metric Ratchet Sets



1/2 inch Drive Metric Ratchet Sets			
Part Number	Description	Pcs/Pkg	Price Each
05003644055	Wera socket set with Zyklop Speed ratchet, 1/2 inch drive, metric, 22 pieces, includes ratchet, 125 mm and 250 mm extensions with free-turning sleeves, 250 mm sliding T-handle, universal joint, (17) sockets (10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 24, 27, 30 and 32 mm). Manufacturer part number: 003644. Sturdy metal case included.	1 set	
05003645055	Wera driver bit and socket set with Zyklop Speed ratchet, 1/2 inch drive, metric, 37 pieces, includes ratchet, 125 mm and 250 mm locking extensions with free-turning sleeves, 250 mm sliding T-handle, universal joint, 52 mm wobble extension, 1/2 inch x 5/16 inch x 50 mm long bit adaptor, (17) sockets (10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 24, 27, 30 and 32 mm), #3 Phillips bit, #3 Pozidriv bit, (4) Hex-Plus bits (5, 6, 8 and 10 mm), (7) Torx bits (TX20, TX25, TX30, TX40, TX45, TX50 and TX55). Manufacturer part number: 003645. Sturdy metal case included.	1 set	



Wera socket set with Zyklop Speed ratchet, 1/2 inch drive, metric, 22 pieces. Includes the pieces listed in the table below.

05003644055 Ratchet Set Contents		
	1/2 Zyklop ratchet	
	Sliding T-handle	1/2 x 250
	6-point socket	10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 24, 27, 30, 32
	Extension	1/2 x 250, 1/2 x 125
	Universal joint	1/2 x 69

Note: Fractional dimensions are in inches.
Whole and decimal dimensions are in millimeters.



Wera driver bit and socket set with Zyklop Speed ratchet, 1/2 inch drive, metric, 37 pieces. Includes the pieces listed in the table below.

05003645055 Ratchet Set Contents		
	1/2 Zyklop ratchet	
	Sliding T-handle	1/2 x 250
	6-point socket	10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 24, 27, 30, 32
	Wobble extension	1/2 x 52
	Universal joint	1/2 x 69
	Lockable extension	1/2 x 250, 1/2 x 125
	Bit adaptor	5/16 x 1/2 x 50
	Hex bit	5, 6, 8, 10
	Phillips bit	PH 3
	Pozidriv bit	PZ 3
	Torx® bit	TX 20, TX 25, TX 30, TX 40, TX 45, TX 50, TX 55

Note: Fractional dimensions are in inches.
Whole and decimal dimensions are in millimeters.

Wera Ratchets



Zyklop Speed Ratchet




Small return angle

The fine 72 tooth ratchet mechanism has a low return angle of 5°. This short stroke allows fast and precise work in small spaces.



Swivel ratchet head


The ratchet head pivots freely and locks at 0°, 15° and 90°, making it possible to work in confined spaces with ample hand clearance.



Simple direction change

Rotating the large thumbwheel quickly changes rotation from clockwise to counterclockwise from any position of the ratchet head.

Wera Speed Ratchets			
Part Number	Description	Pcs/ Pkg	Price Each
05003500055	Wera Zyklop Speed ratchet, 1/4 inch drive, with locking swivel head and ergonomic grip handle.	1	
05003550055	Wera Zyklop Speed ratchet, 3/8 inch drive, with locking swivel head and ergonomic grip handle.	1	
05003600055	Wera Zyklop Speed ratchet, 1/2 inch drive, with locking swivel head and ergonomic grip handle.	1	



Unbelievably fast

The gyrating mass design along with the Kraftform handle and free-turning sleeve allow for rapid rotation when used as a screwdriver.