wiha Tool Sets

Tools that work for you

Screwdriver and Pliers Sets

Part Number	Number of Pieces	Part Image	Set Type	Pliers Type	Screwdriver Type	Tip Sizes	Set Includes	Price
WT26190	8		Screwdriver and pliers set	Long Nose	Philips	#00 #0 #	(7) precision screwdrivers (Phillips: #00, #0, #1, slotted: 1.5mm, 2.0mm, 2.5mm, 3.0mm), (1) 6.3in industrial long nose pliers	
					Slotted	1.5mm 2.0mm 3.0mm		
WT26191			Screwdriver and cutters set	Classic Diagonal	Philips	#00 #0 #1	(7) precision screwdrivers (Phillips #00, #0, #1, slotted 1.5mm, 2.0mm, 2.5mm, 3.0mm), (1) 5in classic grip precision diagonal cutters	
					Slotted	1.5mm 2.0mm 3.0mm		
WT32872	5		Screwdriver, pliers, and cutters set	Long Nose Diagonal	Philips	#2	(1) 6.3in diagonal cutters, (1) 8in long nose pliers, (3) insulated SoftFinished screwdrivers (slotted 3.0mm, 4.5, Phillips #2), belt pack pouch	
					Slotted	3.0mm 4.0mm		
WT32875			Screwdriver and pliers set	Lineman's Long Nose	Philips	#2	(1) 9.5in lineman's pliers, (1) 8in long nose pliers, (3) insulated SoftFinish screwdrivers (slotted 4.5mm, 6.5mm, Phillips #2), belt pack pouch	
					Slotted	4.5mm 6.5mm		
WT32984	6			Combination Long Nose	Philips	#2	(1) combination pliers 8in, (1) long nose pliers 8in, (4) insulated SoftFinish screwdrivers (slotted 3.0mm, 4.5mm, Phillips #2, square #2)	
					Slotted	3.0mm 4.5mm		
					Square	#2		
WT32985	7			Combination Long Nose Diagonal	Philips	#1 #2	(4) insulated SoftFinish screwdrivers (slotted 3.0mm, 4.5mm, Phillips #1, #2), (1) industrial long nose pliers 6.3in, (1) industrial combination pliers 8in, (1) industrial diagonal cutters 6.3in, belt pack pouch	
					Slotted	3.0mm 4.5mm		
WT32986	11			Long Nose Combination Diagonal Wire Stripping	Philips	#1 #2	(1) long nose pliers 6.3in, (1) combination pliers 8in, (1) diagonal cutters 6.3in, (1) stripping pliers 6.3in, (7) insulated SoftFinish screwdrivers (slotted 3.0mm, 4.5mm, 5.5mm, Phillips #1, #2, square #1, #2), roll-up tool pouch	
					Slotted	3.0mm 4.5mm 5.5mm		
					Square	#1 #2		