

PARTEX Tape Dispenser Wire Markers

Overview



The Partex PLD series marker tape dispenser cassette holds 10 rolls of self-adhesive wrap-style marking tape, with each roll containing approximately 475 pre-printed characters. Marker tape is well suited for both pre-wiring and post-connection labeling in the field. The snap hook on the cassette allows it to be attached to a belt or tool bag for convenient on-site use.

Tape is available in yellow or white vinyl (PVC) with black printing and a clear polyester laminate overlay that protects characters from scratches and moisture. Characters include numerals 0–9, letters A–C and L1–L3, and symbols including plus, minus, slash, ground, and blank. The rubber-based adhesive provides a secure bond across a service temperature range of -4 to +158 °F [-20 to +70 °C]. Individual rolls are sold separately as refill packs of two, allowing the reusable cassette to be restocked with any combination of characters as needed.

Features

- Continuous tape wraps around the cable for a secure, snug fit on any cable diameter
- Can be installed before or after wire termination for maximum installation flexibility
- Cassette holds 10 rolls and attaches to a belt or tool bag via snap hook for convenient on-site use
- Individual roll compartments open independently for quick character selection and easy roll replacement
- Metal serrated blade built into the cassette ensures clean, accurate tape cuts
- Each roll contains approximately 475 characters
- Yellow or white vinyl (PVC) tape with black printing on a permanent, rubber-based adhesive
- Clear polyester laminate overlay protects printed characters from scratches and moisture
- Moisture-resistant construction suitable for electrical cabinets, wiring closets, and similar enclosed environments
- Available in numerals, letters, phase markings (L1, L2, L3), symbols, and blank
- Service temperature range: -20 to +70 °C [-4 to +158 °F]
- RoHS compliant

Partex Tape Dispenser Wire Markers

Part Number	Price	Description	Tape Width	Tape Length
<u>PLD-CAS-1</u>	\$10.00	Empty Partex wire marker tape dispenser. (no labels included)	n/a	n/a
<u>PLD-CAS-WT-1</u>	\$29.00	Partex wire marker tape dispenser, numbered 0–9 (1 of each number), standard, black text, white background, PVC. Package of 1.	5mm [0.19in]	2.4m [7.8ft]
<u>PLD-CAS-YW-1</u>	\$29.00	Partex wire marker tape dispenser, numbered 0–9 (1 of each number), standard, black text, yellow background, PVC. Package of 1.		

PARTEX Tape Dispenser Wire Markers

Partex Tape Dispenser Wire Marker Refills

Part Number		Price	Character	Tape Color	Tape Width	Tape Length	Qty/Pack
PLD050CN40.BLK-2		\$5.50	Blank	Yellow	5mm [0.19in]	2.4m [7.8ft]	2
PLD050CN40.0-2		\$5.50	0	Black On Yellow			
PLD050CN40.1-2		\$5.50	1	Black On Yellow			
PLD050CN40.2-2		\$5.50	2	Black On Yellow			
PLD050CN40.3-2		\$5.50	3	Black On Yellow			
PLD050CN40.4-2		\$5.50	4	Black On Yellow			
PLD050CN40.5-2		\$5.50	5	Black On Yellow			
PLD050CN40.6-2		\$5.50	6	Black On Yellow			
PLD050CN40.7-2		\$5.50	7	Black On Yellow			
PLD050CN40.8-2		\$5.50	8	Black On Yellow			
PLD050CN40.9-2		\$5.50	9	Black On Yellow			
PLD050CN40.A-2		\$5.50	A	Black On Yellow			
PLD050CN40.B-2		\$5.50	B	Black On Yellow			
PLD050CN40.C-2		\$5.50	C	Black On Yellow			
PLD050CN40.GND-2		\$5.50	Ground ($\perp$)	Black On Yellow			
PLD050CN40.L1-2		\$5.50	L1	Black On Yellow			
PLD050CN40.L2-2		\$5.50	L2	Black On Yellow			
PLD050CN40.L3-2		\$5.50	L3	Black On Yellow			
PLD050CN40.MNS-2		\$5.50	Minus (-)	Black On Yellow			
PLD050CN40.PLUS-2		\$5.50	Plus (+)	Black On Yellow			
PLD050CN40.SLA-2		\$5.50	Slash (/)	Black On Yellow			
PLD050CN90.BLK-2		\$5.50	Blank	White	5mm [0.19in]	2.4m [7.8ft]	2
PLD050CN90.0-2		\$5.50	0	Black On White			
PLD050CN90.1-2		\$5.50	1	Black On White			
PLD050CN90.2-2		\$5.50	2	Black On White			
PLD050CN90.3-2		\$5.50	3	Black On White			
PLD050CN90.4-2		\$5.50	4	Black On White			
PLD050CN90.5-2		\$5.50	5	Black On White			
PLD050CN90.6-2		\$5.50	6	Black On White			
PLD050CN90.7-2		\$5.50	7	Black On White			
PLD050CN90.8-2		\$5.50	8	Black On White			
PLD050CN90.9-2		\$5.50	9	Black On White			
PLD050CN90.A-2		\$5.50	A	Black On White			
PLD050CN90.B-2		\$5.50	B	Black On White			
PLD050CN90.C-2		\$5.50	C	Black On White			
PLD050CN90.GND-2		\$5.50	Ground ($\perp$)	Black On White			
PLD050CN90.L1-2		\$5.50	L1	Black On White			
PLD050CN90.L2-2		\$5.50	L2	Black On White			
PLD050CN90.L3-2		\$5.50	L3	Black On White			
PLD050CN90.MNS-2		\$5.50	Minus (-)	Black On White			
PLD050CN90.PLUS-2		\$5.50	Plus (+)	Black On White			
PLD050CN90.SLA-2		\$5.50	Slash (/)	Black On White			