



# OKK Series Enclosure Kit – NEMA 12 Freestanding Double-Door



## Description

Each OKK Series enclosure kit contains all the components required to assemble one complete enclosure.

Kits do not include a plinth.

## Material

- 2.0 mm carbon steel

## Finish

- RAL 7035 light gray
- Textured powder coat finish

## Listings

- Fully-assembled OKK Series enclosures are rated as follows:
  - UL 508a Type 12 [UL File E503249]
  - CSA Type 12 [CSA File 115232]
- Complies with the following:
  - NEMA Type 12
  - IEC EN60529 IP55



Create your own configuration using the link button or QR code below:

### [Configuration Tool](#)



View assembly guide with the link button or QR code below:

### [Assembly Guide](#)



## OKK Series Enclosure Kit – NEMA12 Freestanding Double-Door

Kit Number	Price	Assembled Size HxWxD	Kit Includes	Drawing Link
<a href="#">QTA-E181204CDBF</a>	Retired	1800 x 1200 x 400 [70.87 x 47.24 x 15.75]	(1) MTK180-4, (1) OKKTB1240, (1) PNA18C, (1) DBE18C, (1) RPE18C and (1) DLK184	<a href="#">PDF</a>
<a href="#">QTA-E181206CDBF</a>	Retired	1800 x 1200 x 600 [70.87 x 47.24 x 23.62]	(1) MTK180-4, (1) OKKTB1260, (1) PNA18C, (1) DBE18C, (1) RPE18C and (1) DLK186	<a href="#">PDF</a>
<a href="#">QTA-E181208CDBF</a>	Retired	1800 x 1200 x 800 [70.87 x 47.24 x 31.50]	(1) MTK180-4, (1) OKKTB1280, (1) PNA18C, (1) DBE18C, (1) RPE18C and (1) DLK188	<a href="#">PDF</a>
<a href="#">QTA-E201204CDBF</a>	Retired	2000 x 1200 x 400 [78.74 x 47.24 x 15.75]	(1) MTK200-4, (1) OKKTB1240, (1) PNA20C, (1) DBE20C, (1) RPE20C and (1) DLK204	<a href="#">PDF</a>
<a href="#">QTA-E201206CDBF</a>	Retired	2000 x 1200 x 600 [78.74 x 47.24 x 23.62]	(1) MTK200-4, (1) OKKTB1260, (1) PNA20C, (1) DBE20C, (1) RPE20C and (1) DLK206	<a href="#">PDF</a>
<a href="#">QTA-E201208CDBF</a>	Retired	2000 x 1200 x 800 [78.74 x 47.24 x 31.50]	(1) MTK200-4, (1) OKKTB1280, (1) PNA20C, (1) DBE20C, (1) RPE20C and (1) DLK208	<a href="#">PDF</a>

Note: Dimensions in millimeters [inches].