
























# Tools – Deburring Tools

| Deburring Tools        |             |         |  |   |   |
|------------------------|-------------|---------|--|---|---|
| Part #                 | Pcs/<br>Pkg | Price   | Description  | Common Uses   |   |
| <a href="#">107010</a> | 1           | \$6.25  | Universal deburring Handle, with spare blade storage compartment | -   |    |
| <a href="#">107011</a> | 1           |         | Steel blade holder for B blades                                  | -   |    |
| <a href="#">107012</a> | 1           | \$11.50 | Deburring blade - B10  | HSS blade most commonly used for internal and external deburring work on long-chipping materials such as steel, aluminum, plastics etc.                       |    |
| <a href="#">107014</a> | 1           | \$11.50 | Deburring blade - B20  | HSS blade used for short-chipping materials such as brass and cast iron. Can be used in both directions.  |    |
| <a href="#">107015</a> | 1           | \$13.00 | Deburring blade - B30  | HSS blade suitable for the simultaneous deburring of inside and outside bores in material up to 5/32" thick.  |    |
| <a href="#">107016</a> | 1           | \$9.50  | Deburring blade - B50  | Scriber with carbide-tipped point, regrindable.   |    |
| <a href="#">107019</a> | 1           | \$4.00  | Steel blade holder for C blades                                  | -   |    |
| <a href="#">107020</a> | 1           | \$10.50 | Deburring blade - C40  | Small HSS triangular scraper for precision work on surfaces up to 5/32" wide.   |    |
| <a href="#">107021</a> | 1           | \$13.50 | Deburring blade - C42  | Large HSS triangular scraper for precision work on surfaces up to 5/16" wide.   |   |
| <a href="#">107025</a> | 1           | \$4.00  | Steel blade holder for E blades                                  | -   |  |
| <a href="#">107026</a> | 1           | \$13.00 | Deburring blade - E100   | HSS blade with B 10 cutting edge, long shank only. For internal and external deburring work on long-chipping materials such as steel, aluminum, plastics etc. |  |
| <a href="#">107027</a> | 1           | \$13.00 | Deburring blade - E200   | HSS blade with B 20 cutting edge, long shank only. For short-chipping materials such as brass and cast iron. Usable in both directions.                       |  |
| <a href="#">107028</a> | 1           | \$13.00 | Deburring blade - E300   | HSS blade with B 30 cutting edge, long shank only. For simultaneous deburring of internal and external bores in materials up to 5/32" thick.                  |  |
| <a href="#">107029</a> | 1           | \$13.00 | Deburring blade - E350   | HSS blade suitable for deburring straight edges, keyways etc.   |  |
| <a href="#">107031</a> | 1           | \$4.00  | Steel blade holder for F countersinks                            | -   |  |
| <a href="#">107032</a> | 1           | \$10.00 | Countersink F12  | HSS countersink for deburring holes up to 1/2" Dia  |  |
| <a href="#">107033</a> | 1           | \$17.00 | Countersink F20  | HSS countersink for deburring holes up to 3/4" Dia  |  |
| <a href="#">107034</a> | 1           | \$33.50 | Countersink F30  | HSS countersink for deburring holes up to 1-3/16" Dia   |  |
| <a href="#">107054</a> | 1           | \$10.00 | Deburring tool with changeable E100 Blade                        | Internal and External deburring on long-chipping materials such as steel, aluminum and plastic.   |  |

# Tools – Deburring Tool Kits

| Deburring Tool Kits           |         |         |   |   |  |
|-------------------------------|---------|---------|---|---|--|
| Part #                        | Pcs/Pkg | Price   | Description   | Includes  |  |
| <a href="#"><u>107003</u></a> | 1       | \$12.50 | Deburring Kit including Universal Handle, B Holder, B10 and B20 Blades          | <a href="#"><u>107010</u></a> , <a href="#"><u>107011</u></a> , <a href="#"><u>107012</u></a> , <a href="#"><u>107014</u></a>                                 |    |
| <a href="#"><u>107004</u></a> | 1       | \$26.00 | Deburring Kit including Universal Handle, C Holder, and C42 Blade               | <a href="#"><u>107010</u></a> , <a href="#"><u>107019</u></a> , <a href="#"><u>107021</u></a>   |    |
| <a href="#"><u>107006</u></a> | 1       | \$14.50 | Deburring Kit including Universal Handle, E Holder, E100, E200, and E300 Blades | <a href="#"><u>107010</u></a> , <a href="#"><u>107025</u></a> , <a href="#"><u>107026</u></a> , <a href="#"><u>107027</u></a> , <a href="#"><u>107028</u></a> |  |
| <a href="#"><u>107007</u></a> | 1       | \$29.00 | Deburring Kit including Universal Handle, F Holder and F20 Countersink          | <a href="#"><u>107010</u></a> , <a href="#"><u>107031</u></a> , <a href="#"><u>107033</u></a>   |  |