

# Enclosure Accessories



Your Enclosure Source®

## Hole Seals



SCE-LLB5

Extra pushbutton holes can be sealed against dust, dirt, oil, and water with a SCE hole seal. Seals will cover most pushbutton hole sizes. Hole seals come with oil-resistant gasket, #10-32 x 3/8" stud, zinc plated wing nut, and plated steel back plate. Available in stainless steel or powder coated finish.

- Made of heavy gauge steel with ANSI 61 gray powder coat.
- Stainless plate is made of Type 304 stainless with #4 brushed finish.
- NEMA Type 3R, 4, 4X & 12
- UL Recognized Type 3R, 4, 4X & 12 [File # E69392]
- IEC 60529
- IP 56

### Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

### Hole Seals

Part Number	Price	Material/Finish	Qty	Hole Size
<b>SCE-ASPBG-RAL7035</b>	\$3.75	Steel - RAL 7035 Gray	1	22mm pushbutton
<b>SCE-ASPB-RAL7035</b>	\$5.25	Steel - RAL 7035 Gray	1	30mm pushbutton
<b>SCE-ASPBG-09</b>	\$3.75	Steel - ANSI 61 Gray	1	22mm pushbutton
<b>SCE-ASPB-09</b>	\$5.25	Steel - ANSI 61 Gray	1	30mm pushbutton
<b>SCE-ASPBG-05</b>	\$3.75	Steel - SCE-05 White	1	22mm pushbutton
<b>SCE-ASPB-05</b>	\$5.25	Steel - SCE-05 White	1	30mm pushbutton
<b>SCE-ASPBG-SS</b>	\$18.25	Stainless Steel	1	22mm pushbutton
<b>SCE-ASPB-SS</b>	\$19.50	Stainless Steel	1	30mm pushbutton
<b>SCE-ASPBG-09-25</b>	\$83.00	Steel - ANSI 61 Gray	25	22mm pushbutton
<b>SCE-ASPB-09-25</b>	\$118.00	Steel - ANSI 61 Gray	25	30mm pushbutton

*Note: Dimensions in inches [millimeters].*

Designed to seal 2 inch square opening against dust, dirt, oil, and water. Hole seals are made of corrosion and UV resistant Polycarbonate material, supplied with adhesive gasket backing for quick, simple installation.

- UL Recognized 3, 3R, 4, 4X & 12
- IP56



### Square Hole Seal

Part Number	Price	Description	Drawing Link
<b>SCE-HS2S</b>	\$5.75	61 gray, oil-resistant adhesive gasket, 2in square cutout.	<a href="#">PDF</a>

*Note: Dimensions in inches [millimeters].*