

NEMA 12 and 13 Freestanding Work Stations



Your Enclosure Source®



Applications

Designed to house a computer, keyboard, monitor and other additional computer equipment in an industrial environment and provide a degree of protection from dust, oil and moisture.

Construction

- 14-gauge carbon steel or 304 stainless steel
- Seams continuously welded and ground smooth
- Poured-in place oil- and water-resistant gasket
- Flange trough collar around all sides of door opening
- Concealed hinges
- Removable doors
- Ground studs on door and body
- Large, polycarbonate viewing window in top door
- Lifting eyes for easy handling
- Rubber pads with provision for leveling pads on bottom of enclosure
- Black, 1/4-turn latches on top door
- Black, 1/4-turn wing knob latches on keyboard door
- Black, 3-point flush swing handle in lower front and back doors
- Gland plate on lower back of enclosure
- Pullout keyboard shelf with attached self-storing mouse shelf and mouse pad
- Mounting channels welded on sides of interior body for mounting optional subpanels, racks, mounting angles and shelves

Finish

- RAL 7035 gray powder coated inside and out or #4 brushed finish on all exterior surfaces for stainless steel

Listings

- NEMA Type 12 and 13
- cULus Listed Type 12 [File E69392]
- IEC 60529 IP55



Shipping Schedule

| | |
|----------|-------------|
| Same day | 1 - 15 days |
|----------|-------------|

Color indicates shipping lead time in business days.

NEMA 12 and 13 Carbon Steel Freestanding Work Stations

| Part Number | Price | Size HxWxD | Drawing Link | Top Depth | Optional Subpanel | Price |
|------------------------------|------------|--|---------------------|-------------|-----------------------------|---------|
| SCE-60P24WS | \$3,174.00 | 64.00 x 24.25 x 26.39 [1626 x 616 x 670] | PDF | 22.15 [563] | SCE-60P24WS | \$84.00 |
| SCE-642432WS | \$3,365.00 | 64.00 x 24.25 x 34.39 [1626 x 616 x 874] | PDF | 22.15 [563] | SCE-60P24WS | \$84.00 |

Note: Dimensions in inches [millimeters].

NEMA 12 and 13 Stainless Steel Freestanding Work Stations


| Part Number | Price | Size HxWxD | Drawing Link | Top Depth | Optional Subpanel | Price |
|--------------------------------|------------|--|---------------------|-------------|-----------------------------|---------|
| SCE-642424SSWS | \$5,555.00 | 64.00 x 24.25 x 26.39 [1626 x 616 x 670] | PDF | 22.15 [563] | SCE-60P24WS | \$84.00 |
| SCE-642432SSWS | \$5,768.00 | 64.00 x 24.25 x 34.39 [1626 x 616 x 874] | PDF | 22.15 [563] | SCE-60P24WS | \$84.00 |

Note: Dimensions in inches [millimeters].

NEMA 12 and 13 Freestanding Work Stations



Dimensions



Enclosure Accessories

Keyboard and Control Housings for Workstations




| Keyboard Housing | | | |
|-------------------------|----------|---|---------------------|
| Part Number | Price | For Use With | Drawing Link |
| SCE-KBH | \$339.00 | SCE-642424WS, SCE-642424SSWS, SCE-642432WS, SCE-642432SSWS, SCE-342424WS and SCE-342424SSWS | PDF |

Provides protection from dust, dirt, oil, and water for interior components when keyboard drawer is open. Mounts to mounting channels. Keyboard shelf with slides is mounted inside the housing. Hole grommet in rear provided for cords. Powder coated white. Mounting hardware included



| Pullout Keyboard Drawer | | | |
|---------------------------|----------|-----------------------|---------------------|
| Part Number | Price | For Workstation Depth | Drawing Link |
| SCE-KBS | \$495.00 | 24.25 [616] | PDF |
| SCE-KBS32 | \$495.00 | 32.25 [819] | PDF |

Designed to hold a keyboard and mouse on a separate Pullout shelf. Mounts between mounting channels. Made of heavy gauge steel with a white powder coat finish. A mouse pad is included. Drawer is included with workstation. Mounting hardware is included.




| Control Compartment | | | | |
|----------------------------|----------|---|---------------------|---------------------|
| Part Number | Price | For Use With | Material | Drawing Link |
| SCE-WSCC | \$393.00 | SCE-642424WS, SCE-642432WS and SCE-342424WS | carbon steel | PDF |
| SCE-WSCCSS | \$911.00 | | 304 stainless steel | PDF |

Designed to be mounted to the front of the workstation when installation of pushbuttons or control panels is desired. Installed after removing the Pullout keyboard drawer and door. Can be installed with the flat or sloped surface facing up. 20 degree slope on sloped surface. Gasket and mounting hardware included. Made of heavy gauge steel and powder coated RAL 7035 gray. Stainless steel part is made of Type 304 stainless steel with #4 brushed finish.



| Envioline Keyboard Housing | | | |
|----------------------------|----------|----------------------------------|---------------------|
| Part Number | Price | Size | Drawing Link |
| SCE-24KB | \$594.00 | 12.25 x 24 x 6 [311 x 610 x 152] | PDF |

Designed to house a keyboard input. Mounted on the outside of an enclosure. Envioline® type construction with ELJ hinge and mini quarter turn lever knobs. Mouse drawer. Made of heavy gauge steel and powder coated ANSI 61 gray. Provided with UL Recognized sealing washer to maintain Environmental Rating of the enclosure.



Enclosure Accessories



Your Enclosure Source®

Workstation Shelves

- Constructed of heavy gauge carbon steel
- Finished in white powder coat
- Mounting hardware included

| Pullout Shelf | | | | |
|---------------------------|----------|---------------------------|-----------------------|---------------------|
| Part Number | Price | Size WxD | For Workstation Depth | Drawing Link |
| SCE-20POS | \$339.00 | 19.50 x 20.00 [495 x 508] | 24.25 [616] | PDF |
| SCE-22POS | \$344.00 | 21.25 x 22.00 [540 x 559] | 26.00 [660] | PDF |
| SCE-26POS | \$348.00 | 19.50 x 28.00 [495 x 711] | 32.25 [819] | PDF |

Note: Dimensions in inches [millimeters].

Pullout shelves are designed to allow easy access to the back of equipment. Extends 19in and mounts between the mounting channels provided inside the workstation. Slides are included with shelf.



| Vented Pullout Shelf | | | | |
|-----------------------------|----------|---------------------------|-----------------------|---------------------|
| Part Number | Price | Size WxD | For Workstation Depth | Drawing Link |
| SCE-22VEPOS | \$436.00 | 21.25 x 22.00 [540 x 559] | 260. [660] | PDF |

Note: Dimensions in inches [millimeters].

Vented Pullout shelves are designed to allow easy access to the back of equipment and to allow air circulation inside the workstation. Extends 19in and mounts between the mounting channels provided inside the workstation. Slides are included with the shelf.



| Monitor Shelf | | | | |
|----------------------------|---------|--------------------------|------------|---------------------|
| Part Number | Price | Size WxD | Venting | Drawing Link |
| SCE-8STS | \$73.00 | 23.75 x 8.00 [603 x 203] | Non-vented | PDF |
| SCE-8VESTS | \$83.00 | 23.75 x 8.00 [603 x 203] | Vented | PDF |

Note: Dimensions in inches [millimeters].

Designed to support the monitor or other components in the upper section of the workstation. Available in vented and non-vented models. Vented shelf allows air circulation inside the workstation.



Enclosure Accessories



Workstation Shelves

- Constructed of heavy gauge carbon steel
- Finished in white powder coat
- Mounting hardware included

| Stationary Shelf | | | | |
|---------------------------|----------|---------------------------|---------------------------|---------------------|
| Part Number | Price | Size WxD | Used in Workstation Depth | Drawing Link |
| SCE-20STS | \$96.00 | 22.00 x 20.00 [559 x 508] | 24.25 [616] | PDF |
| SCE-22STS | \$101.00 | 23.75 x 22.00 [603 x 559] | 26.00 [660] | PDF |
| SCE-26STS | \$105.00 | 22.00 x 28.00 [559 x 711] | 32.25 [819] | PDF |

Note: Dimensions in inches [millimeters].

Designed to support monitors, PCs, printers or any other equipment. Mounts between the mounting channels provided inside the workstation.



| Vented Stationary Shelf | | | | |
|-----------------------------|----------|---------------------------|---------------------------|---------------------|
| Part Number | Price | Size WxD | Used in Workstation Depth | Drawing Link |
| SCE-20VESTS | \$232.00 | 22.00 x 20.00 [559 x 508] | 24.25 [616] | PDF |
| SCE-22VESTS | \$240.00 | 23.75 x 22.00 [603 x 559] | 26.00 [660] | PDF |
| SCE-26VESTS | \$250.00 | 22.00 x 28.00 [559 x 711] | 32.25 [819] | PDF |

Note: Dimensions in inches [millimeters].

Designed to support monitors, PCs, printers or any other equipment while allowing air circulation inside the workstation. Mounts between the mounting channels provided inside the workstation.



Enclosure Accessories

Workstation Accessories



- Made of heavy gauge steel
- Mounting hardware included

| Monitor Mounting System | | |
|---------------------------|---------|---------------------|
| Part Number | Price | Drawing Link |
| SCE-STMMK | \$71.00 | PDF |

Designed for direct mounting of a flat screen monitor to the workstation window door. Can be used with standard workstation or slope top workstation. Powder coated black texture.



| Blank Top Door | | | | |
|------------------------------|----------|---|--------------------------|---------------------|
| Part Number | Price | For Workstation | Material/Finish Color | Drawing Link |
| SCE-STWBTD | \$213.00 | SCE-66ST2626WS | carbon steel/white | PDF |
| SCE-STWSSBTD | \$633.00 | SCE-66ST2626SSWS | 304 stainless steel | PDF |
| SCE-WSBTD | \$339.00 | SCE-642424WS, SCE-642432WS and SCE-342424WS | carbon steel/RAL 7035 | PDF |
| SCE-WSSBTD | \$500.00 | SCE-642424SSWS, SCE-642432SSWS and SCE-342424SSWS | 304 stainless steel | PDF |

Designed to replace the top door when cutouts are desired. Poured-in-place oil- and water-resistant gasket. Installed by removing hinge pin. Black, 1/4-turn latches. Made of heavy gauge steel and powder coated. Stainless steel door is made of Type 304 stainless steel with #4 brushed finish. Mounting hardware is included.



[SCE-STWBTD](#)

Enclosure Accessories

Workstation Accessories



Pencil Edge/Palm Rest

| Part Number | Price | Material | Drawing Link |
|------------------------------|----------|---------------------|---------------------|
| SCE-STWSPL | \$45.00 | carbon steel | PDF |
| SCE-STWSPLSS | \$156.00 | 304 stainless steel | PDF |

Note: Dimensions in inches [millimeters].

Designed as a palm rest or retainer for the keyboard surface of the workstation. Carbon steel version is made of heavy gauge steel and powder coated white. Stainless steel part made of Type 304 stainless steel with #4 brushed finish. Mounting hardware is included.




[SCE-STWSPL](#)

Panel Support

| Part Number | Price | For Workstation Depth | Drawing Link |
|---------------------------|---------|-----------------------|---------------------|
| SCE-PSK24 | \$82.00 | 24.25 [616] | PDF |
| SCE-PSK32 | \$88.00 | 32.25 [819] | PDF |

Note: Dimensions in inches [millimeters].

Panel supports can be installed horizontally to the left and right side of enclosure. Allows easy installation of optional panels or rack mounting angles and channels to make them adjustable from front to back of the enclosure. Made of heavy gauge steel and powder coated white finish. Four per kit. Mounting hardware is included.



[SCE-PSK24](#)

Side Mount Plate

| Part Number | Price | Size HxW | For Workstation Depth | Drawing Link |
|-----------------------------|---------|---------------------------|-----------------------|---------------------|
| SCE-60P24WS | \$84.00 | 12.00 x 17.50 [305 x 445] | 24.25 [616] | PDF |
| SCE-60P32WS | \$96.00 | 12.00 x 25.50 [305 x 648] | 32.25 [819] | PDF |

Note: Dimensions in inches [millimeters].

Designed to provide extra mounting space on the inner sides of the enclosure. Can be securely attached to the mounting channels. Mounting hardware is included. Made of heavy gauge steel and powder coated white.



[SCE-60P24WS](#)

Enclosure Accessories

Workstation Pedestals and Bases



Your Enclosure Source®

| Pedestal | | | | |
|----------------------------|------------|--|---------------------|---------------------|
| Part Number | Price | Size HxWxD | Material | Drawing Link |
| SCE-PE22 | \$500.00 | 21.38 x 8.00 x 8.00 [543 x 203 x 203] | carbon steel | PDF |
| SCE-PE22SS | \$1,251.00 | 21.38 x 8.00 x 8.00 [543 x 203 x 203] | 304 stainless steel | PDF |

Note: Dimensions in inches [millimeters].

Designed to allow desktop workstations to be floor mounted. Gasket and hardware provided to attach to workstation. Made of heavy gauge steel and powder coated RAL 7035 gray. Stainless steel pedestal is made of Type 304 stainless steel.



[SCE-PE22](#)

| Pedestal Base | | | | |
|--------------------------------|------------|--|---------------------|---------------------|
| Part Number | Price | Size HxWxD | Material | Drawing Link |
| SCE-24PEBASE | \$747.00 | 10.00 x 24.00 x 24.00 [254 x 610 x 610] | carbon steel | PDF |
| SCE-24PEBASESS | \$1,869.00 | 10.00 x 24.00 x 24.00 [254 x 610 x 610] | 304 stainless steel | PDF |

Note: Dimensions in inches [millimeters].

Designed to mount pedestal to the floor. Made of heavy gauge steel and powder coated RAL 7035 gray. Stainless steel base is made of Type 304 stainless steel. Mounting hardware is included.



[SCE-24PEBASE](#)

| Carbon Steel Workstation Plinth Base | | | | |
|--------------------------------------|----------|---|---|---------------------|
| Part Number | Price | Size HxWxD | For Use With | Drawing Link |
| SCE-P2424WS | \$226.00 | 4.00 x 24.25 x 24.25 [102 x 616 x 616] | SCE-642424WS and SCE-342424WS workstation | PDF |
| SCE-P2626WS | Retired | 4.00 x 26.00 x 26.00 [102 x 660 x 660] | SCE-66ST2626WS workstation | PDF |
| SCE-P2432WS | \$263.00 | 4.00 x 32.25 x 24.25 [102 x 819 x 616] | SCE-642432WS workstation | PDF |

Note: Dimensions in inches [millimeters].

Designed to install under an enclosure to provide space for cables to enter from below and raise the enclosure up off the floor. Each plinth base is 4 inches high. Plinth bases are stackable to acquire desired height off the floor. Made of heavy gauge steel and finished with black textured powder coat. Stainless steel parts are made of type 304 stainless steel with #4 brushed finish.

| Workstation Plinth Base | | | | |
|-------------------------------|----------|---|---|---------------------|
| 304 Stainless Steel | Price | Size HxWxD | For Use With | Drawing Link |
| SCE-P2424SSWS | \$684.00 | 4.00 x 24.25 x 24.25 [102 x 616 x 616] | SCE-642424SSWS and SCE-342424SSWS workstation | PDF |
| SCE-P2626SSWS | Retired | 4.00 x 26.00 x 26.00 [102 x 660 x 660] | SCE-66ST2626SSWS workstation | PDF |
| SCE-P2432SSWS | \$782.00 | 4.00 x 32.25 x 24.25 [102 x 819 x 616] | SCE-642432SSWS workstation | PDF |

Note: Dimensions in inches [millimeters].



[SCE-P2424WS](#)