

# NEMA 4,12, and 13 Pushbutton Console



Your Enclosure Source®



## Applications

Designed to offer protection for all standard brands of oil-tight pushbuttons, switches, and pilot lights where slanted surfaces are desired. It offers protection from dust, dirt, oil and water.

## Construction

- 16 gauge carbon steel.
- Continuously-welded seams.
- Captivated cover screws thread into sealed wells.
- 4-way pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights
- Hole diameter is 1.20in [30.5 mm] or 0.87in [22.5].
- Fully-removable cover.
- Poured-in-place oil- and water-resistant gasket.
- Mounting feet included.
- Provisions for subpanel.

## Finish

- ANSI 61 gray powder coated inside and out.
- Optional subpanels powder coated white.

## Listings

- NEMA Type 4, 12, and 13
- cULus Listed Type 4 and 12 [File E69392]
- IEC 60529 IP66



### Shipping Schedule

Same day 1 - 15 days

Color indicates shipping lead time in business days.

## NEMA 4, 12, and 13 Pushbutton Console

22mm	30mm	Price	Size HxWxD	Holes	Drawing Link	Optional Subpanel	Price
<b>SCE-1PBAI</b>	<b>SCE-1PBA</b>	\$65.00	4.08 x 3.56 x 5.08 [104 x 90 x 129]	1	PDF	—	—
<b>SCE-2PBAI</b>	<b>SCE-2PBA</b>	\$75.00	4.08 x 5.81 x 5.08 [104 x 148 x 129]	2	PDF	—	—
<b>SCE-3PBAI</b>	<b>SCE-3PBA</b>	\$85.00	4.08 x 8.06 x 5.08 [104 x 205 x 129]	3	PDF	—	—
<b>SCE-4PBAI</b>	<b>SCE-4PBA</b>	\$97.00	4.08 x 10.31 x 5.08 [104 x 262 x 129]	4	PDF	—	—
<b>SCE-4SPBAI</b>	<b>SCE-4SPBA</b>	\$108.00	7.32 x 6.56 x 6.95 [186 x 167 x 177]	4	PDF	<b>SCE-6P6</b>	\$3.50
<b>SCE-6PBAI</b>	<b>SCE-6PBA</b>	\$125.00	7.32 x 8.81 x 6.95 [186 x 224 x 177]	6	PDF	<b>SCE-8P6</b>	\$4.00
<b>SCE-8PBAI</b>	<b>SCE-8PBA</b>	\$142.00	7.32 x 11.06 x 6.95 [186 x 281 x 177]	8	PDF	<b>SCE-10P6</b>	\$5.00
<b>SCE-9PBAI</b>	<b>SCE-9PBA</b>	\$158.00	7.32 x 13.31 x 6.95 [186 x 338 x 177]	10	PDF	<b>SCE-12P6</b>	\$5.50
<b>SCE-10PBAI</b>	<b>SCE-10PBA</b>	\$148.00	9.27 x 8.81 x 8.07 [235 x 224 x 205]	9	PDF	<b>SCE-8P8</b>	\$5.00
<b>SCE-12PBAI</b>	<b>SCE-12PBA</b>	\$172.00	7.32 x 15.56 x 6.95 [186 x 395 x 177]	12	PDF	<b>SCE-14P6</b>	\$6.00
<b>SCE-12SPBAI</b>	<b>SCE-12SPBA</b>	\$164.00	11.22 x 8.81 x 9.21 [285 x 224 x 234]	12	PDF	<b>SCE-10P8</b>	\$6.00
<b>SCE-16PBAI</b>	<b>SCE-16PBA</b>	\$183.00	11.22 x 11.06 x 9.21 [285 x 281 x 234]	16	PDF	<b>SCE-10P10</b>	\$7.00

Note: Dimensions in inches [millimeters]

# NEMA 4,12, and 13 Pushbutton Console



## Dimensions

