

# NEMA 4, 4X, 12, and 13 22mm Stainless Steel Wall-Mount Pushbutton



## Applications

Designed to offer protection for oil-tight pushbuttons, switches, and pilot lights in wet and hosed down areas and in corrosive atmospheres.

## Construction

- 16 gauge stainless steel Type 304 and 316/316L.
- Continuously welded seams.
- Captivated cover screws thread into sealed wells.
- 4-way pushbutton holes accept all brands of oil-tight pushbuttons, switches and pilot lights.
- Hole diameter is 0.87in [22.5 mm].
- Fully-removable cover.
- Poured-in-place oil- and water-resistant gasket.
- Welded mounting provision top and bottom of back.

## Finish

- #4 brushed finish on all exterior surfaces.

## Listings

- NEMA Type 4, 4X, 12, and 13
- cULus Listed Type 4, 4X, and 12 [File E69392]
- IEC 60529 IP66



### Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

### 22mm NEMA 4, 4X, 12, and 13 Stainless Steel Wall-Mount Pushbutton

304 Stainless Steel	Price	316L Stainless Steel	Price	Size HxWxD	Holes	Drawing Link
<b>SCE-1PBSSI</b>	\$105.00	<b>SCE-1PBSS6I</b>	\$126.00	3.81 x 3.56 x 2.91 [97 x 90 x 74]	1	<a href="#">PDF</a>
<b>SCE-1PBXSSI</b>	\$140.00	<b>SCE-1PBXSS6I</b>	\$168.00	4.31 x 4.31 x 4.91 [109 x 109 x 125]	1	<a href="#">PDF</a>
<b>SCE-2PBSSI</b>	\$132.00	<b>SCE-2PBSS6I</b>	\$158.00	6.06 x 3.56 x 2.91 [154 x 90 x 74]	2	<a href="#">PDF</a>
<b>SCE-3PBSSI</b>	\$143.00	<b>SCE-3PBSS6I</b>	\$172.00	8.31 x 3.56 x 2.91 [211 x 90 x 74]	3	<a href="#">PDF</a>
<b>SCE-4PBSSI</b>	\$162.00	<b>SCE-4PBSS6I</b>	\$195.00	10.56 x 3.56 x 2.91 [268 x 90 x 74]	4	<a href="#">PDF</a>
<b>SCE-4PBXSSI</b>	\$193.00	<b>SCE-4PBXSS6I</b>	\$232.00	10.31 x 4.31 x 4.91 [262 x 109 x 125]	4	<a href="#">PDF</a>
<b>SCE-4SPBSSI</b>	\$178.00	<b>SCE-4SPBSS6I</b>	\$214.00	7.56 x 6.56 x 3.16 [192 x 167 x 80]	4	<a href="#">PDF</a>
<b>SCE-6PBSSI</b>	\$213.00	<b>SCE-6PBSS6I</b>	\$256.00	9.81 x 6.56 x 3.16 [249 x 167 x 80]	6	<a href="#">PDF</a>
<b>SCE-9PBSSI</b>	\$241.00	<b>SCE-9PBSS6I</b>	\$289.00	9.81 x 8.81 x 3.16 [249 x 224 x 80]	9	<a href="#">PDF</a>
<b>SCE-12PBSSI</b>	\$275.00	<b>SCE-12PBSS6I</b>	\$330.00	12.06 x 8.81 x 3.16 [306 x 224 x 80]	12	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters]

# 22mm NEMA 4, 12, and 13 Stainless Steel Wall-Mount Pushbutton



## Dimensions

