

# Small RHC Series NEMA 1 and 3R Hinge-Cover Wall Mount



## Construction

- Bodies and doors fabricated from 16 gauge carbon steel
- Continuous hinge
- Hinge is made of carbon steel with a stainless steel hinge pin
- Lid is supplied with a padlockable draw latch
- Weldnuts provided for mounting optional back panels
- External mounting plates, top and bottom of enclosure
- Grounding provisions provided

## Finish

- ANSI 61 gray polyester powder light texture inside and out over phosphatized surfaces

## Listings

- UL 50, Types 1 & 3R [UL File E6924]
- NEMA/EEMAC Type 1 & 3R



## Applications

Designed for use as wiring boxes and junction boxes, these enclosures provide protection against rain, sleet and snow in outdoor installations, or against dripping water indoors.


Enclosure Shipping Schedule					
Same day	1 - 5 days	1 - 7 days	1 -10 days	1 - 15 days	1 - 20 days

Color indicates shipping lead time in business days.


Small RHC Series NEMA 1 and 3R Hinge-Cover Wall Mount						
Part Number	Price	Enclosure Size HxWxD	Knockout Pattern	Painted Steel Subpanel	Galvanized Subpanel	Perforated Subpanel
RHC060604	\$44.00	6.40 x 6.19 x 4.31 [163 x 157 x 109]	G-F-G	N1P0606	N1P0606G	N1P0606PP
RHC060804	\$49.00	8.40 x 6.19 x 4.31 [213 x 157 x 109]	G-F-G	N1P0608	N1P0608G	N1P0608PP
RHC080804	\$58.00	8.40 x 8.19 x 4.31 [213 x 208 x 109]	G-F-G	N1P0808	N1P0808G	N1P0808PP
RHC080806	\$62.00	8.40 x 8.19 x 6.31 [213 x 208 x 160]	G-F-G	N1P0808	N1P0808G	N1P0808PP
RHC081006	\$68.00	10.40 x 8.19 x 6.31 [264 x 208 x 160]	G-F-G	N1P0810	N1P0810G	N1P0810PP
RHC101206	\$83.00	12.40 x 10.19 x 6.13 [315 x 259 x 160]	G-F-G	N1P1012	N1P1012G	N1P1012PP
RHC121206	\$91.00	12.40 x 12.19 x 6.31 [315 x 310 x 160]	F-G-H-I-G	N1P1212	N1P1212G	N1P1212PP

**Note: Subpanels must be ordered separately.**  
 Dimensions in inches [millimeters]  
 Letters in table correspond to letters on dimensional drawings.


## Dimensions in [mm]



KNOCKOUT PATTERN (CENTERED IN WIDTH)



F = 3/4" X 1" CONCENTRIC KO  
 G = 1/2" X 3/4" CONCENTRIC KO  
 H = 1" SOLID KO  
 I = 1-1/4" SOLID KO



Grounding Kit		
Part Number	Description	Price
WGNDKT	Grounding Kit	\$2.50

**Note: Field grounding kit includes necessary parts to properly ground enclosure**

See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.