



Ultrasonic Liquid Level Sensor Accessories


Ultrasonic Liquid Level Sensor Accessories					
Part No.	Item Photo	Description	Quantity	Weight	Price
LI40-1001		Flowline PodView general purpose digital indicator, displays tank level or volume and sensor relay status, 6-digit LCD display with four relay status indicators, 3-button user interface, polycarbonate panel mount enclosure with NEMA 4 (IP65) faceplate, 6-foot (1.8-meter) 22AWG 4-conductor cable, compatible with any Flowline EchoPod series ultrasonic level sensor with firmware V50 or later	1	0.6	\$195.00
LM50-1001		Flowline side mount bracket, 2 inch NPT female threads, polypropylene (PP), for use with Flowline DL34, LU20, LU23, LU28, LU29, LU74, LU78, LU81, LU83, and LU84 series ultrasonic level sensors	1	0.4	\$32.00
LM50-1001-1		Flowline side mount bracket, 2 inch NPT female threads, polypropylene (PP), and 2 inch NPT male x 1 inch NPT female reducer bushing (PVC), for use with Flowline DL14, DL24, DS14, DL10, DX10, LU27, LU77, and LU80 series ultrasonic level sensors	1	0.6	\$41.00
LM52-1400		Flowline reducer bushing, 2 inch NPT male x 1 inch NPT female threads, PVC, for use with Flowline DL14, DL24, DS14, DL10, DX10, LU27, LU77, and LU80 series ultrasonic level sensors	1	0.2	\$13.00
LM52-2400		Flowline reducer bushing, 3 inch NPT male x 2 inch NPT female threads, PVC, for use with Flowline DL34, LU20, LU23, LU28, LU29, LU74, LU78, LU81, LU83, and LU84 series ultrasonic level sensors	1	0.6	\$29.00
LM52-1890		Flowline low-profile bulkhead fitting, 1 inch NPT female x slip socket, with mounting nut, PVC, for use with Flowline DL14, DL24, DS14, DL10, DX10, LU27, LU77 and LU80 series ultrasonic level sensors	1	0.5	\$41.00
LM52-2890		Flowline low-profile bulkhead fitting, 2 inch NPT female x slip socket, with mounting nut, PVC, for use with Flowline DL34, LU20, LU23, LU28, LU29, LU74, LU78, LU81, LU83, and LU84 series ultrasonic level sensors	1	1.2	\$69.00
LM52-1850		Flowline mounting flange, 1 inch NPT female threads, PVC, for use with Flowline DL14, DL24, DS14, DL10, DX10, LU27, LU77, and LU80 series ultrasonic level sensors	1	0.5	\$41.00
LM52-2850		Flowline mounting flange, 2 inch NPT female threads, PVC, for use with Flowline DL34, LU20, LU23, LU28, LU29, LU74, LU78, LU81, LU83, and LU84 series ultrasonic level sensors	1	1.0	\$60.00
204038		Replacement mounting gasket, for use with Flowline DL14, DL10, DX10, and DS14 series ultrasonic level sensors	1	0.1	\$5.00
200128		Replacement mounting gasket, for use with Flowline DL24, LU27, LU77, and LU80 series ultrasonic level sensors	1	0.1	\$9.00
200129		Replacement mounting gasket, for use with Flowline DL34, LU23, LU28, LU29, LU74, LU78, LU81, LU83, and LU84 series ultrasonic level sensors	1	0.1	\$13.00

When installing the 1" NPT level sensors care should be used to mechanically isolate the sensor housing from the tank. This can easily be done by using any of the Flowline mounting accessories which are designed to provide the isolation needed.


Dimensions

inches [mm]

LM50-1001



LM50-1001-1




Ultrasonic Liquid Level Sensor Accessories


Dimensions

inches [mm]


LM52-1400




LM52-2400




LM52-1890



LM52-2890



LM52-1850



LM52-2850

