

WERMA SIGNALTECHNIK Optical Signal Devices

57/58mm Base Mount Beacons

Features

- Choose from permanent incandescent, permanent LED, or flashing Xenon model
- Base mount installation
- 57 and 58mm diameters
- Light-intensive Xenon flash in flash models
- Bulb not included on incandescent models
- 2 year warranty



200, 201 and 202 Series Beacons Technical Specifications

Part Number	Price	Color	Drawing Link	Description	Voltage	Current	Starting Current	Operating Temp /Protection	Life Duration	Housing Material	Weight g [oz]	Connection	Agency Approvals
35.5 mm Base Mount													
20010000	\$16.50	Red	PDF	Incandescent Permanent Light 57mm	12-240 V AC/DC max (depends on bulb selection; bulb sold separately)	Depends on bulb selection. (Bulb sold separately)	-		up to 5,000h		50 [1.76]		
20020000	\$16.50	Green	PDF										
20030000	\$16.50	Yellow	PDF										
20040000	\$16.50	Clear	PDF										
20050000	\$16.50	Blue	PDF										
20110067	\$75.00	Red	PDF	LED Permanent Light 58mm	115VAC	< 25mA	≤ 0.5 A	-4 to 122°F [-20 to 50°C] IP65	up to 100,000h	Polycarbonate cap Polyamide base	66 [2.33]	Up to 2.5 mm ² Screwless CAGE CLAMP® - technology (8-14 AWG)	cULus file E164155, CE, RoHS
20120067	\$75.00	Green	PDF										
20130067	\$75.00	Yellow	PDF										
20140067	\$105.00	Clear	PDF										
20150067	\$114.00	Blue	PDF										
20110075	\$60.00	Red	PDF										
20120075	\$60.00	Green	PDF										
20130075	\$60.00	Yellow	PDF										
20140075	\$118.00	Clear	PDF										
20150075	\$118.00	Blue	PDF										
20210055	\$96.00	Red	PDF	Xenon Flashing Light (0.75 Hz flash frequency, 1W flash energy) 58mm	24VDC	< 100mA	-		4,000,000 flashes		82 [2.89]		
20220055	\$102.00	Green	PDF										
20230055	\$96.00	Yellow	PDF										
20240055	\$102.00	Clear	PDF										
20250055	\$102.00	Blue	PDF										
20210067	\$96.00	Red	PDF		115VAC	< 20mA	-						
20220067	\$102.00	Green	PDF										
20230067	\$96.00	Yellow	PDF										
20240067	\$102.00	Clear	PDF										
20250067	\$102.00	Blue	PDF										

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at www.AutomationDirect.com

Bulbs



Bulbs for Incandescent Permanent Optical Element					
Part Number	Price	Description	Wattage	Voltage	Life Duration
95584035	\$8.00	Bulb for Incandescent Light BA15d Bayonet Socket	5W	24VDC	up to 5,000h
95584038	\$8.00			230VAC	
95584057	\$8.00			115VAC	



Optical Signal Devices

Beacon Accessories

WERMA Beacons Accessories						
Part Number	Price	Drawing Link	Description	Operating Temp.	Material	Weight
Installation Beacon Accessories						
97581201	\$14.00	PDF	Tube adapter for beacons with 37mm (PG29) mounting installation. Find tube adapter accessories in WERMA Stack light catalog section.	-4 to 122°F [-20 to 50°C]	Polyamide / Fiberglass	1.13 g [0.04 oz]
97581202	\$13.50	PDF	Surface mounting base for beacons with 37mm (PG29) mounting installation		Polyamide / Fiberglass with rubber seal	2.83 g [0.1 oz]
97581503	\$42.50	PDF	Surface mounting enclosure for 1 beacon with 37mm (PG29) mounting installation		Polycarbonate/ ABS blend	8.5 g [0.3 oz]
97581507	\$59.00	PDF	Surface mounting enclosure for 2 beacons with 37mm (PG29) mounting installation			14.17 g [0.5 oz]
97581508	\$77.00	PDF	Surface mounting enclosure for 3 beacons with 37mm (PG29) mounting installation			17g [0.6 oz]
97581522	\$5.50	PDF	Anti-twist washer for beacons with 37mm (PG29) mounting installation		304 Stainless steel	0.57 g [0.02 oz]
Freestanding Beacon Accessories						
96000001	\$16.50	PDF	Bracket for tube mounting - for use with for use with 219 and 209 series industrial signal beacons.	-4 to 122°F [-20 to 50°C]	Polyamide	57g [2.01 oz]
97520901	\$19.50	PDF	Plastic Base with integrated tube for WERMA industrial signal beacons- for use with 209 and 219 series beacons		Polyamide	0.1 lbs [1.6 oz]
97520902	\$5.50	PDF	Cable gland for WERMA industrial signal beacons: M25x1.5, plastic - for use with 209 and 219 series industrial signal beacons		Nylon	0.1 lbs [1.6 oz]
97582603	\$41.50	PDF	Galvanized Wire Guard for WERMA industrial signal beacons - for use with 826, 827, 828 and 829 series industrial signal beacons		Wire D 3mm, chromed	140g [4.93 oz]
97582605	\$9.75	PDF	Plastic Bracket for wall mounting for use with WERMA signal beacons - for use with 826, 827, 828 and 829 series industrial signal beacons		Polycarbonate/ ABS blend	62g [2.19 oz]

