

WERMA SIGNALTECHNIK Optical Signal Devices

57/58 mm Tube Mount Beacons (Tall Lens)

Features

- Beacon with tall lens
- Choose from permanent incandescent, permanent LED, or flashing Xenon models
- Tube mount installation 57 and 58 mm diameters
- Light-intensive Xenon flash in flash models
- Bulb not included with incandescent models
- Various mounting accessories available
- 2 year warranty



219 Series 57/58 mm Beacons Technical Specifications

Part Number	Price	Color	Drawing Link	Description	Voltage	Current	Starting Current	Operating Temp /Protection	Life Duration	Housing Material	Weight g [oz]	Connection	Agency Approvals
M25x1.5 (Tube Mount)													
21910000	\$22.50	Red	PDF	Incandescent Permanent Light 57mm	12-240V AC/DC max (depends on bulb selection; bulb sold separately)	Depends on bulb selection. (Bulb sold separately)	-		up to 5,000h		67 [2.37]		Max. 2.5 mm ² Screwless CAGE CLAMP® - technology (18-14 AWG) cULus file E164155, CE, RoHS
21920000	\$22.50	Green	PDF										
21930000	\$22.50	Yellow	PDF										
21940000	\$22.50	Clear	PDF										
21950000	\$22.50	Blue	PDF	LED Permanent Light 58mm	115VAC	< 25mA	≤ 0.5A	-4 to 122°F [-20 to 50°C] IP65 when mounted	up to 100,000h	Polycarbonate cap Polyamide base	84 [2.96]		
21911067	\$90.00	Red	PDF										
21921067	\$90.00	Green	PDF										
21931067	\$90.00	Yellow	PDF										
21941067	\$134.00	Clear	PDF										
21951067	\$134.00	Blue	PDF										
21911075	\$75.00	Red	PDF	24V AC/DC	< 45mA								
21921075	\$75.00	Green	PDF										
21931075	\$75.00	Yellow	PDF	Xenon Flashing Light (1Hz flash frequency, 1W flash energy) 58mm	24VDC	< 100mA			4,000,000 flashes		100 [3.52]		
21942055	\$113.00	Clear	PDF										
21952055	\$113.00	Blue	PDF										
21912067	\$105.00	Red	PDF		115VAC	< 20mA							
21932067	\$105.00	Yellow	PDF										
21942067	\$113.00	Clear	PDF										
21952067	\$113.00	Blue	PDF										

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page at www.AutomationDirect.com

Bulbs



Bulbs for Incandescent Permanent Optical Element					
Part Number	Price	Description	Wattage	Voltage	Life Duration
95501535	\$8.00	Bulb for Incandescent Light BA15d Bayonet Socket	7W	24V AC/DC	up to 5,000h
95501537	\$8.00			115VAC	
95501538	\$8.00			230VAC	



Optical Signal Devices

Beacon Accessories

WERMA Beacons Accessories						
Part Number	Price	Drawing Link	Description	Operating Temp.	Material	Weight
Installation Beacon Accessories						
97581201	\$14.00	PDF	Tube adapter for beacons with 37mm (PG29) mounting installation. Find tube adapter accessories in WERMA Stack light catalog section.	-4 to 122°F [-20 to 50°C]	Polyamide / Fiberglass	1.13 g [0.04 oz]
97581202	\$13.50	PDF	Surface mounting base for beacons with 37mm (PG29) mounting installation		Polyamide / Fiberglass with rubber seal	2.83 g [0.1 oz]
97581503	\$42.50	PDF	Surface mounting enclosure for 1 beacon with 37mm (PG29) mounting installation		Polycarbonate/ ABS blend	8.5 g [0.3 oz]
97581507	\$59.00	PDF	Surface mounting enclosure for 2 beacons with 37mm (PG29) mounting installation			14.17 g [0.5 oz]
97581508	\$77.00	PDF	Surface mounting enclosure for 3 beacons with 37mm (PG29) mounting installation			17g [0.6 oz]
97581522	\$5.50	PDF	Anti-twist washer for beacons with 37mm (PG29) mounting installation		304 Stainless steel	0.57 g [0.02 oz]
Freestanding Beacon Accessories						
9600001	\$16.50	PDF	Bracket for tube mounting - for use with for use with 219 and 209 series industrial signal beacons.	-4 to 122°F [-20 to 50°C]	Polyamide	57g [2.01 oz]
97520901	\$19.50	PDF	Plastic Base with integrated tube for WERMA industrial signal beacons- for use with 209 and 219 series beacons		Polyamide	0.1 lbs [1.6 oz]
97520902	\$5.50	PDF	Cable gland for WERMA industrial signal beacons: M25x1.5, plastic - for use with 209 and 219 series industrial signal beacons		Nylon	0.1 lbs [1.6 oz]
97582603	\$41.50	PDF	Galvanized Wire Guard for WERMA industrial signal beacons - for use with 826, 827, 828 and 829 series industrial signal beacons		Wire D 3mm, chromed	140g [4.93 oz]
97582605	\$9.75	PDF	Plastic Bracket for wall mounting for use with WERMA signal beacons - for use with 826, 827, 828 and 829 series industrial signal beacons		Polycarbonate/ ABS blend	62g [2.19 oz]

