

# Table of Contents

---

## Chapter 1: Getting Started

<b>Introduction</b> .....	<b>1-2</b>
DL405 Handheld Programmer .....	1-2
Purpose of this manual .....	1-2
Who should read this manual .....	1-2
Supplemental Manuals .....	1-2
Technical Assistance .....	1-2
Manual Layout .....	1-3
<b>How can I use the Handheld?</b> .....	<b>1-4</b>
As a Programming Tool .....	1-4
To Monitor Machine Operations .....	1-4
As a Debugging Tool .....	1-5
As a Low-Cost Message Display .....	1-5
<b>Physical Characteristics and Specifications</b> .....	<b>1-6</b>
Handheld Layout .....	1-6
Connection Options .....	1-6
Specifications .....	1-7
<b>Keypad Layout</b> .....	<b>1-8</b>
Four Groups of Keys .....	1-8
Instruction Keys .....	1-9
Instruction Identifier Keys .....	1-9
Numeric Keys .....	1-9
Editing / Monitoring Keys .....	1-9

## Chapter 2: System Setup

<b>Auxiliary Functions</b> .....	<b>2-2</b>
What are Auxiliary Functions? .....	2-2
Accessing the AUX Functions .....	2-3
Select Auxiliary Function .....	2-3
<b>Handheld Setup</b> .....	<b>2-4</b>
Clearing the Display .....	2-4
Using the Cursor .....	2-4
Turning Off the Beeper .....	2-5
Turning Off the Backlight .....	2-5
<b>CPU Setup</b> .....	<b>2-6</b>
A Few Things to Know .....	2-6
Changing the CPU Modes .....	2-6
Clearing an Existing Program .....	2-8
Initializing System Memory .....	2-9
Setting the CPU Network Address .....	2-10
Setting Retentive Memory Ranges .....	2-11
Setting the Clock and Calendar .....	2-12
<b>I/O Configuration</b> .....	<b>2-13</b>
Automatic Configuration .....	2-13
Automatic I/O Configuration Check .....	2-14
Manual Configuration .....	2-16
Removing a Manual Configuration .....	2-17

---

## Chapter 3: Entering Programs

<b>Entering Simple Ladder Programs</b> .....	<b>3-2</b>
Purpose of the Examples .....	3-2
Handheld Key Sequences .....	3-2
The Basics .....	3-2
Traversing the Program .....	3-2
Accessing Addresses .....	3-2
Address Previous / Next Functions .....	3-2
Previous / Next Keys .....	3-2
Starting at Address 0 .....	3-3
Entering Simple Rungs .....	3-4
Entering Normally Closed Elements .....	3-5
Entering Series Elements .....	3-6
Entering Parallel Elements .....	3-7
Joining Series Branches in Parallel .....	3-8
Joining Parallel Branches in Series .....	3-9
Combination Networks .....	3-10
Entering Timers and Counters .....	3-12
with a V-memory preset .....	3-12
with a constant .....	3-12
Entering Relational Contacts .....	3-14
Entering ASCII Characters .....	3-15
Entering Octal and Hex Numbers .....	3-16
<b>Checking for Program Errors</b> .....	<b>3-17</b>
Error Checking .....	3-17
Syntax Check .....	3-17
Duplicate Reference Check .....	3-18

## Chapter 4: Changing Programs

<b>Two Ways to Edit a Program</b> .....	<b>4-2</b>
Program Mode .....	4-2
Run Mode Edits .....	4-2
<b>Displaying a Program</b> .....	<b>4-3</b>
<b>Finding a Specific Instruction</b> .....	<b>4-4</b>
<b>Changing an Instruction</b> .....	<b>4-5</b>
<b>Inserting an Instruction</b> .....	<b>4-6</b>
<b>Deleting an Instruction</b> .....	<b>4-7</b>
<b>Using Search and Replace</b> .....	<b>4-8</b>
<b>Editing Programs During Run Mode</b> .....	<b>4-9</b>
Selecting AUX 14 .....	4-9
Changing an Instruction During Run Mode .....	4-10
Inserting an Instruction During Run Mode .....	4-11
Deleting an Instruction During Run Mode .....	4-12

## Chapter 5: Naming and Storing Programs

<b>Program Names and Passwords</b> .....	<b>5-2</b>
Program Names .....	5-2
Password Protection .....	5-2
Locking the CPU with the Password .....	5-3
<b>Storing Programs on Memory Cartridges</b> .....	<b>5-4</b>
Types of Memory Cartridge .....	5-4
DL440 Memory Cartridge .....	5-5
Clearing the Memory Cartridge .....	5-6
Copying Programs from the CPU .....	5-7
Writing Programs to the CPU .....	5-8
Comparing CPU and Handheld Programs .....	5-9
<b>Storing Programs on Cassette Tapes</b> .....	<b>5-10</b>
Cassette Characteristics .....	5-10
Connecting the Cassette Recorder .....	5-10
Program Names on Cassettes .....	5-10
Writing a Program to the Cassette .....	5-10
Reading Programs from Cassette Tapes .....	5-12
Comparing Cassette and CPU Programs .....	5-13

## Chapter 6: System Monitoring and Troubleshooting

<b>Troubleshooting Suggestions</b> .....	<b>6-2</b>
<b>Monitoring Discrete I/O Points</b> .....	<b>6-3</b>
<b>Forcing Discrete I/O Points</b> .....	<b>6-4</b>
<b>Monitoring V-Memory Locations</b> .....	<b>6-6</b>
<b>Changing V-Memory Values</b> .....	<b>6-6</b>
<b>Monitoring Timer/Counter Values</b> .....	<b>6-6</b>
<b>Monitoring the CPU Scan Time</b> .....	<b>6-7</b>
<b>Test Modes</b> .....	<b>6-8</b>
TEST-PGM and TEST-RUN .....	6-8
Test Mode Displays .....	6-9
Holding Output States .....	6-10
<b>I/O Diagnostics</b> .....	<b>6-12</b>
Diagnostic Indicators .....	6-12
Using AUX 42 .....	6-13
<b>Custom Messages</b> .....	<b>6-14</b>
Enter the ACON instruction and the first two letters .....	6-17
<b>Checking the Error Message Tables</b> .....	<b>6-18</b>
Two Types of Tables .....	6-18
Viewing the Error Table .....	6-19
Viewing the Message Table .....	6-19
<b>Error Codes</b> .....	<b>6-20</b>

## Appendix A: DL405 Memory Map

<b>Memory Map Overview</b> .....	<b>A-2</b>
DL430 Memory Map .....	A-2
DL440 Memory Map .....	A-3
<b>X Input Bit Map</b> .....	<b>A-4</b>
<b>Y Output Bit Map</b> .....	<b>A-5</b>
<b>Remote I/O Bit Map</b> .....	<b>A-6</b>
<b>Control Relay Bit Map</b> .....	<b>A-8</b>
<b>Stage Control / Status Bit Map</b> .....	<b>A-10</b>
<b>Timer Status Bit Map</b> .....	<b>A-12</b>
<b>Counter Status Bit Map</b> .....	<b>A-13</b>

---