

TABLE OF CONTENTS



Chapter 1 - Introduction

Introduction	1-2
The Purpose of this Manual.....	1-2
Other Reference Materials.....	1-2
Who Should Read this Manual.....	1-2
Quality Technical Support.....	1-3
Conventions Used	1-3
Key Topics for Each Chapter.....	1-3
ECOM Module Introduction.....	1-4
ECOM Communication Possibilities.....	1-4
Your Network PC.....	1-5
Frequently Asked Questions	1-6

Chapter 2 - Setup and Installation

ECOM Network Identifiers	2-2
Module ID.....	2-3
Name.....	2-3
Example:.....	2-4
Ethernet (MAC) Address.....	2-4
Using Multiple Network Identifies.....	2-4
Setting the Module ID with the DIP Switch	2-5
H0 / H2 Series ECOM DIP Switch.....	2-6
H4 Series ECOM DIP Switch.....	2-7
Inserting the ECOM Module in the PLC Base	2-8
H0 Series ECOM Module Installation.....	2-8
DL205 Slot Choices.....	2-8
H2 Series ECOM Module.....	2-9
DL405 Slot Choices.....	2-10
H4 Series ECOM.....	2-11

ECOM Network Layouts	2-11
Network Cabling	2-13
ECOM Supports Two Standards.....	2-13
10/100BaseT Networks	2-13
10/100BaseT Connections.....	2-14
UTP Cable	2-14
10BaseFL Connections.....	2-14
Fiber Optic Cable	2-14
Fiber Optic Module ST Connector	2-14
Maximum Cable Length	2-15
10/100BaseT Distance Limitations	2-15
10BaseFL Distance Limitations.....	2-15
Maximum Number of ECOM Modules on the Network	2-16

Chapter 3 - Configuring ECOMs Using NetEdit3

NetEdit3 Software	3-2
Installing NetEdit3.....	3-2
Launching NetEdit3	3-3
The NetEdit3 Screen	3-3
Adding Network Protocol Support to the NetEdit3 PC.....	3-4
Using NetEdit3	3-5
Ethernet Communication Protocol	3-5
Ethernet Address.....	3-6
Module Type, IP Address and ID	3-6
Module Info> General Information	3-7
Module Info> Ethernet Stats	3-7
ECOM Settings	3-7
ECOM Settings> Configuration> General	3-8
ECOM Settings> Configuration> Advanced.....	3-9
ECOM Settings> Configuration> Peer to Peer	3-10
ECOM Settings> Utils>Test CPU Access	3-12
ECOM Settings> Firmware.....	3-12
FileMenu> Live Update	3-13
F / B / C Columns	3-13

Chapter 4 - RLL Programming for Communications

PLC-to-PLC Communications	4-2
How RLL is Used for Communications.....	4-2
Network Instructions	4-3
Read (RX) and Write (WX) Instructions	4-3
Building the Read (RX) and Write (WX) Routine.....	4-3
The First LD Instruction.....	4-3
The Second LD Instruction.....	4-4
The LDA Instruction.....	4-4
Read (WX) Instruction	4-5
Write (WX) Instruction.....	4-5
Addressing the Different Memory	4-6
Bit Memory	4-6
Word Memory and Aliases	4-6
DirectSOFT is Flexible	4-7
DL05 CPU	4-7
DL06 CPU	4-7
D2-240 CPU.....	4-8
D2-250-1 CPU.....	4-8
D2-260/D2-262 CPU.....	4-9
D4-430 CPU.....	4-9
D4-440 CPU.....	4-10
D4-450/D4-454 CPU.....	4-10
Special Relays for Communications.....	4-11
Program with One Read Instruction	4-13
Program for the Initiating PLC.....	4-13
Program for the Responding PLC.....	4-13
Example Program with One Write Instruction	4-15
Program for the Initiating PLC.....	4-15
Program for the Responding PLC.....	4-15
Integrating Multiple Read and Write Instructions	4-17
Interlocking Relays.....	4-17
First RX/WX Instruction.....	4-18

Second RX/WX Instruction	4-19
Third RX/WX Instruction	4-19
Shift Register	4-20
Store If Equal	4-20
First RX/WX Instruction.....	4-21
Second RX/WX Instruction.....	4-21
Third RX/WX Instruction	4-21

Chapter 5 - Modbus TCP for H0/H2/H4-ECOM100

Modbus TCP	5-2
Client / Server Model.....	5-2
Protocol Description.....	5-2
Supported Modbu Function Codes	5-4
Network Server (Slave) Operation	5-5
Modbus Function Codes Supported.....	5-5
Determining the Modbus Address	5-5
If Your Host Software or Client Requires the Data Type and Address	5-6
Example 1: V2100.....	5-11
Example 2: Y20	5-11
Example 3: T10 Current Value.....	5-11
Example 4: C54.....	5-12
If the Host Software or Client Requires an Address ONLY	5-12
Example 1: V2100.....	5-14
Example 2: Y20	5-14
Example 3: C54.....	5-14
Network Client (Master) Operation.....	5-15
PLC Memory Supported for Client Operation	5-17
Example 1: Calculating Word PLC Address	5-18
Example 2: Calculating Discrete Input PLC Address.....	5-18
Building the Read (RX) or Write (WX) Routine	5-19
Step 1: Identify ECOM Slot Location and Server Node #	5-19
Step 2: Load Number of Bytes to Transfer.....	5-20
Step 3: Specify Master Memory Area.....	5-20
Step 4: Specify Slave Memory Area.....	5-20
Communications from a Ladder Program.....	5-21

Multiple Read and Write Interlocks5-21
 ECOM100 IBOX5-22
 Modbus TCP Setup5-24
 Example Modbus TCP Program5-26
 Troubleshooting:5-26
H0/H2/H4 -ECOM100 System Memory5-30

Chapter 6 - H0/H2/H4-ECOM100 DHCP & HTML Configuration

H0/H2/H4 -ECOM100 DHCP 6-2
 DHCP Issues 6-2
 Disabling DHCP and Assigning a Static IP Address 6-2
Using HTML Configuration..... 6-3
 Connecting to the H0/H2/H4 -ECOM100..... 6-3
 H0/H2/H4-ECOM100 Client Peer to Peer Configuration..... 6-5

Chapter 7 - Maintenance and Troubleshooting

Isolating a Communication Problem 7-2
 Diagnostic Tools and Techniques 7-2
Troubleshooting Chart 7-2
ECOM Module Diagnostic LEDs..... 7-4
 H0 Series Indicators 7-4
 OK Indicator 7-4
 LINK Indicator 7-4
 ACT Indicator 7-4
 ERR Indicator 7-4
 100MBIT Indicator 7-4
Network Server (Slave) Operation 7-5
 H24-ECOM-(F) Indicators 7-5
 LINKGD Indicator 7-5
 ACT Indicator 7-5
 ERROR Indicator 7-5
 H2/H4-ECOM100 Indicators 7-6
 STATUS 7-6
 LINKGD Indicator 7-6

Table of Contents

ACTIVE Indicator	7-6
ERROR Indicator	7-6
100MBIT Indicator	7-6
Using NetEdit3 for Troubleshooting.....	7-7
Select a Module.....	7-7
Module Information.....	7-7
Change Protocol	7-8
Ethernet Stats	7-8
RX/WX Settings.....	7-9
Record the Module Settings.....	7-9
Replacing the ECOM Module	7-10
Diagnosing Network Cable Problems	7-11

Appendix A - General Specifications

General Specifications	A-2
ECOM Specifications	A-2
Ethernet Standards	A-4

Appendix B - Peerlink Specifications

Peerlink Function for ECOM100	B-2
Peerlink Data-Sharing Network.....	B-3
Configuration.....	B-4
Parameters:.....	B-5
DL05.....	B-6
DL06.....	B-7
DL205.....	B-8
DL405.....	B-9
Do-more	B-10
Block Summary.....	B-11

Appendix C - Security Considerations for Control Systems Networks

Security Considerations for Control Systems Networks.....	C-2
--	------------