

Table of Contents

Chapter One: Getting Started

Introduction	1-2
The Purpose of this Manual	1-2
Who Should Read this Manual	1-2
Where to Begin	1-2
Supplemental Manuals	1-2
How this Manual is Organized	1-3
Technical Assistance	1-3
HSC Features	1-4
What is a High Speed Counter?	1-4
Who Needs a High Speed Counter?	1-4
Types of Counting	1-4
Standard Counting	1-4
Quadrature Counting	1-5
Output Control	1-5
Sampling	1-6
Home Search	1-6
How Does the HSC Work With the CPU?	1-7
Setup Performed Via Shared Memory	1-7
Physical Characteristics & Specifications	1-8
LED Assignments	1-8
Overview of HSC Inputs and Outputs	1-10
Y Data Type Equivalents for Some Functions	1-10
X Input and Y Output Assignments	1-11
Putting It All Together	1-12
Five Steps for Using the HSC	1-12
The Next Chapter	1-12

Chapter 2: Installation & Wiring

How to Install the D4-HSC	2-2
Connecting the Wiring	2-3
Wiring the D4-HSC Terminal Block	2-3
Wiring Guidelines	2-3
Connecting the Power Supply	2-4
Using an External Power Supply	2-4
Using the Internal DL-405 System Power Supply	2-4

Count Input Wiring Diagram	2-5
Control Input Wiring Diagram	2-6
Control Output Wiring Diagram	2-7
Chapter 3: Understanding the Operation	
The Operating Basics	3-2
Assigning Your Data Types	3-3
Automatic Configuration	3-3
Using the X and Y Assignment Table	3-4
I/O Assignment Table	3-5
Reading and Writing Shared Memory	3-6
Contents and Data Flow	3-6
The Two-Step Process for Writing Data to Shared Memory	3-7
Reading Data From Shared Memory	3-7
Understanding How Numbers are Stored In Shared Memory	3-8
Why is it important?	3-8
Allocating the 4 Bytes of Memory	3-8
Dealing With the Negative Numbers	3-9
Placing a Negative Number into Shared Memory	3-9
The Next Chapter	3-9
Chapter Four: Setting Up and Controlling the Counting	
Introduction to Using <i>DirectSOFT</i>	4-2
Selecting the Counting Mode	4-3
Determining Which Mode to Use	4-3
Ladder Logic for Determining the Counting Mode	4-3
Selecting the Counting Direction	4-4
How Ym+13 and Ym+14 Together Determine Counting Direction	4-4
Ladder Logic to Select Counting Direction	4-4
Selecting the Counting Resolution	4-5
Choose from 3 Resolution Settings	4-6
Why Change the Counting Resolution?	4-6
Example RLL: 2x Resolution	4-6
Example RLL: 4x Resolution	4-6
Default Setting	4-6
Specifying an Offset	4-7
What is an Offset?	4-7
External Method	4-7
Internal Method	4-7
Specifying a Preset	4-8
What is a Preset?	4-8
How Does the Preset Affect the Outputs?	4-8
Loading the Preset Into Shared Memory	4-8
Checking the Status of Preset Relative to Current Count	4-8

Starting and Resetting the Current Count	4-9
Starting the Counter	4-9
Automatically Resetting the Counter	4-9
Internal Reset	4-9
External Reset Using RST	4-9
Summary of Reset Count Relays	4-9
External Reset Using INZ	4-10
Latching or Inhibiting the Current Count	4-11
What Does Latching Do?	4-11
How Do You Trigger the Latching Process?	4-11
Sample RLL for Latching	4-11
What Is Meant By Inhibiting the Count?	4-11
How Do You Inhibit the Count?	4-11
Sample RLL for Inhibiting the Count	4-11
Summary of Latch and Inhibiting Output Relays	4-11
Monitoring Overflow and Resetting Flags	4-12
What is a Counting Overflow?	4-12
Status Flag for Overflow	4-12
Tracking Overflows	4-12
Summary of Input and Output Relays for Overflow and Flag Reset	4-12
 Chapter Five: Controlling the Outputs	
Introduction	5-2
The 4 Control Outputs	5-2
All the Output Signals Look the Same	5-2
The 4 Output Relays for Turning ON Each Control Output	5-2
Using the Internal Relays to Control the Outputs is Optional	5-2
Manual Output Control	5-3
Using Ym+6 and Ym+23 to turn direction outputs ON or OFF	5-3
Automatic Output Control	5-3
Also Called HSC RUN	5-3
How Do You Invoke HSC RUN?	5-3
Example of Using Ym+3 to Activate HSC RUN	5-3
Using the Direction Outputs	5-4
What is a Direction Output?	5-4
How the HSC Knows When to Turn ON CW or CCW	5-4
Timing Diagrams for HSC RUN	5-5
Current Count < Preset	5-5
Current Count = Preset	5-5
Current Count > Preset	5-5
Using the Speed Outputs with the Direction Outputs	5-6
What are the Speed Outputs?	5-6
2 Ways to Initiate OUT1 and OUT2	5-6
Using HSC RUN to Initiate OUT1	5-6
How OUT2 is Initiated in HSC RUN	5-6
Monitoring Speed Output Status	5-6
Figure A: Example of Outputs (Decel=1000, Preset=3000, Current Count >Preset)	5-6
Figure B: Example of Outputs (Decel=1000, Preset=3000, Current Count<Preset)	5-6

Chapter Six: Special Features

Planning a Home Search Application	6-2
Requirements for Home Search	6-2
Example of Home Search Application	6-2
Using Sampling	6-4
Why Use Sampling?	6-4
Enabling and Monitoring the Sampling	6-4
How to Calculate the Timebase	6-5
What Happens If You Want to Enter a Value with Decimal Points?	6-5
Summary of Input and Output Relays for Sampling	6-5

Chapter Seven: Program Applications

A Quick Checkout of the Module	7-1
What It Does	7-2
How It Works	7-2
Things You Need for the Example	7-2
Wiring Diagram for the Example	7-2
RLL Program for Quick Checkout of the Module	7-3
Application No.1: Drilling Operation	7-4
Ladder Logic for Drilling Operation	7-5
Application No. 2: Cut-to-Length Operation	7-8
Ladder Logic for Cut-to-Length Operation	7-9

Appendix A: Introduction to Motor Drives and Encoders

What is a Drive and How Does It Connect to the HSC?	A-2
What is an Encoder and How Does It Connect to the HSC?	A-3
How the Incremental Encoder Works	A-3
What is the Z-Marker?	A-3

Appendix B: Summary of Tables and Charts Presented in the Text

Specifications	B-2
X and Y Assignment Table	B-4
Shared Memory Table	B-5
Table for Determining Count Direction	B-6
Counting Resolution Table (Quadrature Only)	B-7