

Index

A

- ABS function, 1-21
- accounts
 - assigning security levels (note), 6-4
 - definition, 6-1
 - forgetting your password (note), 6-3
 - modifying, 6-4
- acknowledging alarms, 9-11 to 9-13
- ACOS function, 1-29
- action verification, 6-20
- Alarm object class
 - creating alarm objects, 9-2 to ??
- alarms, 9-1 to 9-13
 - acknowledging, 9-11 to 9-13
 - alarm subsystem, 9-4 to 9-13
 - areas, 9-4
 - circular reference alarms, 9-3
 - database-generated alarms, 9-1 to ??
 - DDE, 5-5 to 5-6
 - defining alarm conditions, 9-1 to ??
 - deselecting, 9-11
 - display options, 9-7 to ??
 - filters, 9-8
 - priorities, 9-6
 - selecting, 9-11
- Alarms window, 9-6 to 9-7
 - color scheme (table), 9-7
 - illustration of, 9-6
 - viewing alarms, 9-6
- aliases
 - optional use of (note), 11-5
 - purpose and use, 11-4 to 11-5
- AND function, 1-18
- Animator object class
 - displaying dynamic graphics (table), 2-6 to 2-7
- arithmetic operators, 1-15

- ASIN function, 1-29
- ATAN function, 1-29
- ATAN2 function, 1-30
- AVG function, 1-24

B

- bitmap (.BMP) graphics
 - compared with Windows metafiles, 2-18 to 2-19
 - displaying, 2-4 to 2-6
- .BMP files. *See* bitmap (.BMP) graphics

C

- CBL compiler, B-1
 - circular reference alarms, 9-3
 - Citadel Historical Database Logger, 7-5 to 7-9
 - accessing data with ODBC driver, 8-1 to 8-17
 - data transforms, 8-6 to 8-7
 - SQL examples, 8-7 to 8-8
 - traces table, 8-5
 - using Microsoft Access, 8-13
 - using Microsoft Excel, 8-13
 - using Microsoft Query, 8-8 to 8-13
 - using Microsoft Visual Basic, 8-17
 - creating historical database, 7-7 to 7-8
 - data location, 7-5 to 7-6
 - information overload, 7-9
 - logging criteria, 7-9
- client, DDE, 5-3 to 5-4
 - colors
 - alarm status (table), 9-7
 - using in graphics, 2-3 to 2-4
 - comma-separated value (.CSV) files
 - for Spreadsheet Logger, 7-3
 - communications service. *See* serial communications.
 - comparison operators, 1-15 to 1-18
 - control panels
 - report generation, 7-11 to 7-13

- viewing security, 6-10
- controllable objects
 - networking considerations, A-3 to A-4
 - security considerations, 6-9 to 6-10
 - viewing security, 6-10 to 6-11
- conventions, manual, vii to ??
- copying object databases, 11-15
- COS function, 1-30
- .CSV (comma-separated values) files, 7-3
- CTS timeout setting, 3-5
- custom graphics
 - See also* graphics
 - creating, 2-14 to 2-17
 - step-by-step example, 2-14 to 2-17
 - displaying static graphics, 2-4 to 2-6
 - exporting to Lookout, ?? to 2-16
 - exporting to LookoutDirect, 2-16 to ??
 - testing in Lookout, ?? to 2-17
 - testing in LookoutDirect, 2-16 to ??

D

- data logging
 - Citadel Historical Database Logger, 7-5 to 7-9
 - report generation, 7-11 to 7-13
 - Spreadsheet Logger, 7-1 to 7-4
- data transforms, 8-6 to 8-7
- dates
 - date/time functions (table), 1-31
- DDE (dynamic data exchange), 5-1 to 5-6
 - alarms, 5-5 to 5-6
 - client, 5-3 to 5-4
 - linking Lookout to other applications, ?? to 5-5
 - linking LookoutDirect to other applications, 5-2 to ??
 - networking considerations, A-12 to A-14
 - adding trusted DDE share, A-13 to A-14
 - running NETDDE.EXE automatically, A-12 to A-13
 - overview, 5-1 to 5-2

- peer-to-peer, 5-4 to 5-5
- server, 5-2 to 5-3
- DialGauge object class
 - displaying dynamic graphics (table), 2-6 to 2-7
- Dialing prefix settings (table), 3-6
- Dial-up serial connection, 3-5 to 3-7
- displaying
 - expressions, 1-8 to ??
- driver objects
 - purpose and use, 3-1 to 3-2
 - types of, 3-1
- dynamic data exchange. *See* DDE (dynamic data exchange)
- dynamic graphics, 2-6 to 2-13
 - See also* graphics
 - displaying
 - logical signals, 2-7 to 2-10
 - numeric signals, 2-10 to 2-11
 - text signals, 2-12 to 2-13
 - tools for displaying (table), 2-6 to 2-7

E

- editing database parameters, 11-1 to 11-8
 - logical parameters, 11-7 to 11-8
 - numeric parameters, 11-4 to 11-7
 - text parameters, 11-8
- editing object parameters (example), 11-1 to 11-3
- Event Logger, 7-10
 - See also* logging data and events
 - data location, 7-10
 - information overload, 7-10
- EXACT function, 1-26
- EXP function, 1-22
- exporting object databases, 11-9 to 11-13
 - copying object databases, 11-15
 - creating database spreadsheet, 11-11 to 11-13
 - overview, 11-9
 - procedure, 11-9 to 11-11
- Expression dialog box, 1-12
- expression functions, 1-18 to 1-31

- date/time functions (table), 1-31
- logical functions (table), 1-18 to 1-20
- lookup functions (table), 1-20, 1-21
- mathematical functions (table), 1-21 to 1-24
- statistical functions (table), 1-24 to 1-25
- text functions (table), 1-26 to 1-29
- trigonometric functions (table), 1-29 to 1-30
- Expression object class
 - creating Expression objects, 1-10 to 1-11
- expressions, 1-1 to 1-31
 - as connections, 1-12
 - as parameters, 1-11 to 1-12
 - creating, 1-3 to 1-12
 - displaying on control panels, 1-8 to ??
 - examples, 1-1 to 1-2
 - functions, 1-18 to 1-31
 - illegal conditions, 1-2 to 1-3
 - result of, 1-1
 - syntax, 1-14 to 1-18
 - arithmetic operators, 1-15
 - comparison operators, 1-15 to 1-18
 - text operator, 1-15
 - white space, 1-14
 - tools for displaying dynamic graphics (table), 2-6 to 2-7
- F**
- FACT function, 1-22
- FALSE function, 1-19
- FIND function, 1-26
- FIXED function, 1-26
- G**
- Gauge object class
 - displaying dynamic graphics (table), 2-6 to 2-7
- graphic file types
 - bitmaps vs. metafiles, 2-18 to 2-19
 - memory considerations, 2-19
- graphics, 2-1 to 2-19
 - animating. *See* Animator object class
 - creating custom graphics, 2-14 to 2-17
 - dynamic graphics, 2-6 to 2-13
 - file types, 2-18 to 2-19
 - screen resolution considerations (note), 2-1
 - static graphics, 2-2 to 2-6
- H**
- hardware networking, A-10
- Hardwired serial connections, 3-4
- historical database logging. *See* Citadel Historical Database Logger
- I**
- importing object databases
 - copying object databases, 11-15
 - overview, 11-9
 - procedure, 11-13 to 11-15
- insets
 - displaying in graphics, 2-2 to 2-4
- INT function, 1-22
- Is equal to (=) operator, 1-16
- Is greater than (>) operator, 1-15
- Is greater than or equal to (>=) operator, 1-15
- Is less than (<) operator, 1-15
- Is less than or equal to (<=) operator, 1-15
- Is not equal to (<>) operator, 1-16
- L**
- LCHOOSE function, 1-21
- LEFT function, 1-26
- LEN function, 1-27
- LIF function, 1-19
- lines, displaying in graphics, 2-2 to 2-4
- LN function, 1-22
- LOG function, 1-22
- LOG10 function, 1-22
- logging data and events, 7-1 to 7-13
 - Citadel Historical Database Logger, 7-5 to 7-9
 - Event Logger, 7-10
 - report generation, 7-11 to 7-13
 - Spreadsheet Logger, 7-1 to 7-4
- logical data members

- editing parameters, 11-7 to 11-8
- logical expressions
 - displaying dynamic graphics (table), 2-6 to 2-7
 - functions (table), 1-18 to 1-20
- logical signals, displaying in graphics, 2-7 to 2-10
- LOWER function, 1-27

M

- mathematical functions (table), 1-21 to 1-24
- MAX function, 1-24
- menu bars
 - viewing security, 6-11
- Microsoft Access
 - accessing Citadel data, 8-13
 - compliance with ODBC (note), 8-4
- Microsoft Excel, accessing Citadel data, 8-13
- Microsoft Query
 - accessing Citadel data, 8-8 to 8-13
 - compliance with ODBC (note), 8-4
- Microsoft Visual Basic
 - accessing Citadel data, 8-17
 - compliance with ODBC (note), 8-4

MID function, 1-27

MIN function, 1-24

MOD function, 1-23

modem settings, 3-5 to 3-7

- multilink networking, A-3 to A-5
 - compared with table networking, A-11
 - linking controllable objects, A-3 to A-4
 - linking non-controllable objects, A-4 to A-5

- Multistate object class
 - displaying dynamic graphics (table), 2-6 to 2-7

N

- NCHOOSE function, 1-21
- networking, 4-1 to 4-7, A-1 to A-14
 - See also* redundancy
 - capabilities, A-1 to A-2
 - DDE considerations, A-12 to A-14

- adding trusted DDE share, A-13 to A-14
- running NETDDE.EXE
 - automatically, A-12 to A-13
- hardware networking, A-10
- methods, A-2
- multilink, A-3 to A-5
 - compared with table networking, A-11
 - linking controllable objects, A-3 to A-4
 - linking non-controllable objects, A-4 to A-5
- overview, A-2
- requirements, A-1
- table networking, A-6 to A-9
 - compared with multilink networking, A-11
 - examples, A-6 to A-8
 - routing signals to and from driver objects, A-8
 - topography (figure), A-9
- networking considerations
 - controllable objects, A-3 to A-4
 - non-controllable objects, A-4 to A-5
- NIF function, 1-19, 1-19
- NOT function, 1-19
- NOW function, 1-31
- numeric data members
 - editing parameters, 11-4 to 11-7
- numeric expressions, for displaying dynamic graphics (table), 2-6 to 2-7
- numeric signals, displaying in graphics, 2-10 to 2-11

O

- object databases
 - copying, 11-15
 - creating database-generated alarms, 9-1 to ??
 - editing parameters, 11-1 to 11-8
 - exporting, 11-9 to 11-11
 - importing, 11-13 to 11-15

- object parameters
 - editing, 11-1 to 11-8
 - example, 11-1 to 11-3
 - expressions as parameters, 1-11 to 1-12
 - logical parameters, 11-7 to 11-8
 - numeric parameters, 11-4 to 11-7
 - text parameters, 11-8
- objects
 - connecting
 - expressions as connections, 1-12
 - networking considerations
 - controllable objects, A-3 to A-4
 - non-controllable objects, A-4 to A-5
- ODBC
 - definition, 8-1
- ODBC driver
 - accessing Citadel data, 8-1 to 8-17
 - data transforms, 8-6 to 8-7
 - ODBC-compliant applications (note), 8-4
 - SQL examples, 8-7 to 8-8
 - traces table, 8-5
 - with Microsoft Access, 8-13
 - with Microsoft Excel, 8-13
 - with Microsoft Query, 8-8 to 8-13
 - with Microsoft Visual Basic, 8-17
- Open Database Connectivity (ODBC). *See* ODBC
- operators
 - arithmetic, 1-15
 - comparison, 1-15 to 1-18
 - text, 1-15
- OR function, 1-19
- P**
- passwords
 - forgetting your password (note), 6-3
 - protecting process files, 6-19 to 6-20
 - revising accounts, 6-4
- Pause between calls (modem) setting, 3-7
- peer-to-peer links, DDE, 5-4 to 5-5
- PI function, 1-23
- Pipe object class
 - displaying dynamic graphics (table), 2-6 to 2-7
- plates
 - displaying in graphics, 2-2 to 2-4
- Poll Rate, 3-2
- Popup control panels
 - viewing security, 6-11 to 6-12
- Pot object class
 - displaying dynamic graphics (table), 2-6 to 2-7
 - displaying dynamic numeric signals, 2-10 to 2-11
- printing
 - alarms, 9-10 to 9-11
- prioritizing alarms, 9-6
- process files
 - protecting, 6-19 to 6-20
- PRODUCT function, 1-23
- PROPER function, 1-27
- Pushbutton object class
 - action verification, 6-20
 - displaying dynamic graphics (table), 2-6 to 2-7
- R**
- Radio (RTS/CTS) serial connection, 3-4 to 3-5
- RAND function, 1-23
- Receive gap setting, 3-3 to 3-4
- rectangles, displaying in graphics, 2-2 to 2-4
- redundancy, 10-1
 - basic standby principles, 10-2
 - failover scenarios, 10-3
 - standby configuration, 10-4
- REPLACE function, 1-27
- report generation, 7-11 to 7-13
 - control panel reports, 7-11 to 7-13
 - third party reports, 7-13
- REPT function, 1-27
- Retries (modem) setting, 3-6
- RIGHT function, 1-28

- ROUND function, 1-23
- RTS delay off time period, 3-5
- RTS/CTS handshaking settings, 3-4 to 3-5
- S**
- screen resolution
 - graphics (note), 2-1
- SEARCH function, 1-28
- security, 6-1 to 6-20
 - action verification, 6-20
 - control security, 6-9 to 6-10
 - overview, 6-1
 - process file security, 6-19 to 6-20
 - viewing security, 6-10 to 6-12
 - control panels, 6-10
 - controllable objects, 6-10 to 6-11
 - system settings, 6-11 to 6-12
- serial communications, 3-1 to 3-7
 - defining serial port settings, 3-2 to 3-7
 - dial-up modem settings, 3-5 to 3-7
 - driver objects, 3-1 to 3-2
 - Hardwired connections, 3-4
 - overview, 3-2
 - Receive gap setting, 3-3 to 3-4
 - RTS/CTS handshaking settings, 3-4 to 3-5
 - selecting serial port, 3-3
- Serial port data field, 3-3
- server, DDE, 5-2 to 5-3
- SIGN function, 1-23
- SIN function, 1-30
- space, in expressions, 1-14
- Spinner object class
 - displaying dynamic graphics (table), 2-6 to 2-7
- Spreadsheet Logger, 7-1 to 7-4
 - concurrent file access, 7-4
 - .CSV files, 7-3
 - data location, 7-2 to ??
 - file and disk errors, 7-3
 - information overload, 7-4
- Spreadsheet object class
 - exporting object database to spreadsheet file, 11-11 to 11-13
- SQL
 - See also* ODBC driver definition, 8-1
- SQRT function, 1-24
- standby
 - basic principles, 10-2
 - configuration, 10-4
 - failover scenarios, 10-3
- static graphics, 2-2 to 2-6
 - custom graphics, 2-4 to 2-6
 - displaying text, plates, insets, rectangles, and lines, 2-2 to 2-4
- statistical functions (table), 1-24 to 1-25
- STDEV function, 1-25
- STDEVP function, 1-25
- Structured Query Language. *See* SQL
- SUM function, 1-25
- Switch object class
 - action verification, 6-20
 - displaying
 - dynamic graphics (table), 2-6 to 2-7
 - logical signals in graphics, 2-7 to 2-10
- system options, setting for security, 6-9 to 6-10
- T**
- table networking, A-6 to A-9
 - compared with multilink networking, A-11
 - examples, A-6 to A-8
 - routing signals to and from driver objects, A-8
 - topography (figure), A-9
- tabs, in expressions, 1-14
- TAN function, 1-30
- TCHOOSE function, 1-20, 1-21
- text
 - displaying in graphics, 2-2 to 2-4
- text data members
 - editing, 11-8

- text expressions, for displaying dynamic graphics (table), 2-6 to 2-7
- TEXT function, 1-28
- text functions (table), 1-26 to 1-29
- text operators, 1-15
- text signals, displaying in graphics, 2-12 to 2-13
- third party reports, 7-13
- TIF function, 1-20
- time
 - date/time functions (table), 1-31
- title bars
 - viewing security, 6-11
- TODAY function, 1-31
- traces table, for Citadel data, 8-5
- Transparent pixel data fields, 2-5
- trigonometric functions (table), 1-29 to 1-30
- TRIM function, 1-28
- TRUE function, 1-20
- TRUNC function, 1-24
- trusted DDE share, A-13 to A-14
- U**
- UPPER function, 1-29
- V**
- VAR function, 1-25
- VARP function, 1-25
- viewing security, 6-10 to 6-12
 - control panels, 6-10
 - controllable objects, 6-10 to 6-11
 - system settings, 6-11 to 6-12
- Visual Basic
 - accessing Citadel data, 8-17
 - compliance with ODBC (note), 8-4
- W**
- Wait for connection (modem) setting, 3-6 to 3-7
- white space, in expressions, 1-14
- Windows Metafile (.WMF) graphics
 - compared with bitmap files, 2-18 to 2-19
 - displaying, 2-4 to 2-6
- .WMF. *See* Windows Metafile (.WMF) graphics
- X**
- XOR function, 1-20