

GCX/ECX Series 22mm Metal Pilot Devices Selection Guide




Flush

- Momentary 30 or 40mm operators
- Available in six colors: black, red, yellow, blue, white and green
- One contact block included
- ON/OFF models also available

Ours: \$6.50 (GCX1100)

Allen-Bradley: \$56.88* (800F-MX10, 800F-ALM + 800FM-F2)



Extended

- Momentary 30mm operators
- Available in six colors: black, red, yellow, blue, white and green
- One contact block included

Ours: \$7.25 (GCX1110)

Allen-Bradley: \$59.77* (800F-MX01, 800F-ALM + 800FM-E2)



Two way

- Two way on/off control
- With or without illuminated indicators
- One NO and one NC contact block included




Illuminated

- Available in clear, red, yellow, blue, white and green; 24 and 120-volt models
- Momentary and push-push styles
- Flush or extended operators available
- Incandescent and LED models
- One contact block included

Ours: \$12.00 (GCX1212-24)

Allen-Bradley: \$21.12* (800FM-LE3 + 800F-ALM, D3C)



Mushroom

- Available in momentary, twist-to-release, and key release models
- One contact block included
- Also available in incandescent and LED illuminated models

Ours: \$12.50 (GCX1131)

Allen-Bradley: \$89.75* (800FM-MT44 + 800F-MX01 + 800F-ALM)



Audible annunciators and potentiometers

- Audible annunciators with or without LED indicator
- 5 and 10 KΩ potentiometers



Selector switches

- Two and three-position in spring return and maintained, non-illuminated and illuminated; incandescent and LED models
- Contact block included

Ours: \$9.75 (GCX1300)

Allen-Bradley: \$64.20* (800FM-SM22 + 800F-MX10 + 800F-ALM)



Key switches

- Two and three-position
- Contact blocks included

Ours: \$18.00 (GCX1420)

Allen-Bradley: \$94.66* (800FM-KM21 + 800F-MX10 + 800F-ALM)



Joysticks

- Two and four-position, maintained and momentary
- Contact blocks included

Ours: \$26.50 (ECX1510)

Allen-Bradley: \$176.85* (800FM-JR2 + 800F-MX20 + 800F-ALM)



Pilot lights

- Available in six colors: red, green, white, clear, yellow and blue
- 24 and 120-volt models with LED
- Frosted diffuser for even lighting
- Incandescent or LED indicators

Ours: \$5.50 (ECX1052-24)

Allen-Bradley: \$70.55* (800FM-P3 + 800F-ALM + 800F-D3C)

Accessories



• One to six-hole enclosures

• Bulbs and LEDs

• Protective actuator caps


*All prices are U.S. published prices. AutomationDirect's prices are from April 2014 Price List. Prices and specifications may vary by dealer and configuration. Allen-Bradley industrial control component prices from www.rockwellautomation.com/en/e-tools 2/28/2014.

GCX Series 22mm Metal Pilot Devices Specifications


Assembly information

These pushbuttons and indicator lights are supplied with the appropriate contact blocks, unless otherwise indicated. Use these drawings as a guide to make sure there is adequate clearance behind the panel.


Pushbuttons and selector switches




Illuminated pushbuttons and selector switches/pilot lights



Mounting



This layout is suitable if all switches are 230V or less and the same polarity.




This layout is suitable if all switches are 400V or less and different polarity.



NOTE: Contact blocks can be arranged up to three deep by two wide.

Typical Wiring



Specifications

These specifications apply to all GCX and ECX 22 mm metal pushbuttons and switches.

Physical Specifications	
Standards Reference	CEI EN 60947-5-1, CSA C22-2 n.14
Approvals	CSA, IMQ (where specified), UL File E189258
Enclosure Material	Zn + Al + Mg alloy, chromium plated
Contacts Material	Silver
Protection Degree	IP 40 for GCX3151-24, GCX3151-120, GCX3153-24 and GCX3153-120. IP 65 for all others. (See Appendix of this catalog for explanation of IP ratings according to IEC 144 CEI 70-1.)
Temperature Ratings	Storage: -40° to 80°C (-40° to 176° F) Operating: -25° to +70°C (-13° to 158° F)
Working Positions	All working positions are allowed
Mechanical Life	Pushbuttons, selector switches: Joy stick switches: 1,000,000 operations Mushroom pushbuttons: 300,000 operations

Electrical Specifications	
Rated Thermal Current (contact block)	A300, Q300 (Refer to E22 Series mounting/contact rating section for details)
Rated Insulation Voltage	Ui 660V according to CEI EN 60947-5-1, 300V according to CSA C22-2 n.14
Dielectric Strength	3kV (1 second)
Insulation Resistance	2MΩ min. (500VDC)
Initial Contact Resistance	≤25mΩ
Short-Circuit Protection*	Cartridge fuses gl 10A - 500V 10,3x38l1 100kA
Terminal Markings	According to CENELEC EN 50013
Connections	Single screw with non-loosening plate clamp, 14AWG max.
Contacts Operation	Self-cleaning types EN01 (N.C.) EN 10 (N.O.) slow action, positive opening
Operation Frequency	3600 operations per hour max.
Utilization Category	AC15 (Control of AC electromagnetic loads) 24 volts AC at 10 amps 130 volts AC at 6.5 amps DC13 (Control of DC electromagnetic loads) 24 volts DC at 1.5 amps 110 volts DC at 0.5 amps


*Note: Recommended, not supplied

GCX Series 22mm Plastic Pilot Devices Specifications


Assembly information

These pushbuttons and indicator lights are supplied with the appropriate contact blocks, unless otherwise indicated. Use these drawings as a guide to make sure there is adequate clearance behind the panel.


Pushbuttons and selector switches




Illuminated pushbuttons and selector switches/indicator lights




Mounting



This layout is suitable if all switches are 230V or less and the same polarity.




This layout is suitable if all switches are 400V or less and different polarity.



NOTE: Contact blocks can be arranged up to three deep by two wide.

Typical Wiring



Specifications

These specifications apply to all the GCX and ECX 22mm plastic pushbuttons and switches.

Physical Specifications		Electrical Specifications	
Standards Reference	CEI EN 60947-5-1, CSA C22-2 n.14	Rated Thermal Current (contact block)	A300, Q300 (Refer to E22 Series mounting/contact rating section for details)
Approvals	UL File E189258, IMQ (where specified)	Rated Insulation Voltage	Ui 660V according to CEI EN 60947-5-1, 300V according to CSA C22-2 n.14 and UL 508
Enclosure Material	Fiberglass reinforced thermoplastic	Dielectric Strength	3kV (1 second)
Contacts Material	Silver	Insulation Resistance	2MΩ min. (500VDC)
Protection Degree	IP 40 for GCX3151-24, GCX3151-120, GCX3153-24 and GCX3153-120. IP 65 for all others. (See Appendix of this catalog for explanation of IP ratings according to IEC 144 CEI 70-1.)	Initial Contact Resistance	≤25mΩ
Electric Shock Protection	IEC 536, Class II	Short-Circuit Protection*	Cartridge fuses gl 10 A-500V 10, 3x381 100 KA
Temperature Ratings	Storage: -40° to 80°C (-40° to 176° F) Operating: -25° to +70°C (-13° to 158° F)	Terminal Markings	According to CENELEC EN 50013
Working Positions	All working positions are allowed	Connections	Single screw with non-loosening plate clamp, 14AWG max., Tighten to 0.8Nm max
Mechanical Life	Pushbuttons, selector switches, joy stick switches: 1,000,000 operations Emergency mushrooms and push-push pushbuttons: 300,000 operations	Contacts Operation	Self-cleaning types EN01 (N.C.) EN 10 (N.O.) slow action, positive opening
Positive Opening Operation	(according to IEC 947-5-1) All functions incorporating an NC contact are positive opening operation	Operation Frequency	3600 operations per hour max.
		Utilization Category	AC15 (Control of AC electromagnetic loads) 24 volts AC at 10 amps 130 volts AC at 6.5 amps DC13 (Control of DC electromagnetic loads) 24 volts DC at 1.5 amps 110 volts DC at 0.5 amps

*Note: Recommended, not supplied

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.