



Cat6a Industrial Ethernet Cable



SYSTEMATIC TECHNOLOGY

A104338-1 Cable Specifications						
	Part Number	Wire/Cable Type	Flexibility	Minimum Cut Length (ft)*	Approximate Weight (lb/ft)	Price per foot
	A104338-1	Cat6a industrial Ethernet	Flexible	20	0.04	\$1.93
Physical Properties						
Conductor Gauge	26 AWG	Conductor Stranding		7-stranded bare copper		
Conductor Material	Bare Copper	Conductor Insulation Wall Thickness		0.019 in; nominal		
Conductor Assembly	4 twisted pairs	Bare Conductor Diameter		0.010 in; nominal		
Color Code	Pair 1	Blue, White/Blue	Insulated Conductor Diameter		0.048 in; nominal	
	Pair 2	Orange, White/Orange	Twisted Conductor Diameter		0.096 in; nominal	
	Pair 3	Green, White/Green	Overall Cable Diameter		0.252 in; nominal	
	Pair 4	Brown, White/Brown	Jacket Color		Green	
Voltage Rating	300V	Jacket Thickness		0.030 in; nominal		
Temperature Rating	-40 to 80 °C (-40 to 176 °F)	Jacket Material		PVC		
Plenum	No	Sunlight Resistant		No		
Shield	Shielded	Oil Resistance		Yes		
Drain	No	Flame Retardant		Yes		
Conductor Insulation Material	Special Polyolefin	Sample Print Legend		<LÜTZE logo> ELECTRONIC ETHERNET (C) PVC 104338 (4x(2xAWG26/7)) Cat 6A E331628 c(UL)us CMG 75°C RoHS <date YYWW> UKCA CE-44 <metermarking>m		
Minimum Bend Radius	1.51in					
Cabled Core Diameter	0.192 in					
Electrical Characteristics (for 100 meters of cable)						
Impedance (1-100 MHz)	100 Ω 1 – 100 MHz	UL Classification		(cULus) TYPE CMG		
Capacitance	14.94 pF/ft @ 1MHz; Nominal	Approvals**		cULus, CE, RoHS		
Resistance, Max.	76.8 Ω DC per 1000ft	Attenuation Crosstalk Ratio, Far End (ACRF)		$1 \leq f \leq 500 \text{ MHz: } 27.8 - 20 \text{ LOG}(f/100) \text{ dB MIN}$		
Dielectric Withstanding, Min.	1500V RMS	Insertion Loss		$1 \leq f \leq 500 \text{ MHz: } 1.82 \sqrt{(f)} + 0.0091(f) + 0.25/\sqrt{(f)} \text{ dB MAX}$		
Return Loss	$1 \leq f < 10 \text{ MHz: } 20 + 5 \text{ LOG}(f) \text{ dB MIN}$ $10 \leq f < 20 \text{ MHz: } 25 \text{ dB MIN}$ $20 \leq f \leq 500 \text{ MHz: } 25 - 7.0 \text{ LOG}(f/20) \text{ dB MIN}$	Power Sum Attenuation to Crosstalk Ratio, Far End (PSACRF)		$1 \leq f \leq 500 \text{ MHz: } 24.8 - 20 \text{ LOG}(f/100) \text{ dB MIN}$		
Near End Crosstalk (NEXT)	$1 \leq f \leq 500 \text{ MHz: } 44.3 - 15 \text{ LOG}(f/100) \text{ dB MIN}$	Cross Section				
Power Sum Near End Crosstalk (PSNEXT)	$1 \leq f \leq 500 \text{ MHz: } 42.3 - 15 \text{ LOG}(f/100) \text{ dB MIN}$					
TCL	$1 \leq f \leq 250 \text{ MHz: } 30 - 10 \text{ LOG}(f/100) \text{ dB MIN}$					
ELTCTL	$1 \leq f \leq 30 \text{ MHz: } 35 - 20 \text{ LOG}(f) \text{ dB MIN}$					
Velocity Of Propagation	0.77%					
Delay	$4 \leq f \leq 500 \text{ MHz: } 534 + 36/\sqrt{(f)} \text{ ns MAX}$					
Delay Skew	$1 \leq f \leq 500 \text{ MHz: } <25\text{ns}/100\text{m}$					

* See web store www.AutomationDirect.com for maximum cut lengths

** To obtain the most current agency approval information, see the Agency Approval Checklist section on the part number's web page at www.AutomationDirect.com



Please Note: Our prices on Continuous Flexing IE Cable are closely tied to the market price for copper. This allows us to offer the best savings possible if conditions are favorable; however, it also means that our prices may increase if market conditions warrant.



LUTZE Industrial Ethernet Cables

LUTZE Industrial Ethernet Cables



Many industrial applications expose cables to hazards that are not present in commercial data cabling installations. Although a cable suited for commercial applications may initially work in a harsh industrial environment, it could quickly fail when used in an industrial application. While commercial grade cables may have a low initial product cost, downtime due to premature failure can be avoided by using a cable that has been designed and tested for the industrial environment. LUTZE's Industrial Ethernet cables were developed to survive the many industrial hazards that commercial cables will not, such as oils, harsh chemicals and cleaning agents often associated with the factory floor.

There are more than just physical hazards to overcome in an industrial application; electrical threats pose an issue for Ethernet cables as well. The presence of EMF/EMI can create a real issue for communication networks and where you can use a shielded commercial product. In most cases, the shielding provided is a single layer of foil which is adequate for installation away from the factory floor. However, when dealing with electrical noise generated by motors and switching equipment, commercial cables struggle to meet the demands of a typical industrial environment. The Industrial Ethernet cables from LUTZE are made with both a foil layer and a tinned copper braid to provide superior noise rejection compared to the commercial counterparts.

Furthermore, commercial Ethernet cables have a tube jacket surrounding the conductor pairs with room within for the pairs to move around and even untwist in applications requiring constant motion. This results in early mechanical or electrical failure of the cable. LUTZE continuous flexing Industrial Ethernet cable have a jacket that is pressure extruded over the cable core, effectively "locking" the conductor pairs in place. This type of jacket construction provides very stable electrical performance, even when the cable is impacted, bent, or repeatedly flexed. Pressure extrusion also provides a very smooth, round, and firm jacket profile that is crush resistant and ideal for obtaining a reliable termination and seal when installing connectors.

Features

- Available in Category 5e, 6 and 6a
- In compliance with TIA 568-C.2 and TIA 1005
- Designed for use in EtherNet/IP systems *
- 26-22 AWG stranded or 22 AWG solid
- 2 or 4 twisted pairs
- Shielded constructions
- Rugged TPE and PVC jacket options
- UL Type CMX OUTDOOR – CM and UL AWM Style 2463 (80°C, 600V)
- Cut to length in 1-foot increments
- Low 20-foot minimum length

* EtherNet/IP is a trademark of ODVA, Inc.

Description

AutomationDirect offers Lutze Industrial Ethernet cable in 2 and 4 pair, unshielded and shielded constructions. Conductors are color coded high density polyethylene insulation. Shielded constructions include both a tinned copper braid shield and aluminized polyester foil overall shield. All constructions feature a rugged jacket with excellent moisture, chemical, UV and weathering resistance, exceptional low-temperature flexibility, and good flame and fire resistance. Some are specifically designed and constructed for continuous flexing applications. Agency approvals include UL Type CMX OUTDOOR, UL Type CMG/PLTC, UL AWM Style 2570, and UL AWM Style 20201.

Click on the thumbnail to the right or go to <https://www.automationdirect.com/VID-WD-0016> for a short introduction on our cut to length cable

