



Profinet Type B Cable



SYSTEMATIC TECHNOLOGY

A104307-1 Cable Specifications

		Part Number	Wire/Cable Type	Flexibility	Minimum Cut Length (ft)*	Approximate Weight (lb/ft)	Price per foot
		A104307-1	Profinet Type B	Flexible	20	0.04	\$1.60
Physical Properties							
Conductor Gauge		22 AWG		Conductor Stranding		7-stranded tinned copper	
Conductor Material		Tinned Copper		Conductor Insulation Wall Thickness		0.015 in; nominal	
Conductor Assembly		1 star quad		Bare Conductor Diameter		0.029 in; nominal	
Color Code	Pair 1	White, Blue		Insulated Conductor Diameter		0.059 in; nominal	
	Pair 2	Yellow, Orange		Twisted Conductor Diameter		0.118 in; nominal	
	Pair 3	N/A		Overall Cable Diameter		0.256 in; nominal	
	Pair 4	N/A		Jacket Color		Green	
Voltage Rating		600V		Jacket Thickness		0.039 in; nominal	
Temperature Rating		-40 to 80 °C (-40 to 176 °F)		Jacket Material		PVC	
Plenum		No		Sunlight Resistant		Yes	
Shield		Overall Aluminized Polyester Foil And Tinned Copper Braid		Oil Resistance		Yes	
Drain		No		Flame Retardant		Yes	
Conductor Insulation Material		Special Polyolefin		Sample Print Legend		<LÜTZE logo> ELECTRONIC ETHERNET (C) PVC 104307 (2x2xAWG22/7) PROFINET TYPE B Cat 5e E336436 (UL) TYPE PLTC FT4 or c(UL)us TYPE CMG 75°C or <logo cURus> AWM STYLE 20201 60°C 600V I/II A/B FT1 RoHS <date YYYYWW> UKCA CE- 44 <metermarking>m	
Minimum Bend Radius		1.54in					
Cabled Core Diameter		0.182 in					
Electrical Characteristics (for 100 meters of cable)							
Impedance (1-100 MHz)		100 Ω 1 – 100 MHz		UL Classification		(cULus) TYPE CMG/PLTC or AWM Style 20201; (cURus) Class I and II, Div. 2; Class 1 Div. 2	
Capacitance		15.2 pF/ft @ 1MHz; Nominal		Approvals**		cULus, cURus, CE, RoHs	
Resistance, Max.		29.5 Ω DC per 1000ft		Attenuation Crosstalk Ratio, Far End (ACRF)		1 ≤ f ≤ 100 MHz: 23.8 - 20 LOG(f/100) dB MIN	
Dielectric Withstanding, Min.		1500V RMS		Insertion Loss		1 ≤ f ≤ 100 MHz: 1.967 √f + 0.023(f) + 0.050/√f dB MAX	
Return Loss		1 ≤ f < 10 MHz: 20 + 5 LOG(f) dB MIN 10 ≤ f < 20 MHz: 25 dB MIN 20 ≤ f ≤ 100 MHz: 25 - 7.0 LOG(f/20) dB MIN		Power Sum Attenuation to Crosstalk Ratio, Far End (PSACRF)		1 ≤ f ≤ 100 MHz: 20.8 - 20 LOG(f/100) dB MIN	
Near End Crosstalk (NEXT)		1 ≤ f ≤ 100 MHz: 35.3 - 15 LOG(f/100) dB MIN		Cross Section			
Power Sum Near End Crosstalk (PSNEXT)		1 ≤ f ≤ 100 MHz: 32.3 - 15 LOG(f/100) dB MIN					
TCL		1 ≤ f ≤ 100 MHz: 30 - 10 LOG(f/100) dB MIN					
ELTCTL		1 ≤ f ≤ 30 MHz: 35 - 20 LOG(f) dB MIN					
Velocity Of Propagation		65%					
Delay		4 ≤ f ≤ 100 MHz: 534 + 36/√(f ns MAX					
Delay Skew		1 ≤ f ≤ 100 MHz: <20ns/100m					

* See web store www.AutomationDirect.com for maximum cut lengths** To obtain the most current agency approval information, see the Agency Approval Checklist section on the part number's web page at www.AutomationDirect.com

Please Note: Our prices on Continuous Flexing IE Cable are closely tied to the market price for copper. This allows us to offer the best savings possible if conditions are favorable; however, it also means that our prices may increase if market conditions warrant.