

ACUAMP® DCT Series DC Current Transducers



DCT series current transducers combine a Hall effect sensor and signal conditioner into a single package for use in DC current applications up to 750A. The DCT series offers jumper-selectable or fixed current input ranges and industry standard 4-20 mA or +/-10 VDC outputs. The DCT series is designed to be compatible with most PLCs, data loggers and SCADA systems. Full-scale input ranges are jumper selectable to 400A (depending on model). This series is available in split-core or fixed-core models.

Applications

Battery Banks

- Monitor load current
- Monitor charging current
- Verifies operation

Transportation

- Measures traction power or auxiliary loads

Wind and Solar Generated Power

- Measure the current produced or consumed.
- Detect mechanical problems before failure occurs.

Electric Heating Elements

- Monitors heater loads
- Faster response than temperature sensors

Monitor DC Powered Motors

- Monitor current of cranes, saws, sorters and positioning equipment.

Features

- 4-20 mA or +/-10 VDC outputs
- Built-in mounting feet with optional 35mm DIN rail adapter available
- Factory matched and calibrated single piece transducer is more accurate than traditional two-piece field installed products.
- Selectable input ranges allow end users to tailor sensing ranges, improve the odds of having the right range for the job and reduces setup time.
- Output is magnetically isolated from the input for safety and to eliminate voltage drop.
- Reduced installation costs
- Split core models make installation a snap.
- Five-year warranty



Click on the thumbnail or go to <https://www.automationdirect.com/VID-CT-0001> for a short introductory video on the AcuAmp Current Switches, Transducers and Indicators



DCT Series DC Current Transducers


Part Number	Description	Pcs/Pkg	Wt (lb)	Price
<u>DCT100-42-24-F</u>	AcuAMP DC current transducer, fixed core, 0-50, 0-75, or 0-100A selectable sensing range, 4-20mA output.	1	0.35	\$166.00
<u>DCT200-42-24-F</u>	AcuAMP DC current transducer, fixed core, 0-100, 0-150, or 0-200A selectable sensing range, 4-20mA output.	1	0.35	\$166.00
<u>DCT100-42-24-S</u>	AcuAMP DC current transducer, split core, 0-50, 0-75, or 0-100A selectable sensing range, 4-20mA output.	1	0.45	\$220.00
<u>DCT200-42-24-S</u>	AcuAMP DC current transducer, split core, 0-100, 0-150, or 0-200A selectable sensing range, 4-20mA output.	1	0.45	\$220.00
<u>DCT400-42-24-S</u>	AcuAMP DC current transducer, split core, 0-200, 0-300, or 0-400A selectable sensing range, 4-20mA output.	1	0.45	\$220.00
<u>DCT750-42-24-F</u>	AcuAMP DC current transducer, large aperture fixed core, 0-500A sensing range, 4-20mA output.	1	0.75	\$292.00
<u>DCT750-42-24-F</u>	AcuAMP DC current transducer, large aperture fixed core, 0-750A sensing range, 4-20mA output.	1	0.75	\$301.00
<u>DCT100-10B-24-S</u>	AcuAMP DC current transducer, split core, bi-directional 0-100A sensing range, bi-polar +/- 0-10 VDC output.	1	0.45	\$251.00
<u>DCT200-10B-24-S</u>	AcuAMP DC current transducer, split core, bi-directional 0-200A sensing range, bi-polar +/- 0-10 VDC output.	1	0.45	\$251.00
<u>DCT300-10B-24-S</u>	AcuAMP DC current transducer, split core, bi-directional 0-300A sensing range, bi-polar +/- 0-10 VDC output.	1	0.45	\$251.00
Accessories				
<u>DRA-2B</u>	35mm DIN rail adapters, 1.70"x0.45"x0.83" [43.7x11.4x21.0 mm]	2	0.40	\$6.00

ACUAMP® DCT Series DC Current Transducers


DCT Series Specifications		
Models Available	10B	42
Power Supply	20-45 VDC	20-45 VDC, 22-38 VAC; Units 500A and over 24 VAC/DC - use Class 2 power supply, Power and signal are isolated.
Power Consumption	2VA	
Output Signal	+/-10VDC	4-20 mA sourcing
Output Load	50kΩ minimum	500Ω maximum
Output Limit	11.5 VDC	23mA
Accuracy	Split-core: 2% FS	Fixed-core: 1% FS; Units 500A and over 2% FS Split-core: 2% FS
Response Time	Split-core: 100ms	Fixed-core: 20ms; Units 500A and over 100ms Split-core: 100ms
Repeatability	1.0% FS	1.0% FS
Input Ranges	Fixed 0-100A, 0-200A & 0-300A	Jumper selectable from 0 to 400A; Fixed ranges on units 500A and over
Sensing Aperture	Split-core: 0.85" [21.6 mm] sq.	Fixed-core: 0.75" [19.1 mm] dia.; Units 500A and over 1.77" [45mm] dia. Split-core: 0.85" [21.6 mm] sq.
Isolation Voltage	3kV (monitored line to output)	
Frequency Range	DC	
Case	UL 94V-0 Flammability Rated	
Environmental	Operating Temperature: -4 to 122°F [-20 to 50°C]	
	Relative Humidity: 0-95% RH, non-condensing	
	Pollution Degree 2	
	Altitude to 2000 meters	
Certifications	cULus listed (E197592), CE	

Wiring



Connection for units up to 400A



Connection for units 500A and over




Our Bi-Directional DC Current Sensors provide an excellent means to monitor battery charging circuits by providing feedback during charging and during battery operation.




ACUAMP® DCT Series DC Current Transducers

Dimensions


Inches [mm]



DCT Series Fixed-Core



DCT Series Split-Core



DCT Series Fixed-Core - Units 500A and over

Notes: Deadfront captive screw terminals.
14AWG solid or stranded. Observe polarity.

See our website www.AutomationDirect.com for complete Engineering drawings.



DC Current Switches and Transducers

Overview

The AcuAMP series of DC current sensors is a family of high-performance sensors offering outstanding features, flexibility, and durability at an incredible Price. Choose from a wide selection of current transducers and current switches, all designed in a rugged industry standard feed-through package.

DCT and DCS100 series have multiple input ranges (set by movable jumpers) for maximum flexibility across many current ratings. DCT series include output choices of 4 to 20 mA or +/-10 VDC bidirectional models.


DCS series outputs are available in isolated solid state Normally Open and in Single Pole Double Throw (SPDT) relay configurations.

DCT series current transducers combine a Hall Effect sensor and signal conditioner into a single package for use in DC current applications up to 400A. DCT series are available in split-core or fixed-core enclosures.

DCS100 series combine a Hall effect sensor, signal conditioner and a limit alarm into a single package. DCS100 series models are available in a fixed

core case with the choice of a relay or universal solid-state output.

All models are panel-mountable; convenient DIN-rail adapter accessories are available. Use the Selection Guide below to find the best sensor for your requirements.



Selection Guide

AcuAMP DC Current Sensors Specifications by Model Type			
Specifications	Transducer		Switch
Model	DCT	DCT 500 to 750A Large Aperture	DCS100
Power Supply	20-45 VDC*, 22-38 VAC	24 VAC/DC, Use Class 2 power supply	20-28 VAC/VDC
Power Consumption	2VA		
Setpoint (Trip point)	N/A	N/A	11-Turn Potentiometer
Output Signal	4-20 mA Sourcing +/- 10VDC (Bidirectional models only)	4-20 mA Sourcing	N/A
Output Limit	4-20 mA: 23mA 0-10 VDC: 11.5 VDC	23mA	N/A
Output Loading	4-20 mA: 500Ω max 0-10 VDC: 50kΩ min.	500Ω max	N/A
Output Switch	N/A		AE models: Normally Open Solid State 1C models: Single Pole Double Throw (SPDT) Relay
Switch Rating	N/A		AE models: Solid State N.O. (0.15 A @ 240 VAC/ VDC) 1C models: SPDT (Form C) Relay 5A General Purpose @ 240VAC 3A Inductive @ 240VAC 3A @ 30VDC 1/8 HP @ 240VAC
Off State Leakage	N/A		AE: <10μA; 1C: None
Accuracy	Fixed core: 1% FS, Split core: 2% FS	2% FS	N/A
Current Ranges	Jumper Selectable: DCT100-42: 0-50A, 0-75A, 0-100A DCT200-42: 0-100A, 0-150A, 0-200A DCT400-42: 0-200A, 0-300A, 0-400A DCT500-42: 0-500A Fixed: DCT100-10B: 0-100A Bidirectional DCT200-10B: 0-200A Bidirectional DCT300-10B: 0-300A Bidirectional	Fixed: DCT500-42: 0-500A DCT750-42: 0-750A	5-15, 10-50 and 20-100 A, Jumper Selectable
Repeatability	1% FS	1% FS	0.5% FS
Response Time	Fixed core: 20ms (to 90% of step change) Split core: 100ms (to 90% of step change)	100ms (to 90% of step change)	100ms (10% above setpoint), 20ms (100% above setpoint)
Hysteresis Approx	N/A		5% of setpoint
Isolation Voltage	3KV		
Frequency Range	DC		
Case	UL 94V-0 Flammability Rated		
Environmental	Operating Temperature: -4 to 122°F [-20 to 50°C]		Operating Temperature: AE = -40 to 140°F [-40 to 60°C]; 1C = -4 to 122°F [-20 to 50°C]
	Relative Humidity: 0-95% RH, Non-condensing		
	Pollution Degree 2		
	Altitude to 2000 meters		
Sensing Aperture	Fixed core: 0.75" [19.1 mm] dia. Split core: 0.85" [21.6 mm] sq	1.77" [45mm] dia.	0.75" [19.1 mm] dia.

* DC only for -10B Bidirectional models



DC Current Switches and Transducers Applications


Application Guide

AcuAMP DC current sensors are a great fit for many applications, including battery charge systems, solar panels, and Uninterruptible Power Systems. With both current transducers and current switches, this sensor family gives you valuable data for processes ranging from monitoring loads to preventive maintenance.


The bi-directional models allow the monitoring of batteries while they are being charged or consumed and can be used to trigger a warning if critical low levels are reached. They can also monitor the output of a photovoltaic array to make sure there is enough energy being generated to keep the process running.

Transducer


Battery Charging System - Bidirectional Output



Failure Detection



Solar Panel - Current Drop



Click on the thumbnail or go to <https://www.automationdirect.com/VID-CT-0001> for a short introductory video on the AcuAmp Current Switches, Transducers and Indicators

When the sun is blocked, the current drops. The Current Operated Switch detects the drop in current and activates the relay which turns on the alarm light.